




4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

BLUE	HARD TRAY	323X136X19	30u"	86.5	8	44.5	70	73.15	89	71.65	164	8-2371900-8	5
BLACK	HARD TRAY	323X136X19	30u"	86.5	8	44.5	70	73.15	89	71.65	164	6-2371900-8	5
BLUE	HARD TRAY	330X235X19.3	30u"	86.5	8	44.5	70	73.15	89	71.65	164	7-2371900-8	
BLACK	HARD TRAY	330X235X19.3	30u"	45.0	8	44.5	70	73.15	89	71.65	164	7-2371900-4	
BLACK	HARD TRAY	330X235X19.3	30u"	86.5	8	44.5	70	73.15	89	71.65	164	5-2371900-8	
BLACK	HARD TRAY	330X235X19.3	30u"	53.5	8	28	37	40.15	56	38.65	98	5-2371900-7	
BLACK	SOFT TRAY	338X235X20.3	30u"	36.5	8	19.5	20	23.15	39	21.65	64	5-2371900-6	
BLACK	SOFT TRAY	TBD	30u"	22.5	8	12.5	6	9.15	25	7.65	36	5-2371900-5	
BLACK	HARD TRAY	330X235X19.3	30u"	10.0	8	44.5	70	73.15	89	71.65	164	5-2371900-4	
BLACK	HARD TRAY	330X235X19.3	30u"	10.0	8	28	37	40.15	56	38.65	98	5-2371900-3	
BLACK	SOFT TRAY	338X235X20.3	30u"	10.0	8	19.5	20	23.15	39	21.65	64	5-2371900-2	
BLACK	SOFT TRAY	TBD	30u"	10.0	8	12.5	6	9.15	25	7.65	36	5-2371900-1	
BLACK	HARD TRAY	330X235X19.3	15u"	86.5	8	44.5	70	73.15	89	71.65	164	4-2371900-8	
BLACK	HARD TRAY	330X235X19.3	15u"	53.5	8	28	37	40.15	56	38.65	98	4-2371900-7	
BLACK	SOFT TRAY	338X235X20.3	15u"	36.5	8	19.5	20	23.15	39	21.65	64	4-2371900-6	
BLACK	SOFT TRAY	TBD	15u"	22.5	8	12.5	6	9.15	25	7.65	36	4-2371900-5	
BLACK	HARD TRAY	330X235X19.3	15u"	10.0	8	44.5	70	73.15	89	71.65	164	4-2371900-4	
BLACK	HARD TRAY	330X235X19.3	15u"	10.0	8	28	37	40.15	56	38.65	98	4-2371900-3	
BLACK	SOFT TRAY	338X235X20.3	15u"	10.0	8	19.5	20	23.15	39	21.65	64	4-2371900-2	
BLACK	SOFT TRAY	TBD	15u"	10.0	8	12.5	6	9.15	25	7.65	36	4-2371900-1	
BLACK	HARD TRAY	330X235X19.3	G/F	86.5	8	44.5	70	73.15	89	71.65	164	3-2371900-8	
BLACK	HARD TRAY	330X235X19.3	G/F	53.5	8	28	37	40.15	56	38.65	98	3-2371900-7	
BLACK	SOFT TRAY	338X235X20.3	G/F	36.5	8	19.5	20	23.15	39	21.65	64	3-2371900-6	
BLACK	SOFT TRAY	TBD	G/F	22.5	8	12.5	6	9.15	25	7.65	36	3-2371900-5	
BLACK	HARD TRAY	330X235X19.3	G/F	10.0	8	44.5	70	73.15	89	71.65	164	3-2371900-4	
BLACK	HARD TRAY	330X235X19.3	G/F	10.0	8	28	37	40.15	56	38.65	98	3-2371900-3	
BLACK	SOFT TRAY	338X235X20.3	G/F	10.0	8	19.5	20	23.15	39	21.65	64	3-2371900-2	
BLACK	SOFT TRAY	TBD	G/F	10.0	8	12.5	6	9.15	25	7.65	36	3-2371900-1	
BLACK	HARD TRAY	330X235X19.3	30u"	NA		44.5	70	73.15	89	71.65	164	2-2371900-4	
BLACK	HARD TRAY	330X235X19.3	30u"	NA		28	37	40.15	56	38.65	98	2-2371900-3	
BLACK	SOFT TRAY	338X235X20.3	30u"	NA		19.5	20	23.15	39	21.65	64	2-2371900-2	
BLACK	SOFT TRAY	TBD	30u"	NA		12.5	6	9.15	25	7.65	36	2-2371900-1	
BLACK	HARD TRAY	330X235X19.3	15u"	NA		44.5	70	73.15	89	71.65	164	1-2371900-4	
BLACK	HARD TRAY	330X235X19.3	15u"	NA		28	37	40.15	56	38.65	98	1-2371900-3	
BLACK	SOFT TRAY	338X235X20.3	15u"	NA		19.5	20	23.15	39	21.65	64	1-2371900-2	
BLACK	SOFT TRAY	TBD	15u"	NA		12.5	6	9.15	25	7.65	36	1-2371900-1	
BLACK	HARD TRAY	330X235X19.3	G/F	NA		44.5	70	73.15	89	71.65	164	2371900-4	
BLACK	HARD TRAY	330X235X19.3	G/F	NA		28	37	40.15	56	38.65	98	2371900-3	
BLACK	SOFT TRAY	338X235X20.3	G/F	NA		19.5	20	23.15	39	21.65	64	2371900-2	
BLACK	SOFT TRAY	TBD	G/F	NA		12.5	6	9.15	25	7.65	36	2371900-1	
COLOR	TYPE	L * W * H(TRAY)	PRECIOUS PLATING THICKNESS (TOTAL)	W	V	J	N	C	B	A	POS.	PART NUMBER	
	PACKAGE			MYLAR SIZE (PAGE 4)									

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.3

2 PLC ±0.20

3 PLC ±0.050

4 PLC ±-

ANGLES ±-

FINISH -

MATERIAL

-

-

DWN SANDERS_YAN 08APR2020

CHK MIKE.CHEN 08APR2020

APVD HOPE.LU 08APR2020

PRODUCT SPEC 108-160247

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME PCI EXPRESS CARD EDGE CONNECTOR GEN5, 1.5 SOLDER TAB, WITHOUT RIDGE

SIZE A2CAGE CODE 00779DRAWING NO C-2371900RESTRICTED TO -


SCALE 6:1SHEET 2 OF 7REV B


1471-9 (3/13)



A

1471-9 (3/13)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SANDERS YAN CHK MIKE.CHEN APVD HOPE LW PRODUCT SPEC 108-160247 APPLICATION SPEC - WEIGHT -		08APR2020 08APR2020 08APR2020		TE TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PCI EXPRESS CARD EDGE CONNECTOR GEN5, 1.5 SOLDER TAB, WITHOUT RIDGE					
		0 PLC ±.3 1 PLC ±0.3 2 PLC ±0.20 3 PLC ±0.050 4 PLC ±. ANGLES ±.		FINISH		SIZE A2		CAGE CODE 00779	
MATERIAL		FINISH		WEIGHT		DRAWING NO C-2371900		RESTRICTED TO	
-		-		-		SCALE 6:1		SHEET 3 of 7	
-		-		CUSTOMER DRAWING		REV B			



1471-9 (3/13)

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20


BY -

ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

FRONT VIEW




36POS AS SHOWN
SCALE 4:1

FRONT VIEW




64POS AS SHOWN
SCALE 4:1

FRONT VIEW



98POS AS SHOWN
SCALE 4:1

FRONT VIEW




164POS AS SHOWN
SCALE 4:1

W REF

V REF

J REF




MYLAR SIZE
SCALE 4:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
SANDERS, YAN
CHK
MIKE, CHEN
APVD
HOPE, LU

08APR2020
08APR2020
08APR2020

DIMENSIONS:
mm



TOLERANCES, UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.3

2 PLC ±0.20

3 PLC ±0.050

4 PLC ANGLES ±-

FINISH

MATERIAL

-

-

PRODUCT SPEC
108-160247

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

NAME
PCI EXPRESS CARD EDGE CONNECTOR
GEN5, 1.5 SOLDER TAB, WITHOUT RIDGE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2371900

RESTRICTED TO
-

SCALE
6:1

SHEET
5 OF 7

REV
B

TE Connectivity


1471-9 (3/13)

D


C

B

A




HARD TRAY: 164POS
SCALE 1:2




HARD TRAY: 98POS
SCALE 1:2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 08APR2020 SANDERS, YAN	 TE Connectivity			
DIMENSIONS: mm		CHK 08APR2020 MIKE, CHEN				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.3 2 PLC ±0.20 3 PLC ±0.050 4 PLC ± ANGLES ± FINISH		APVD 08APR2020 HOPE, LU	NAME PCI EXPRESS CARD EDGE CONNECTOR GEN5, 1.5 SOLDER TAB, WITHOUT RIDGE			
MATERIAL -		PRODUCT SPEC 108-160247	SIZE A2	CAGE CODE 00779	DRAWING NO C-2371900	RESTRICTED TO -
		APPLICATION SPEC -	SCALE 6:1		SHEET 6 OF 7	REV B
		WEIGHT -	CUSTOMER DRAWING			

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



SOFT TRAY: 64POS
SCALE 1:2



HARD TRAY: FOR 6-2371900-8 AND 8-2371900-8 (164POS)
SCALE 1:2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2371900-4](#) [2-2371900-4](#) [2371900-4](#) [3-2371900-4](#) [3-2371900-8](#) [4-2371900-4](#) [4-2371900-8](#) [5-2371900-4](#) [5-2371900-8](#) [6-2371900-8](#) [7-2371900-4](#)