





SMT

KEY LOCATIONS




NOTES:

1. MATERIAL:  
CONNECTOR:  
HOUSING - HIGH TEMPERATURE THERMOPLASTIC GLASS FILLED, UL 94V-0, BLACK  
TERMINALS - COPPER ALLOY  
SHELL  
NICKEL SILVER, C770, THICKNESS: 0.250/0.254
2. FINISH:  
CONNECTOR  
OPTION 1  
CONTACT AREA - 0.38µm MIN GOLD OVER 2.54 µm NICKEL  
SOLDER FOOT AREA - 2.54-5.09µm TIN OVER 1.27 µm NICKEL  
OPTION 2  
CONTACT AREA - 0.76µm MIN GOLD OVER 2.54 µm NICKEL  
SOLDER FOOT AREA - 2.54-5.09µm TIN OVER 1.27 µm NICKEL
3. TERMINAL SOLDER FEET TO BE COPLANAR WITHIN 0.10 MEASURED FROM DATUM E
4. DATE CODE: 4 DIGIT (3 DIGIT DAY, 1 DIGIT YEAR) ON CONNECTOR ONLY
5. CIRCUIT IDENTIFIER: SEE APPROPRIATE INDUSTRY SPECIFICATION FOR LOCATION OF PIN 1
6. TO BE USED WITH THE FOLLOWING CABLE SERIES:  
79575/74563/79576/74573/79536/74562/74569/74586
7. PACKAGED PER PACKAGING SPECIFICATION: PK-75783-001
8. CONFORMS TO PRODUCT SPECIFICATION: PS-75783-001
9. PROCESS PER APPLICATION SPECIFICATION: AS-75783-001
10. THIS PART CONFORMS TO CLASS C REQUIREMENTS OF COSMETIC SPEC PS-45499-002



36 CIRCUIT RETENTION FIT SHELL OPTION SHOWN








iPass™ IS A TRADEMARK OF MOLEX

CIRCUIT SIZE	DIM 'A'	DIM 'B'	DIM 'C'
36	16.00	17.80	15.80
50	21.60	23.40	21.40
68	28.80	30.60	28.60

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS <b>mm</b>		SCALE <b>5:1</b>		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS 75784-0110, 75784-0112, 75784-0125, 75784-0147 & 75784-0148							
GENERAL TOLERANCES (UNLESS SPECIFIED)						STATUS: Production					
ANGULAR TOL ± 0.5°						DRWN: Vishal Ramesh Hosur 2024-05-08					
4 PLACES ±						CHK'D: Ganesh Rao B 2024-05-20					
3 PLACES ±						APPR: Gurunandan GA 2024-05-20					
2 PLACES ± 0.130						DRAWING SERIES <b>C-SIZE 75784</b>					
1 PLACE ± 0.25						DOCUMENT NUMBER <b>SD-75784-001</b>					
0 PLACES ±						DOC TYPE DOC PART REVISION <b>PSD 001 D9</b>					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		MATERIAL NUMBER SEE TABLE		CUSTOMER GENERAL MARKET		SHEET NUMBER 1 OF 12	

# ASSEMBLY WITH PRE-POSITIONING DEVICE

PICK & PLACE NOZZLE AREA




36 CIRCUIT RETENTION FIT SHOWN

**NOTES:**





1. PICK AND PLACE LOCATION DEFINED ON APPLICATION SPECIFICATION AS-75783-001
2. PACKAGING CONSISTS OF CONNECTOR AND SHELL WITH A PRE-POSITIONING PICK AND PLACE DEVICE THAT ARE PACKAGED IN "TAPE AND REEL" FOR ROBOTIC PICK AND PLACE.

iPass™ IS A TRADEMARK OF MOLEX


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS <b>mm</b>		SCALE <b>5:1</b>		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS 75784-0110, 75784-0112, 75784-0125, 75784-0147 & 75784-0148				 <p>I-PASS VERT CONNECTOR INTERNAL ASSY W/SHELL 0.8MM PITCH I/O</p>			
GENERAL TOLERANCES (UNLESS SPECIFIED)				STATUS: Production							
ANGULAR TOL ± 0.5°				DRWN: Vishal Ramesh Hosur 2024-05-08				DOCUMENT NUMBER			
4 PLACES ±				CHK'D: Ganesh Rao B 2024-05-20				SD-75784-001			
3 PLACES ±				APPR: Gurunandan GA 2024-05-20				PSD 001 D9			
2 PLACES ± 0.130				THIRD ANGLE PROJECTION				MATERIAL NUMBER			
1 PLACE ± 0.25				DRAWING				CUSTOMER			
0 PLACES ±				C-SIZE				GENERAL MARKET			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SERIES				SHEET NUMBER			
				75784				SEE TABLE			
								2 OF 12			

CIRCUIT SIZE	DIM 'D'
36	19.50
50	25.10
68	32.30


# SHELL PCB INTERFACE



**RETENTION-FIT  
SHELL OPTION**



**SMT SHELL OPTION**





**THRU-HOLE SHELL OPTION  
SEE TABLE FOR LENGTH  
(X.XX DENOTES LENGTH)**

**RECOMMENDED PCB THICKNESS  
FOR SPECIFIED TAIL LENGTH**





TAIL LENGTH	PCB THICKNESS
1.96	1.57 (.062)
2.79	2.36 (.093)
3.18	2.79 (.110)
3.56	3.18 (.125)

**NOTE:**  
 RETENTION FIT DENOTES TAILS THAT OFFER RETENTION TO PCB DURING REFLOW PROCESS  
 SMT DENOTES SURFACE MOUNT TERMINATION  
 T/H X.XX DENOTES THRU-HOLE TAIL OF LENGTH X.XX

iPass™ IS A TRADEMARK OF MOLEX

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS 75784-0110, 75784-0112, 75784-0125, 75784-0147 & 75784-0148							
mm		4:1		 I-PASS VERT CONNECTOR INTERNAL ASSY W/SHELL 0.8MM PITCH I/O PRODUCT SALES DRAWING							
GENERAL TOLERANCES (UNLESS SPECIFIED)											
ANGULAR TOL ± 0.5°											
4 PLACES		±									
3 PLACES		±									
2 PLACES		± 0.130		STATUS: Production		2024-05-08		DOCUMENT NUMBER		DOC TYPE   DOC PART   REVISION	
1 PLACE		± 0.25		DRWN: Vishal Ramesh Hosur		2024-05-20		SD-75784-001		PSD 001 D9	
0 PLACES		±		CHK'D: Ganesh Rao B		2024-05-20		MATERIAL NUMBER		CUSTOMER	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		SHEET NUMBER	
						C-SIZE		75784		3 OF 12	
								SEE TABLE		GENERAL MARKET	

# KEYING OPTIONS



	UNIVERSAL SHELL	LEFT KEY SHELL	RIGHT KEY SHELL	DUAL KEY SHELL
NO KEY PLUG	YES	NO	NO	NO
LEFT KEY PLUG	YES	YES	NO	NO
RIGHT KEY PLUG	YES	NO	YES	NO
UNIVERSAL PLUG	YES	YES	YES	YES

iPass™ IS A TRADEMARK OF MOLEX

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS <b>mm</b>		SCALE <b>2:1</b>		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS 75784-0110, 75784-0112, 75784-0125, 75784-0147 & 75784-0148							
GENERAL TOLERANCES (UNLESS SPECIFIED)				STATUS: Production DRWN: Vishal Ramesh Hosur 2024-05-08 CHK'D: Ganesh Rao B 2024-05-20 APPR: Gurunandan GA 2024-05-20							
ANGULAR TOL ± 0.5°											
4 PLACES ±											
3 PLACES ±											
2 PLACES ± 0.130											
1 PLACE ± 0.25				DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
0 PLACES ±				<b>SD-75784-001</b>				<b>PSD</b>		<b>001 D9</b>	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER	
				<b>C-SIZE</b>		<b>75784</b>		<b>SEE TABLE</b>		<b>GENERAL MARKET</b>	
				SHEET NUMBER		4 OF 12					

**molex**

I-PASS VERT CONNECTOR  
INTERNAL ASSY W/SHELL 0.8MM PITCH I/O

PRODUCT SALES DRAWING

A

# 36 CIRCUIT ITEM NUMBERS

CIRCUIT SIZE	ITEM NUMBER	PLATING OPTION	SHELL PCB OPTION	SHELL KEY OPTION
36	75784-0109	OPTION 1	RETENTION	DUAL
36	75784-0111	OPTION 1	SMT	RIGHT
36	75784-0119	OPTION 2	RETENTION	LEFT
36	75784-0120	OPTION 2	RETENTION	RIGHT
36	75784-0126	OPTION 1	SMT	UNIVERSAL
36	75784-0131	OPTION 1	T/H 1.96	DUAL
36	75784-0132	OPTION 1	T/H 1.96	UNIVERSAL
36	75784-0136	OPTION 2	T/H 1.69	UNIVERSAL

CIRCUIT SIZE	ITEM NUMBER	PLATING OPTION	SHELL PCB OPTION	SHELL KEY OPTION
36	75784-0137	OPTION 1	T/H 2.79	LEFT
36	75784-0138	OPTION 1	T/H 2.79	RIGHT
36	75784-0139	OPTION 1	T/H 2.79	DUAL
36	75784-0140	OPTION 1	T/H 2.79	UNIVERSAL
36	75784-0143	OPTION 2	T/H 2.79	DUAL
36	75784-0144	OPTION 2	T/H 2.79	UNIVERSAL
36	75784-0152	OPTION 2	T/H 3.18	UNIVERSAL
36	75784-0156	OPTION 1	T/H 3.56	UNIVERSAL
36	75784-0159	OPTION 2	T/H 3.56	DUAL
36	75784-0160	OPTION 2	T/H 3.56	UNIVERSAL

iPass™ IS A TRADEMARK OF MOLEX

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS	SCALE	CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS 75784-0110, 75784-0112, 75784-0125, 75784-0147 & 75784-0148			<h1 style="margin: 0;">molex</h1>						
GENERAL TOLERANCES (UNLESS SPECIFIED)		STATUS: Production DRWN: Vishal Ramesh Hosur 2024-05-08 CHK'D: Ganesh Rao B 2024-05-20 APPR: Gurunandan GA 2024-05-20			I-PASS VERT CONNECTOR INTERNAL ASSY W/SHELL 0.8MM PITCH I/O						
ANGULAR TOL ± 0.5°					PRODUCT SALES DRAWING						
4 PLACES ±					DOCUMENT NUMBER			DOC TYPE	DOC PART	REVISION	
3 PLACES ±					SD-75784-001			PSD	001	D9	
2 PLACES ± 0.130					MATERIAL NUMBER			CUSTOMER		SHEET NUMBER	
1 PLACE ± 0.25		SEE TABLE			GENERAL MARKET		5 OF 12				
0 PLACES ±		THIRD ANGLE PROJECTION		DRAWING	SERIES						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				C-SIZE	75784						



# 68 CIRCUIT ITEM NUMBERS



CIRCUIT SIZE	ITEM NUMBER	PLATING OPTION	SHELL PCB OPTION	SHELL KEY OPTION
68	75784-0332	OPTION 1	T/H 1.96	UNIVERSAL

CIRCUIT SIZE	ITEM NUMBER	PLATING OPTION	SHELL PCB OPTION	SHELL KEY OPTION
68	75784-0338	OPTION 1	T/H 2.79	RIGHT
68	75784-0340	OPTION 1	T/H 2.79	UNIVERSAL
68	75784-0348	OPTION 1	T/H 3.18	UNIVERSAL

iPass™ IS A TRADEMARK OF MOLEX

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS	SCALE	CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS 75784-0110, 75784-0112, 75784-0125, 75784-0147 & 75784-0148				molex			
mm	1:1					I-PASS VERT CONNECTOR INTERNAL ASSY W/SHELL 0.8MM PITCH I/O			
GENERAL TOLERANCES (UNLESS SPECIFIED)						PRODUCT SALES DRAWING			
ANGULAR TOL ± 0.5°									
4 PLACES ±									
3 PLACES ±									
2 PLACES ± 0.130		STATUS: Production							
1 PLACE ± 0.25		DRWN: Vishal Ramesh Hosur		2024-05-08		DOCUMENT NUMBER		DOC TYPE   DOC PART   REVISION	
0 PLACES ±		CHK'D: Ganesh Rao B		2024-05-20		SD-75784-001		PSD 001 D9	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER	
				C-SIZE		75784		SEE TABLE	
				GENERAL MARKET		7 OF 12			

# VERTICAL CONNECTOR WITH RETENTION FIT & THRU-HOLE SHELL PCB FOOT PRINT





CIRCUIT SIZE	PEG TO PEG	FIRST TO LAST PAD	CENTERLINE TO PAD	CENTERLINE TO PAD	SHELL PEG TO PEG	SHELL FOOTPRINT WIDTH
	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'	DIM 'E'	DIM 'F'
36	16.00	13.60	6.60	7.00	17.80	19.80
50	21.60	19.20	9.40	9.80	23.40	25.40
68	28.80	26.40	13.00	13.40	30.60	32.60

iPass™ IS A TRADEMARK OF MOLEX

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																							
DIMENSION UNITS	SCALE	CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS 75784-0110, 75784-0112, 75784-0125, 75784-0147 & 75784-0148																					
mm	5:1	<div style="font-size: 24px; font-weight: bold; margin-bottom: 10px;">molex</div> <p style="margin: 0;">I-PASS VERT CONNECTOR INTERNAL ASSY W/SHELL 0.8MM PITCH I/O</p> <p style="margin: 0;">PRODUCT SALES DRAWING</p> <table border="1" style="width: 100%; border-collapse: collapse; font-size: 8px;"> <tr> <td colspan="3" style="font-size: 8px;">DOCUMENT NUMBER</td> <td style="font-size: 8px;">DOC TYPE</td> <td style="font-size: 8px;">DOC PART</td> <td style="font-size: 8px;">REVISION</td> </tr> <tr> <td colspan="3" style="text-align: center; font-weight: bold;">SD-75784-001</td> <td style="text-align: center;">PSD</td> <td style="text-align: center;">001</td> <td style="text-align: center;">D9</td> </tr> </table>										DOCUMENT NUMBER			DOC TYPE	DOC PART	REVISION	SD-75784-001			PSD	001	D9
DOCUMENT NUMBER												DOC TYPE	DOC PART	REVISION									
SD-75784-001												PSD	001	D9									
GENERAL TOLERANCES (UNLESS SPECIFIED)																							
ANGULAR TOL ± 0.5°																							
4 PLACES	±																						
3 PLACES	±																						
2 PLACES	± 0.130																						
1 PLACE	± 0.25																						
0 PLACES	±																						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER																
			C-SIZE	75784	SEE TABLE	GENERAL MARKET	8 OF 12																
		STATUS: Production		2024-05-08																			
		DRWN: Vishal Ramesh Hosur		2024-05-20																			
		CHK'D: Ganesh Rao B		2024-05-20																			
		APPR: Gurunandan GA		2024-05-20																			



# VERTICAL CONNECTOR WITH SMT SHELL PCB FOOT PRINT



	PEG TO PEG	FIRST TO LAST PAD	CENTERLINE TO PAD	CENTERLINE TO PAD	SHELL PEG TO PEG	SHELL FOOTPRINT WIDTH	CENTERLINE TO PAD EDGE
CIRCUIT SIZE	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'	DIM 'E'	DIM 'F'	DIM 'G'
36	16.00	13.60	6.60	7.00	17.80	20.80	8.825
50	21.60	19.20	9.40	9.80	23.40	26.40	11.625
68	28.80	26.40	13.00	13.40	30.60	33.60	15.225


iPass™ IS A TRADEMARK OF MOLEX

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS <b>mm</b>	SCALE <b>5:1</b>	CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS 75784-0110, 75784-0112, 75784-0125, 75784-0147 & 75784-0148	<b>molex</b>			
GENERAL TOLERANCES (UNLESS SPECIFIED)						I-PASS VERT CONNECTOR INTERNAL ASSY W/SHELL 0.8MM PITCH I/O
ANGULAR TOL ± 0.5°			PRODUCT SALES DRAWING			
4 PLACES ±			DOCUMENT NUMBER			
3 PLACES ±			SD-75784-001			
2 PLACES ± 0.130			DOC TYPE   DOC PART   REVISION			
1 PLACE ± 0.25			PSD   001   D9			
0 PLACES ±			SHEET NUMBER			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION	DRAWING <b>C-SIZE</b>	SERIES <b>75784</b>	MATERIAL NUMBER SEE TABLE	CUSTOMER GENERAL MARKET	9 OF 12

STATUS: Production  
 DRWN: Vishal Ramesh Hosur 2024-05-08  
 CHK'D: Ganesh Rao B 2024-05-20  
 APPR: Gurunandan GA 2024-05-20

# VERTICAL CONNECTOR WITH SHELL PCB FOOT PRINT DESCRIPTIONS






36 CIRCUIT SHOWN

iPass™ IS A TRADEMARK OF MOLEX

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIMENSION UNITS	SCALE	CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS 75784-0110, 75784-0112, 75784-0125, 75784-0147 & 75784-0148			molex							
GENERAL TOLERANCES (UNLESS SPECIFIED)		STATUS: Production DRWN: Vishal Ramesh Hosur 2024-05-08 CHK'D: Ganesh Rao B 2024-05-20 APPR: Gurunandan GA 2024-05-20			I-PASS VERT CONNECTOR INTERNAL ASSY W/SHELL 0.8MM PITCH I/O							
ANGULAR TOL ± 0.5°					PRODUCT SALES DRAWING							
4 PLACES ±					DOCUMENT NUMBER			DOC TYPE	DOC PART	REVISION		
3 PLACES ±					SD-75784-001			PSD	001	D9		
2 PLACES ± 0.130					MATERIAL NUMBER			CUSTOMER		SHEET NUMBER		
1 PLACE ± 0.25		SEE TABLE			GENERAL MARKET		10 OF 12					
0 PLACES ±		THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				C-SIZE	75784	SEE TABLE		GENERAL MARKET				

# MATING INTERFACE (FOR REFERENCE ONLY)



- NOTES:
- PAD CONFIGURATION FOR FIRST MATE.
  - PAD CONFIGURATION FOR SECOND MATE.
  - PAD CONFIGURATION FOR THIRD MATE. (HIGH SPEED SIGNALS)
  - FOR PIN ASSIGNMENTS AND MATING SEQUENCE (1ST, 2ND, 3RD), SEE APPLICABLE SPECIFICATION.
  - MINIMUM STEP REQUIRED IF PCB MADE WIDER THAN TONGUE.



iPass™ IS A TRADEMARK OF MOLEX

CIRCUIT SIZE	TERM/SIDE 'N'	DIM 'B'	DIM 'C'	DIM 'D'	DIM 'E'
36	18	13.60	6.60	7.00	15.60
50	25	19.20	9.40	9.80	21.20
68	34	26.40	13.00	13.40	28.40

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
DIMENSION UNITS <b>mm</b>	SCALE <b>1:1</b>	CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS 75784-0110, 75784-0112, 75784-0125, 75784-0147 & 75784-0148			
GENERAL TOLERANCES (UNLESS SPECIFIED)		<p><b>molex</b></p> <p>I-PASS VERT CONNECTOR INTERNAL ASSY W/SHELL 0.8MM PITCH I/O</p> <p>PRODUCT SALES DRAWING</p>			
ANGULAR TOL ± 0.5°					
4 PLACES	±				
3 PLACES	±				
2 PLACES	± 0.130				
1 PLACE	± 0.25	STATUS: Production	2024-05-08	DOCUMENT NUMBER	DOC TYPE   DOC PART   REVISION
0 PLACES	±	DRWN: Vishal Ramesh Hosur	2024-05-20	<b>SD-75784-001</b>	PSD 001 D9
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER   CUSTOMER   SHEET NUMBER
			<b>C-SIZE</b>	<b>75784</b>	SEE TABLE   GENERAL MARKET   11 OF 12

REVISION DESCRIPTION

REV	DATE	DESCRIPTION
D5	2019/4/17	DRAWING MIGRATION TO ECTR
D6	2021/08/03	OBSOLETE PART NUMBERS: 757840008,757840019,757840020,757840021,757840022,757840023,757840024,757840029,757840030,757840031,757840033, 757840034,757840035,757840107,757840108,757840130,757840135,757840145,757840146,757840149,757840153,757840154, 757840155,757840157,757840158,757840207,757840209,757840210,757840211,757840219,757840220,757840221,757840222, 757840223,757840224,757840227,757840228,757840229,757840230,757840231,757840233,757840234,757840235,757840236, 757840237,757840238,757840239,757840241,757840242,757840243,757840246,757840247,757840248,757840249,757840250, 757840251,757840309,757840310,757840311,757840312,757840319,757840321,757840322,757840323,757840325,757840331, 757840335,757840339,757840341,757840342,757840343,757840345,757840346,757840347,757840349,757840350
D7	2023/03/29	1)OBSOLETE PART NUMBERS 757840050, 757840252, 757840051, 757840052, 757840012, 757840336, 757840337, 757840141, 757840142, 757840025, 757840344, 757840028, 757840026, 757840032, 757840150, 757840151, 757840352, 757840232, 757840039, 757840037, 757840038, 757840042, 757840240, 757840043, 757840040, 757840041, 757840046, 757840047, 757840121, 757840045, 757840127, 757840007, 757840048, 757840049.  2)REMOVED SHEET 5 AND REMOVED 26 CKT ITEM NUMBERS
D8	2024/02/23	75784-0136 & 75784-0137, MENTIONED PART NUMBER HAVE BEEN RE-ADDED TO THE SHEET 5.
D9	2024/05/08	REMOVED OBSOLETE PART NUMBERS 75784-0110, 75784-0112, 75784-0125, 75784-0147 & 75784-0148

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
DIMENSION UNITS		SCALE	CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS 75784-0110, 75784-0112, 75784-0125, 75784-0147 & 75784-0148							
mm		1:1								
GENERAL TOLERANCES (UNLESS SPECIFIED)			STATUS: Production DRWN: Vishal Ramesh Hosur 2024-05-08 CHK'D: Ganesh Rao B 2024-05-20 APPR: Gurunandan GA 2024-05-20				I-PASS VERT CONNECTOR INTERNAL ASSY W/SHELL 0.8MM PITCH I/O			
ANGULAR TOL ± 0.5°										
4 PLACES ±										
3 PLACES ±										
2 PLACES ± 0.130										
1 PLACE ± 0.25										
0 PLACES ±			PRODUCT SALES DRAWING DOCUMENT NUMBER: SD-75784-001   DOC TYPE: PSD   DOC PART: 001   REVISION: D9							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER			
			C-SIZE	75784	SEE TABLE	GENERAL MARKET	12 OF 12			