

DO NOT
SCALE FROM
THIS PRINT

TABLE 1		
LEAD STYLE	"A"	"B"
-02	.075 [1.91] 	.075[1.91]
-03	.065 [1.65] 	.055[1.40]

TABLE 4	
POSITIONS	COPLANARITY
02 THRU 29	.004[0.10]
30 THRU 50	.006[0.15]

No OF POS PER ROW
-02 THRU -50
(SEE NOTE 10)

LEAD STYLE
-02: .075 [1.91]
(USE T-1S16-03-XX-2)
-03: .065 [1.65]
(USE T-1S16-04-XX-2)

PLATING SPECIFICATION
-L: 10µ" LIGHT SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
-F: 3µ" FLASH SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
-H: 30µ" HEAVY GOLD IN CONTACT AREA, 3µ" FLASH GOLD ON TAIL
-G: 10µ" GOLD IN CONTACT AREA, 3µ" FLASH GOLD ON TAIL
-LM: 10µ" LIGHT SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
-FM: 3µ" FLASH SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL

PACKAGING (SEE NOTE 5)
BLANK: TUBES (SEE NOTE 11)
-TR: TAPE & REEL (SEE NOTES 12 & 13)
-FR: FULL REEL QTY TAPE & REEL (SEE NOTES 12 & 13)

PICK & PLACE OPTION
-P: PICK & PLACE PAD (USE PPP-30)
(USE PPP-30-NT FOR TAPE & REEL)
(SEE FIG 3, SHT 4; 6 POS MIN)

OPTIONS
-ES: SNAP ON END SHROUDS
(SEE FIG 2, SHT 2; 9 POS MIN)
MOLD TO POSITION END SHROUDS
(5 POS MIN; SEE FIG 2, SHT 2)
(SAMTEC DISCRETION ON WHICH END SHROUDS ARE USED FOR POSITIONS -09 AND GREATER)
-EP: GUIDE POST (SEE FIG 4, SHT 4; 9 POS MIN)
(USE ONLY WHEN MATING WITH A CLM)
-EC: LOCKING CLIP (SEE FIG 5, SHT 4)
(SEE NOTE 9; 9 POS MIN)
-A: ALIGNMENT PIN (SEE FIG 6 & 7, SHT 5)
(SAMTEC DISCRETION ON WHICH -A PIN IS USED)
(MOLDED: 3 POS MIN, USE FTMH-75-D-XX)
(STAKED: 7 POS MIN, USE FTMH-60-D)

ROW SPECIFICATION
-DV: DOUBLE ROW VERTICAL
(USE FTMH-75-D)






FIG 1
FTMH-125-03-X-DV SHOWN

NOTES:

1.  REPRESENTS CRITICAL DIMENSION.
2. MINIMUM PUSHOUT FORCE: 1.0 LB = 16 OZ.
3. MAXIMUM BURR: .003 [0.08]
4. MAXIMUM CUT FLASH: .010 [0.25]
5. POSITIONS -02 THRU -04 TO BE LAYER PACKAGED.
6. MEASURED AT BEND RADIUS.
7. SHEAR TAILS TO DIMENSION SHOWN.
8. FOR SELECTIVE PLATING OPTIONS, GOLD PLATING TO BE ON POST, TIN PLATING TO BE ON TAIL.
9. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -EC OPTION IS NOT COMPATIBLE WITH AUTO PLACEMENT. SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -EC OPTION.
10. NUMBER OF POSITIONS MAY BE AS HIGH AS -75 FOR SAMTEC MANUFACTURING ONLY.
11. TUBES ARE STANDARD PACKAGING.
12. ORDERS WILL BE PACKAGED ACCORDING TO THE SAMTEC PACKAGING EFFICIENCY STANDARDS (SPES) FOUND ON WWW.SAMTEC.COM.
13. ATTACH LABEL TO EACH REEL.



UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS ANGLES
.XX: ±.01[0.3]
.XXX: ±.005[0.13]
.XXXX: ±.0020[0.051]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL

DO NOT SCALE DRAWING

SHEET SCALE: 5:1

INSULATOR:
BLACK, LCP, UL-94-V-0
TERMINAL:
PHOSPHOR BRONZE

DESCRIPTION:
1mm x 1mm DOUBLE VERTICAL SMT TERMINAL STRIP

DWG. NO.

FTMH-1XX-XX-XX-DV-XX-X-XX

BY: PURVIS 04/22/96

SHEET 1 OF 6







FIG 2
-ES: END SHROUDS
FTMH-112-02-X-DV-ES SHOWN
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)


PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC. DO NOT SCALE DRAWING SHEET SCALE: 5:1	 520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322	
	DESCRIPTION: 1mm x 1mm DOUBLE VERTICAL SMT TERMINAL STRIP	
	DWG. NO. FTMH-1XX-XX-XX-DV-XX-X-XX	
	BY: PURVIS	04/22/96



FTMH-105-XX-XX-DV-ES SHOWN (BEFORE CUT)



FTMH-110-XX-XX-DV-ES SHOWN (BEFORE CUT)



FTMH-113-XX-XX-DV-ES SHOWN (BEFORE CUT)

• PROPRIETARY NOTE •
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 5:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
1mm x 1mm DOUBLE VERTICAL SMT TERMINAL STRIP

DWG. NO.
FTMH-1XX-XX-XX-DV-XX-X-XX

BY: PURVIS 04/22/96 SHEET 3 OF 6

NOTE
"M" = USED MEASURED DIMENSION (REF)
"P" = $(("M" - .200[5.08]) / 2) \pm .020[.51]$




FIG 3
-P: PICK & PLACE PAD
FTMH-125-03-X-DV-P SHOWN
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)

TABLE 3	
PAD	"B"
PPP-30	.125[3.18]
PPP-30-NT	.190[4.83]




FIG 4
-EP: GUIDE POST
FTMH-125-03-X-DV-EP SHOWN
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)






FIG 5
-EC: LOCKING CLIP
FTMH-125-03-X-DV-EC SHOWN
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)



PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING
SHEET SCALE: 5:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
1mm x 1mm DOUBLE VERTICAL SMT TERMINAL STRIP
DWG. NO.
FTMH-1XX-XX-XX-DV-XX-X-XX
BY: PURVIS 04/22/96 SHEET 4 OF 6




FIG 6
-A: ALIGNMENT PIN (STAKED)
(MIN 7 POSITIONS)
FTMH-125-03-X-DV-A SHOWN
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)









FIG 7
-A: ALIGNMENT PIN (MOLDED)
(MIN 3 POSITIONS)
FTMH-125-03-X-DV-A SHOWN
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)




-A OPTION
PT-1-24-01-60



-ES-P OPTION
PT-1-24-01-63



-EP, -EP-A & -EP-A-P OPTION
PT-1-24-02-15



-EC OPTION
PT-1-24-01-60

PACKAGING VIEWS

TABLE 2			
(SEE NOTE 5 FOR PACKAGING NOTES)			
LEAD STYLE	OPTION (S)	PACKAGING TUBE	TUBE PLUG
-02, -03	-NONE	PT-1-24-01-60	TP-03 (x 2)
-02, -03	-A	PT-1-24-01-60	TP-03 (x 2)
-02, -03	-P, -A-P	PT-1-24-01-60	TP-03 (x 2)
-02, -03	-ES, -ES-P, -ES-A	PT-1-24-01-63	TP-24 (x 2)
-02, -03	-EC, -EC-P, -EC-A	PT-1-24-01-60	TP-03 (x 2)
-02, -03	EP, -EP-A, -EP-A-P	PT-1-24-02-15	TP-03 (x 2)

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 5:1









520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
1mm x 1mm DOUBLE VERTICAL SMT TERMINAL STRIP

DWG. NO.
FTMH-1XX-XX-XX-DV-XX-X-XX

BY: PURVIS 04/22/96 SHEET 5 OF 6



• PROPRIETARY NOTE •
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

samtec
520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DO NOT SCALE DRAWING

SHEET SCALE: 5:1

DESCRIPTION:
1mm x 1mm DOUBLE VERTICAL SMT TERMINAL STRIP

DWG. NO.
FTMH-1XX-XX-XX-DV-XX-X-XX

BY: PURVIS 04/22/96 SHEET 6 OF 6

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[FTMH-107-03-F-DV-ES-TR](#) [FTMH-110-03-L-DV-ES-P-TR](#) [FTMH-106-02-L-DV-P](#) [FTMH-112-02-F-DV-A-P-TR](#)
[FTMH-106-03-F-DV-ES-A](#) [FTMH-104-03-L-DV-TR](#) [FTMH-120-02-F-DV-A-P-TR](#) [FTMH-106-03-F-DV](#) [FTMH-112-03-F-](#)
[DV-ES](#) [FTMH-115-02-FM-DV-A-P-TR](#) [FTMH-107-03-LM-DV-ES-A](#) [FTMH-106-03-F-DV-ES](#) [FTMH-105-02-L-DV-ES-](#)
[TR](#) [FTMH-107-02-L-DV-A-P-TR](#) [FTMH-105-02-F-DV-TR](#) [FTMH-110-02-L-DV-ES-A-TR](#) [FTMH-107-03-LM-DV-ES-A-P-](#)
[TR](#) [FTMH-120-03-F-DV-P-TR](#) [FTMH-110-02-L-DV-A-P-TR](#) [FTMH-120-03-F-DV-TR](#) [FTMH-105-03-L-DV-TR](#) [FTMH-](#)
[111-03-F-DV-P](#) [FTMH-106-03-F-DV-ES-A-P-TR](#) [FTMH-107-03-LM-DV-P-TR](#) [FTMH-110-03-L-DV-ES-A-P-TR](#) [FTMH-](#)
[107-02-L-DV-P](#) [FTMH-110-02-L-DV-ES-A-P-TR](#) [FTMH-112-02-L-DV-P](#) [FTMH-111-03-F-DV-P-TR](#) [FTMH-112-02-L-](#)
[DV-A-P-TR](#) [FTMH-105-03-F-DV-A](#) [FTMH-112-02-F-DV-A-P](#) [FTMH-120-03-F-DV-A-P-TR](#) [FTMH-103-02-F-DV-A](#)
[FTMH-106-03-F-DV-P-TR](#) [FTMH-107-03-L-DV-ES-A-P-TR](#) [FTMH-120-03-LM-DV-ES](#) [FTMH-115-02-F-DV-ES-A](#)
[FTMH-120-03-F-DV-ES-P-TR](#) [FTMH-128-03-F-DV](#) [FTMH-139-03-L-DV-ES](#) [FTMH-122-03-L-DV-EC](#) [FTMH-126-03-F-](#)
[DV-ES](#) [FTMH-126-03-L-DV](#) [FTMH-127-02-F-DV](#) [FTMH-132-02-F-DV-ES-P-TR](#) [FTMH-137-03-H-DV-EC-P-TR](#) [FTMH-](#)
[103-02-F-DV-A-TR](#) [FTMH-105-02-FM-DV](#) [FTMH-106-02-L-DV-ES-A](#) [FTMH-107-03-G-DV](#) [FTMH-107-03-LM-DV-ES](#)
[FTMH-106-03-L-DV-ES-P-TR](#) [FTMH-107-03-F-DV-ES](#) [FTMH-105-02-LM-DV](#) [FTMH-106-02-L-DV-ES](#) [FTMH-108-03-](#)
[F-DV-P-TR](#) [FTMH-109-02-L-DV-P-TR](#) [FTMH-104-02-L-DV-A-TR](#) [FTMH-106-03-FM-DV](#) [FTMH-107-03-L-DV-ES-P-TR](#)
[FTMH-111-02-L-DV-ES-A](#) [FTMH-112-02-F-DV-ES-A-P](#) [FTMH-112-03-F-DV-A](#) [FTMH-103-02-FM-DV-A](#) [FTMH-105-](#)
[02-L-DV-A-TR](#) [FTMH-109-02-L-DV](#) [FTMH-111-03-F-DV-ES](#) [FTMH-112-03-L-DV-EP](#) [FTMH-112-03-L-DV-ES-TR](#)
[FTMH-105-03-LM-DV-ES](#) [FTMH-107-02-F-DV-ES-A-P](#) [FTMH-108-02-L-DV-TR](#) [FTMH-110-03-LM-DV](#) [FTMH-112-02-](#)
[L-DV-EC](#) [FTMH-112-02-L-DV-ES-A](#) [FTMH-122-03-L-DV](#) [FTMH-125-02-L-DV-EP-A-P-TR](#) [FTMH-126-03-L-DV-ES](#)
[FTMH-130-03-L-DV-ES-A-P-TR](#) [FTMH-132-02-L-DV-EC-A](#) [FTMH-135-02-L-DV-EC-A](#) [FTMH-140-02-L-DV-ES-P-TR](#)
[FTMH-144-03-F-DV](#) [FTMH-150-02-L-DV-ES-P-TR](#) [FTMH-107-03-L-DV-P](#) [FTMH-110-03-L-DV-EC](#) [FTMH-110-03-LM-](#)
[DV-P-TR](#) [FTMH-111-03-L-DV-P](#) [FTMH-112-03-F-DV-ES-A](#) [FTMH-112-03-L-DV-A-P](#) [FTMH-115-02-L-DV-EC](#) [FTMH-](#)
[115-02-L-DV-ES-P-TR](#) [FTMH-115-03-F-DV-P-TR](#) [FTMH-120-02-F-DV-ES-P-TR](#) [FTMH-120-02-FM-DV-A-P](#) [FTMH-](#)
[120-02-L-DV-ES-P-TR](#) [FTMH-120-03-FM-DV-ES-P-TR](#) [FTMH-125-02-F-DV-A](#) [FTMH-130-03-F-DV-P](#)