

SACC-CIP-M12MS-8P SMD T - Contact carrier

1411945

<https://www.phoenixcontact.com/us/products/1411945>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 8-position, Pin, straight, M12, coding: A, PCB mounting, SMD reflow, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1238928

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Additional gasket for the device when not plugged in

Commercial data

Item number	1411945
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	AB23
Product key	ABQBGM
GTIN	4046356990714
Weight per piece (including packing)	4.468 g
Weight per piece (excluding packing)	4 g
Customs tariff number	85366990
Country of origin	DE

SACC-CIP-M12MS-8P SMD T - Contact carrier

1411945

<https://www.phoenixcontact.com/us/products/1411945>



Technical data

Product properties

Product type	Contact insert
Application	Signal
Number of positions	8
Seal present	yes
Shielded	no
Coding	A
Thread type	M12

Data management status

Article revision	02
------------------	----

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V
Nominal current I_N	2 A

Connection data

Connection method	SMD reflow
-------------------	------------

Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Coding	A

Mechanical properties

Mechanical data

SACC-CIP-M12MS-8P SMD T - Contact carrier

1411945

<https://www.phoenixcontact.com/us/products/1411945>



Insertion/withdrawal cycles

> 100

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 105 °C (Plug / socket)
	-55 °C ... 105 °C (without mechanical actuation)

Standards and regulations

M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101
Note	In line with

Mounting

Mounting type	PCB mounting
---------------	--------------

Packaging specifications

Type of packaging	Tray
Delivery state	with assembly pad

SACC-CIP-M12MS-8P SMD T - Contact carrier


1411945

<https://www.phoenixcontact.com/us/products/1411945>



Drawings

Schematic diagram



Pin assignment M12 plug, 8-pos., view plug side

SACC-CIP-M12MS-8P SMD T - Contact carrier

1411945

<https://www.phoenixcontact.com/us/products/1411945>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411945>

cULus Recognized				
Approval ID: E221474-20160506				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	30 V	2 A	-	-

SACC-CIP-M12MS-8P SMD T - Contact carrier

1411945

<https://www.phoenixcontact.com/us/products/1411945>



Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CIP-M12MS-8P SMD T - Contact carrier

1411945

<https://www.phoenixcontact.com/us/products/1411945>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a041a330-8cbb-4cda-abef-0df2521c8028

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com