

HC-STA-B06-HHFS-BLANK-EL-AL - Housing



1419901

<https://www.phoenixcontact.com/pc/products/1419901>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing B6, for single locking latch, material: Die-cast aluminum, salt water resistant, variable, height: 72 mm, cable gland: none, Standard, Without thread opening for screw connection

Product description

Sleeve housing, without screw thread

Your advantages

- Good shielding in the event of electromagnetic interference

Commercial data

Item number	1419901
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BF7APB
Catalog page	Page 600 (C-2-2019)
GTIN	4055626201252
Weight per piece (including packing)	185.3 g
Weight per piece (excluding packing)	185.3 g
Customs tariff number	85389099
Country of origin	CN

HC-STA-B06-HHFS-BLANK-EL-AL - Housing



1419901

<https://www.phoenixcontact.com/pc/products/1419901>

Technical data

Notes

General	For contact inserts HC-B6, BB10, DD24, M Tall housings for extra large wiring space
General	also available as a powder-coated or color version: 1372642 HC-STA-B06-HHFS-BLANK-EL/...


Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B6
Type	Tall design
Cable outlet	variable
Pg screw connection	none

Data management status

Article revision	01
------------------	----

Dimensions

Dimensional drawing	
Width	44 mm
Height	72 mm
Length	60 mm

Material specifications

Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated

Mechanical properties

Mechanical data

Locking type	Pin
--------------	-----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)

HC-STA-B06-HHFS-BLANK-EL-AL - Housing



1419901

<https://www.phoenixcontact.com/pc/products/1419901>

	12 (UL 50e)
Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C

HC-STA-B06-HHFS-BLANK-EL-AL - Housing


1419901

<https://www.phoenixcontact.com/pc/products/1419901>



Drawings

Dimensional drawing



Dimensional drawing

HC-STA-B06-HHFS-BLANK-EL-AL - Housing



1419901

<https://www.phoenixcontact.com/pc/products/1419901>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/pc/products/1419901>

DNV

Approval ID: TAE000037S



EAC

Approval ID: RU C-DE.AI30.B.01102



EAC

Approval ID: RU C-DE.BL08.B.00511

HC-STA-B06-HHFS-BLANK-EL-AL - Housing



1419901

<https://www.phoenixcontact.com/pc/products/1419901>

Classifications

ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

ETIM

ETIM 9.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

HC-STA-B06-HHFS-BLANK-EL-AL - Housing



1419901

<https://www.phoenixcontact.com/pc/products/1419901>

Accessories

US-EMLP (20X9) CUS - Plastic label

0830085

<https://www.phoenixcontact.com/pc/products/0830085>

Plastic label, Card, can be ordered: by card, white, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 75



HC-B06-HCWS-PLR-BK - Protective cover

1346525

<https://www.phoenixcontact.com/pc/products/1346525>

Protective cover B6, with single locking latch, protective cover material: PC, height: 26.3 mm, seal: yes



HC-STA-B06-HHFS-BLANK-EL-AL - Housing

1419901

<https://www.phoenixcontact.com/pc/products/1419901>



US-EMLP-HA (20X9) - Plastic label

0830989

<https://www.phoenixcontact.com/pc/products/0830989>



Plastic label, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, Number of individual labels: 70, text field height: 9 mm, text field width: 20 mm

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG

Flachsmarktstraße 8

D-32825 Blomberg

+49 (0) 5235-3 00

info@phoenixcontact.com