

PRODUCT NUMBER
77311-YXX-XXLF

PLATING SEE SHEET 2

PIN STYLE SEE SHEET 2

RoHS COMPATIBLE
SEE NOTE 6

TOTAL NB OF POSITIONS 01 TO 36

OPTION LETTER SEE SHEET 2

PRODUCT NUMBER (BERGSTRIK PACKAGING)
77311-YXX-00LF

PLATING

1= 0.76µm GOLD/GXT ON CONTACT
AREA, 2µm TIN MIN ON TAILS

8= 0.38µm GOLD/GXT ON CONTACT
AREA, 2µm TIN MIN ON TAILS



4= 2.0µm TIN MIN FULL PLATED

1.27µm NICKEL MIN UNDERLAYER FOR
ALL PLATING VERSIONS



INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 6

POSITIONS PER REEL : 00=36,000 (BERGSTRIK)

PIN STYLE	MATING	SOLDER	OAL
01	5.84	2.41	10.8
02	5.84	3.42	11.8
18	5.84	3.05	11.43
22	7.75	3.05	13.35
24	6.75	2.9	12.2
27	6.6	2.66	11.8



OPTIONAL PICK-UP CAP
(SEE NOTE 7)



NOTES:

- HOUSING MAT'L : HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: BLACK
- PIN MATERIAL : PHOSPHOR BRONZE
- BERGSTRIK PRODUCT PACKAGED IN POLYBAGS. BERGSTRIK PRODUCT PACKAGED PER REELS.
- 9N MIN RETENTION IN EITHER DIRECTION

- TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm

6. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.


b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.
- REFLOW COMPATIBLE


c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004



BERGSTRIK HEADER REEL PACKAGING DIMENSIONS

mat'l. code SEE NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family BERGSTIK									
ltr	ecn no	dr	date	tolerances unless otherwise specified						title									
CW	F-38159	DDE	20.08.26	angles	linear	.X ±0.3			scale 5:1	UNSHR.HEADER STR SR TMT									
CX	F-39392	DDE	20.12.18			.XX ±0.15													
						.XXX ±0.05													
CS	F-29484	DDE	18.03.08	dr	D.LE		01.01.24			dwg no		sheet 1 of 3		size					
CT	F-31328	LMU	18.09.20	engr	JM.C		01.01.24			77311				A3					
CU	F-33636	LMU	19.05.22	chr	JM.C		01.01.24												
CV	F-35304	LMU	19.11.04	appd	JF.N		01.01.24			type		CUSTOMER		Drawing					
sheet index	revision sheet	CX	BY	M															
		1	2	3															

OPTIONS : - = POLYBAG PACKAGING

T = TUBE PACKAGING WITHOUT PICK UP CAP

K = TAPE & REEL PACKAGING, WITHOUT PICK UP CAP
ONLY FOR P/N 77311-462K04(LF) AND 77311-462K05(LF)

A = TAPE & REEL PACKAGING, WITH PICK UP CAP. AS AVAILABLE

KC = TAPE & REEL PACKAGING WITHOUT PICK UP CAP AND WITH HIGH RETENTION FEATURES

KV = TAPE & REEL PACKAGING WITHOUT PICK UP CAP FOR CUSTOMER DEDICATED PART
ONLY FOR P/N 77311-462KV04LF

AV = TAPE & REEL PACKAGING WITH PICK UP CAP FOR CUSTOMER DEDICATED PART

C = HIGH RETENTION FEATURES, SEE SHEET 2

V = BLIBOX PACKAGING FOR CUSTOMER DEDICATED PART. ONLY FOR 77311-4BNV01LF

R = RETENTION FEATURES, SEE BELOW

IF RETENTION FEATURE "R" AND TUBE PACKAGING "T" ARE BOTH REQUIRED

OPTIONAL LETTER "R" WILL APPEAR INSTEAD OF THE FIRST DASH

EXAMPLE : 77311R424T03LF


RETENTION FEATURES :

- 1 - PART NUMBER 77311-XXXXXXLF: DIM "Z"=(0.99)
PART NUMBER 77311-XXXXCXXLF: DIM "Z"= 1.05MIN -1.15MAX
- 2 - PINS "A" AND "B" USED FOR RETENTION.
- 3 - DIRECTION OF RETENTION SHOWN BY ARROWS.
- 4 - ON 4 TO 36 POSITIONS HEADER; RETENTION IS IN MID POSITION OF HEADER (4 CENTRAL PINS)
- 5 - FOR RETENTION OPTION , SOLDER TAIL LENGTH TO BE 2.9 MIN UP TO 3.5 MAX.
- 6 - HOUSING MATERIAL FOR P/N 77311-4AJC03LF & 77311-TAJC03LF
HIGH TEMPERATURE THERMOPLASTIC UL94V-0 COLOR : NATURAL

PLATING SPECIFICATIONS :

- 7 - ONLY FOR PLATING 1XX, 8.0MM GOLD / GXT PLATING AREA
FROM PIN TYPE ON MATING SIDE

RETENTION FEATURES



PLATING :

- 1 = 0.76μm GOLD/GXT ON CONTACT AREA, 2μm TIN MIN ON TAIL
- 4 = 2μm TIN MIN FULL PLATED
- 5 = 0.25μm GOLD/GXT ON CONTACT AREA, 2μm TIN MIN ON TAIL
- 8 = 0.38μm GOLD/GXT ON CONTACT AREA, 2μm TIN MIN ON TAIL
- G = 0.76μm FULL GXT
- S = 0.38μm FULL GXT
- T = 2μm TIN MIN FULL PLATED INCLUDED PIN TYP
- 1.27μm NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS

mat'l. code				surface	tolerance	projection	product family		
				ISO 1302	ISO 406 ISO 1101		BERGSTIK		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title		
BU	B-20596	AMA	15.03.30	angles	linear	mm	UNSHR.HEADER		
BV	F-22085	LMU	15.10.05				STR SR TMT		
BW	F-22100	AMA	15.10.08			scale N/A			
BX	F-26241	LMU	17.03.01	dr	D.LE	01.01.24	dwg no		
BY	F-39392	DDE	20.12.18	engr	JM.C	01.01.24	sheet 2 of 3		
				chr	JM.C	01.01.24	size		
BT	B-20497	BVE	15.03.18	appd	JF.N	01.01.24	77311		
sheet	revision						type		
index	sheet						CUSTOMER Drawing		

[illegible]

NOTE 6

NOTE 7

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI / Amphenol:

[77311-101-07LF](#) [77311-101-31LF](#) [77311-102-13LF](#) [77311-102-18LF](#) [77311-102-19LF](#) [77311-102-23LF](#) [77311-102-28LF](#) [77311-102-29LF](#) [77311-102-30LF](#) [77311-102-31LF](#) [77311-102-33LF](#) [77311-102-34LF](#) [77311-102-35LF](#) [77311-111-02LF](#) [77311-119-13LF](#) [77311-122-11LF](#) [77311-122-15LF](#) [77311-122-19LF](#) [77311-122-21LF](#) [77311-122-23LF](#) [77311-122-25LF](#) [77311-122-26LF](#) [77311-122-27LF](#) [77311-122-28LF](#) [77311-122-29LF](#) [77311-122-30LF](#) [77311-122-31LF](#) [77311-122-32LF](#) [77311-122-33LF](#) [77311-122-34LF](#) [77311-122-35LF](#) [77311-124-11LF](#) [77311-124-19LF](#) [77311-124-22LF](#) [77311-124-23LF](#) [77311-124-25LF](#) [77311-124-27LF](#) [77311-124-28LF](#) [77311-124-29LF](#) [77311-124-30LF](#) [77311-124-31LF](#) [77311-124-33LF](#) [77311-124-34LF](#) [77311-124-35LF](#) [77311-127-11LF](#) [77311-127-12LF](#) [77311-127-17LF](#) [77311-127-22LF](#) [77311-127-23LF](#) [77311-127-25LF](#) [77311-127-26LF](#) [77311-127-27LF](#) [77311-127-28LF](#) [77311-127-29LF](#) [77311-127-30LF](#) [77311-127-31LF](#) [77311-127-33LF](#) [77311-127-34LF](#) [77311-127-35LF](#) [77311-402-36LF](#) [77311-422-04LF](#) [77311-422-05LF](#) [77311-424-10LF](#) [77311-801-09LF](#) [77311-801-11LF](#) [77311-801-13LF](#) [77311-801-14LF](#) [77311-801-15LF](#) [77311-801-16LF](#) [77311-801-18LF](#) [77311-801-20LF](#) [77311-801-21LF](#) [77311-801-22LF](#) [77311-801-28LF](#) [77311-801-29LF](#) [77311-801-31LF](#) [77311-801-33LF](#) [77311-801-34LF](#) [77311-801-35LF](#) [77311-802-15LF](#) [77311-802-17LF](#) [77311-802-19LF](#) [77311-802-21LF](#) [77311-802-23LF](#) [77311-802-24LF](#) [77311-802-25LF](#) [77311-802-26LF](#) [77311-802-27LF](#) [77311-802-28LF](#) [77311-802-29LF](#) [77311-802-30LF](#) [77311-802-31LF](#) [77311-802-32LF](#) [77311-802-33LF](#) [77311-802-34LF](#) [77311-802-35LF](#) [77311-818-09LF](#) [77311-818-12LF](#) [77311-818-13LF](#) [77311-818-15LF](#)