



Description: 2mm Dual Row Receptacle





04~20 pin : 0.10mm
22~50 pin : 0.20mm
52~80 pin : 0.30mm

Recommended P.C. Board Hole Layout



Units = mm

Tolerance
.X ±0.3
.XX ±0.20
.XXX ±0.100



Material:

Insulator: Nylon-6T, Black, UL 94V-O
Process Temperature: 260°C for 10 seconds
Contact: Phosphor Bronze
Gold Flash Mating Side
100μ" Tin on Board Side

Electrical:

Current Rating: 2 Amps
Contact Resistance: 20 mOhms Max.
Insulation Resistance: 5000 MOhms Min.
Working Voltage: 250V
Temperature: -40° C TO +105° C

2 5 6 4 Y Y 0 1 R P 2

Series

2564 = Dual Row

Position

Dual - Increments of 2
(04 to 80)

Type

01 = Straight

Plating Options

P2 = Gold Flash Mating Side, 100μ" Tin on Board Side



NorComp

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF NorComp AND
SHALL NOT BE REPRODUCED, COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OF SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

DRAWN:
PAM JENKINS

DATE:
1-30-06

SCALE:
NTS

SHEET
1

OF
1

REV
3

DWG NO.
2564YY01RP2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[25640401RP2](#) [25641001RP2](#) [25641201RP2](#) [25641401RP2](#) [25641601RP2](#) [25641801RP2](#) [25642001RP2](#)
[25642201RP2](#) [25642401RP2](#) [25643001RP2](#) [25645001RP2](#) [25647201RP2](#) [25644001RP2](#)