


PT07 SE (MS3124)

SP07 SE




jam nut receptacle



TERMINATION ASSEMBLIES
"SE" (SR), MS / "F" Strain Relief

"SE", MS / "E" Open Wire Seal

"SP", MS / "P" Potting Boot



PT07SE-XX-XXX
 SP07SE-XX-XXX
 MS3124E-XX-XXX

PT07SE-XX-XXX (SR)
 SP07SE-XX-XXX (SR)
 MS3124F-XX-XXX

PT07SP-XX-XXX
 SP07SP-XX-XXX
 MS3124P-XX-XXX

To complete part number see how to order on page 39.
 All lockwire holes are .044 Dia. Min.

Shell Size	Receptacle Front View		Receptacle Side View						
	H Hex Max.	S Max.	A Dia. +.001 -.005	J Flat +.000 -.010	K +.011 -.010	M ±.005	P Panel Thickness		R Thread Class 2A
							Min.	Max.	
8	.767	.954	.473	.530	.125	.696	.062	.125	.5625-24 UNEF
10	.892	1.078	.590	.655	.125	.696	.062	.125	.6875-24 NEF
12	1.079	1.266	.750	.818	.125	.696	.062	.125	.8750-20 UNEF
14	1.205	1.391	.875	.942	.125	.696	.062	.125	1.0000-20 UNEF
16	1.329	1.516	1.000	1.066	.125	.696	.062	.125	1.1250-18 NEF
18	1.455	1.641	1.125	1.191	.125	.696	.062	.125	1.2500-18 NEF
20	1.579	1.828	1.250	1.316	.156	.884	.062	.250	1.3750-18 NEF
22	1.705	1.954	1.375	1.441	.156	.884	.062	.250	1.5000-18 NEF
24	1.829	2.078	1.500	1.566	.156	.917	.062	.250	1.6250-18 NEF

Shell Size	Class "SE", MS / "E"		Class "SE" (SR), MS / "F"				Class "SP", MS / "P"		
	L Max.	N Max.	F Min.	G Dia. Free	L Max.	N Max.	G Dia.	L Max.	N Dia. Max.
8	1.438	.749	.234	.125	1.922	.828	—	—	—
10	1.438	.874	.297	.188	1.922	.891	.444	1.656	.734
12	1.438	.999	.422	.312	1.922	1.016	.558	1.656	.858
14	1.438	1.124	.547	.375	1.922	1.141	.683	1.656	.984
16	1.438	1.249	.609	.500	2.000	1.203	.808	1.656	1.110
18	1.438	1.374	.734	.625	2.000	1.469	.909	1.656	1.234
20	1.625	1.530	.734	.625	2.172	1.469	1.034	1.922	1.360
22	1.625	1.655	.922	.750	2.172	1.656	1.159	1.922	1.484
24	1.688	1.780	.984	.800	2.234	1.750	1.284	1.951	1.610

All dimensions for reference only.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[MS3124E14-18S](#) [MS3124E20-39S](#) [MS3124F10-6S](#) [MS3124E18-30S](#) [MS3124E18-32P\(LC\)](#) [MS3124E20-41S\(LC\)](#)
[MS3124E22-21P\(LC\)](#) [MS3124E22-21S\(LC\)](#) [MS3124E22-41P\(LC\)](#) [MS3124E22-41S\(LC\)](#) [MS3124E22-55S\(LC\)](#)
[MS3124F10-6P\(LC\)](#) [MS3124F12-10P\(LC\)](#) [MS3124F12-8P\(LC\)](#) [MS3124F14-12P](#) [MS3124F14-18P](#) [MS3124F14-18S](#)
[MS3124F16-26S\(LC\)](#) [MS3124F16-8S](#) [MS3124F20-16P](#) [MS3124F22-41P](#) [MS3124P10-6S](#) [MS3124P14-19P](#)
[MS3124P8-33P](#) [MS3124P8-33S](#) [MS3124E14-19PY](#) [MS3124E16-26PY](#) [MS3124E16-26PY-LC](#) [MS3124E16-26PZ](#)
[MS3124F14-15PY](#) [MS3124F22-55SW](#) [MS3124F22-55SX](#) [MS3124F22-55SZ](#) [MS3124E12-10PY](#) [MS3124E18-11SX](#)