

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1700711001](#)
Status: **Active**
Overview: [High-Speed Pluggable I/O Solutions](#)
Description: zSFP+ Stacked Ganged Assembly with Elastomeric Gasket, 2-by-1 No Light Pipes, 40 Circuits


Documents:
[3D Model](#) [Product Specification TS-170071-0001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [Application Specification AS-170071-0002-001 \(PDF\)](#)
[Product Specification PS-170071-0001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
UL E29179

General
Product Family I/O Connectors
Series [170071](#)
Application Module-to-Board
Component Type Receptacle
Electrical Model Yes
Overview [High-Speed Pluggable I/O Solutions](#)
Product Name zSFP Plus, zSFP+
Type N/A
UPC 884982401891

Physical
Circuits (Loaded) 40
Color - Resin Black
Durability (mating cycles max) 100
Flammability 94V-0
Gender Female
Lock to Mating Part Yes
Material - Metal High Performance Alloy (HPA)
Material - Plating Mating Gold
Material - Plating Termination Matte Tin
Material - Resin High Temperature Thermoplastic
Net Weight 24.271/g
Number of Rows 2
Orientation Right Angle
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 2.36mm
Packaging Type Tray
Panel Mount No
Pitch - Mating Interface 0.80mm
Pitch - Termination Interface 0.80mm
Plating min - Mating 0.762µm
Plating min - Termination 0.762µm
Polarized to Mating Part Yes
Polarized to PCB Yes
Ports 2
Surface Mount Compatible (SMC) No
Temperature Range - Operating -40° to +85°C
Termination Interface: Style Through Hole - Compliant Pin

Electrical
Current - Maximum per Contact 0.5A



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
ED/30/2017 (7 July
2017)
Halogen-Free
Status
Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
[170071](#) Series

Shield Type	N/A
Shielded	Yes
Voltage - Maximum	30V AC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-170071-0002-001
Electrical Model Document	EE-170071-0001
Product Specification	PS-170071-0001, TS-170071-0001-001
S-Parameter Model	SP-170426-1000
Sales Drawing	SD-170071-0001

This document was generated on 08/22/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION