



10		9		
CKTS	DIM A	DIM B	DIM C	
4	5.08	2.54	NA	0.10
6	7.62	5.08	2.54	0.10
8	10.16	7.62	5.08	0.10
10	12.70	10.16	7.62	0.10
12	15.24	12.70	10.16	0.10
14	17.78	15.24	12.70	0.10
16	20.32	17.78	15.24	0.10
18	22.86	20.32	17.78	0.10
20	25.40	22.86	20.32	0.10
22	27.94	25.40	22.86	0.15
24	30.48	27.94	25.40	0.15
26	33.02	30.48	27.94	0.15
28	35.56	33.02	30.48	0.15
30	38.10	35.56	33.02	0.15
32	40.64	38.10	35.56	0.15
34	43.18	40.64	38.10	0.15
36	45.72	43.18	40.64	0.15
38	48.26	45.72	43.18	0.15
40	50.80	48.26	45.72	0.15
42	53.34	50.80	48.26	0.23
44	55.88	53.34	50.80	0.23
46	58.42	55.88	53.34	0.23
48	60.96	58.42	55.88	0.23
50	63.50	60.96	58.42	0.23
52	66.04	63.50	60.96	0.23
54	68.58	66.04	63.50	0.23
56	71.12	68.58	66.04	0.23
58	73.66	71.12	68.58	0.23
60	76.20	73.66	71.12	0.23
62	78.74	76.20	73.66	0.30
64	81.28	78.74	76.20	0.30
66	83.82	81.28	78.74	0.30
68	86.36	83.82	81.28	0.30
70	88.90	86.36	83.82	0.30
72	91.44	88.90	86.36	0.30
74	93.98	91.44	88.90	0.30
76	96.52	93.98	91.44	0.30
78	99.06	96.52	93.98	0.30
80	101.60	99.06	96.52	0.30
90	114.30	111.76	109.22	0.38
100	127.00	124.46	122.06	0.38



SOLDER PAD —
FOR CKTS
WITHOUT PEGS


- NOTES:
1. HOUSING MATERIAL: LCP, UL 94V-0 COLOR: BLACK
PIN MATERIAL: COPPER ALLOY
 2. FINISH:
124 = BRIGHT TIN: 3.81 MICROMETERS MIN OVER MATTE NICKEL
207 = SELECT GOLD: 0.38 MICROMETERS MIN IN CONTACT AREA
SELECT BRIGHT TIN: 2.0 MICROMETERS MIN IN SMT TAIL
BOTH OVER NICKEL.
206 = SELECT GOLD: 0.75 MICROMETERS MIN IN CONTACT AREA
SELECT BRIGHT TIN: 2.0 MICROMETERS MIN IN SMT TAIL
BOTH OVER NICKEL.
197 = REFLOW MATTE TIN: 1.52 MICROMETERS MIN OVER MATTE NICKEL
222 = MATTE TIN: 2.54 MICROMETERS MIN OVER MATTE NICKEL
118 = BRIGHT TIN: 1.52 MICROMETERS MIN OVER NICKEL
 3. PRODUCT SPECIFICATION: PS-71308
 4. PACKAGING SPECIFICATION: SEE CHART
 5. COSMETIC SPECIFICATION: PS-45499-002 CLASS B
 6. SOLDERABILITY SPECIFICATION: SMES-152

DRAWING SHEET INDEX		
SHEET NO	PEG STYLE	DIM M MATING HEIGHT
2	NONE	6.10
3	NONE	6.10
4	NONE	8.13
5	LONG	6.10
6	LONG	8.13
7	SHORT	6.10
8	SHORT	8.13
9	PARTS WITH VOIDS	

CGRID HEADER ASSY VERTICAL DUAL ROW SM

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
713080000-SD	PSD	000	A
MATERIAL NUMBER	CUSTOMER	SHEET NUMBER	
		1 OF 10	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex		
mm		3:1							
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 743966 DRWN: DANUSA 2022/10/27 CHK'D: SUAIFR 2023/03/31 APPR: MRAMAKRISHNA 2023/03/31			CGRID HEADER ASSY VERTICAL DUAL ROW SMT		
ANGULAR TOL ± °									
4 PLACES		±							
3 PLACES		±		INITIAL REVISION: DRWN: KSAMIEC 2017/09/07 APPR: FSMITH 2018/07/03			PRODUCT CUSTOMER DRAWING		
2 PLACES		± 0.13							
1 PLACE		± 0.25							
0 PLACES		± 0.0		DOCUMENT NUMBER 713080000-SD			DOC TYPE	DOC PART	REVISION
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							THIRD ANGLE PROJECTION	DRAWING	SERIES
				B-SIZE	71308				1 OF 10



10	9	8	7	6	5	4	3	2	1
PLATING:	124 - BRIGHT TIN	124 - BRIGHT TIN	124 - BRIGHT TIN	207 - 0.38 SGOLD	207 - 0.38 SGOLD	207 - 0.38 SGOLD	206 - 0.76 SGOLD	206 - 0.76 SGOLD	206 - 0.76 SGOLD
PACKAGING:	TUBE 713080001-PK	TUBE 713080002-PK	T&R 713080000-PK STYLE A	TUBE 713080001-PK	TUBE 713080002-PK	T&R 713080000-PK STYLE A	TUBE 713080001-PK	TUBE 713080002-PK	T&R 713080000-PK STYLE A
PICK AND PLACE CAPS	NO	YES	YES	NO	YES	YES	NO	YES	YES
CKTS:	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO
4	015-91-2040	NA	015-91-6040	015-91-0040	NA	015-91-6042	015-91-3040	NA	015-91-6043
6	015-91-2060 / 71308-9060	NA	015-91-6060	015-91-0060	NA	015-91-6062	015-91-3060 / 71308-9061	NA	015-91-6063
8	015-91-2080 / 71308-9080	015-91-3087	015-91-6080	015-91-0080	015-91-3086	015-91-6082	015-91-3080	015-91-3088	015-91-6083
10	015-91-2100	015-91-3107	015-91-6100	015-91-0100	015-91-3106	015-91-6102	015-91-3100 / 71308-3110	015-91-3108	015-91-6103
12	015-91-2120	015-91-3127	015-91-6120	015-91-0120	015-91-3126	015-91-6122	015-91-3120	015-91-3128	015-91-6123
14	015-91-2140	015-91-3147	015-91-6140	015-91-0140 / 71308-9140	015-91-3146	015-91-6142	015-91-3140	015-91-3148	015-91-6143
16	015-91-2160	015-91-3167	015-91-6160	015-91-0160	015-91-3166	015-91-6162	015-91-3160	015-91-3168	015-91-6163
18	015-91-2180	015-91-3187		015-91-0180	015-91-3186		015-91-3180	015-91-3188	
20	015-91-2200	015-91-3207	015-91-6200	015-91-0200 / 71308-9200	015-91-3206	015-91-6202	015-91-3200	015-91-3208	015-91-6203
22	015-91-2220	015-91-3227		015-91-0220	015-91-3226		015-91-3220	015-91-3228	
24	015-91-2240	015-91-3247	71308-2240	015-91-0240	015-91-3246		015-91-3240	015-91-3248	
26	015-91-2260	015-91-3267	015-91-6260	015-91-0260	015-91-3266	015-91-6262	015-91-3260	015-91-3268	
28	015-91-2280	015-91-3287		015-91-0280	015-91-3286		015-91-3280	015-91-3288	
30	015-91-2300	015-91-3307		015-91-0300	015-91-3306		015-91-3300	015-91-3308	
32	015-91-2320	015-91-3327		015-91-0320	015-91-3326		015-91-3320	015-91-3328	
34	015-91-2340	015-91-3347		015-91-0340	015-91-3346		015-91-3340	015-91-3348	
36	015-91-2360	015-91-3367		015-91-0360	015-91-3366		015-91-3360	015-91-3368	
38	015-91-2380	015-91-3387		015-91-0380	015-91-3386		015-91-3380	015-91-3388	
40	015-91-2400	015-91-3407	015-91-6400	015-91-0400	015-91-3406	015-91-6402	015-91-3400	015-91-3408	015-91-6403
42	015-91-2420	015-91-3427		015-91-0420	015-91-3426		015-91-3420	015-91-3428	
44	015-91-2440	015-91-3447		015-91-0440	015-91-3446		015-91-3440	015-91-3448	
46	015-91-2460	015-91-3467		015-91-0460	71308-0546		015-91-3460	015-91-3468	
48	015-91-2480	015-91-3487		015-91-0480	015-91-3486		015-91-3480	015-91-3488	
50	015-91-2500	015-91-3507	015-91-6500	015-91-0500	015-91-3506	015-91-6502	015-91-3500	015-91-3508	015-91-6503
52	015-91-2520	015-91-3527		015-91-0520	015-91-3526		015-91-3520	015-91-3528	
54	015-91-2540	015-91-3547		015-91-0540	015-91-3546		015-91-3540	015-91-3548	
56	015-91-2560	015-91-3567		015-91-0560	015-91-3566		015-91-3560	015-91-3568	
58	015-91-2580	015-91-3587		015-91-0580	015-91-3586		015-91-3580	015-91-3588	
60	015-91-2600	015-91-3607		015-91-0600	015-91-3606		015-91-3600	015-91-3608	
62	015-91-2620	015-91-3627		015-91-0620	015-91-3626		015-91-3620	015-91-3628	
64	015-91-2640	015-91-3647		015-91-0640	015-91-3646		015-91-3640	015-91-3648	
66	015-91-2660	015-91-3667		015-91-0660	015-91-3666		015-91-3660	015-91-3668	
68	015-91-2680	015-91-3687		015-91-0680	015-91-3686		015-91-3680	015-91-3688	
70	015-91-2700	015-91-3707		015-91-0700	015-91-3706		015-91-3700	015-91-3708	
72	015-91-2720	015-91-3727		015-91-0720	015-91-3726		015-91-3720	015-91-3728	
74	015-91-2740	015-91-3747		015-91-0740	015-91-3746		015-91-3740	015-91-3748	
76	015-91-2760	015-91-3767		015-91-0760	015-91-3766		015-91-3760	015-91-3768	
78	015-91-2780	015-91-3787		015-91-0780	015-91-3786		015-91-3780	015-91-3788	
80	015-91-2800	015-91-3807		015-91-0800	015-91-3806		015-91-3800	015-91-3808	
90				71308-0190					
100	71308-0101	71308-0500		71308-0200	71308-0600		71308-0300	71308-0700	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

1:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ± °

4 PLACES ±

3 PLACES ±

2 PLACES ± 0.13

1 PLACE ± 0.25

0 PLACES ± 0.0

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

DRAWING

B-SIZE

SERIES

71308

CURRENT REV DESC:

EC NO: 743966
DRWN: DANUSA 2022/10/27
CHK'D: SUAIFR 2023/03/31
APPR: MRAMAKRISHNA 2023/03/31

INITIAL REVISION:
DRWN: KSAMIEC 2017/09/07
APPR: FSMITH 2018/07/03

DOCUMENT NUMBER

713080000-SD

DOC TYPE

PSD

DOC PART

000

REVISION

A9

PRODUCT CUSTOMER DRAWING

MATERIAL NUMBER

CUSTOMER

SHEET NUMBER

3 OF 10

6.10

NO PEGS

DOCUMENT STATUS

P1

RELEASE DATE

2023/03/31

07:34:54

9

8

7

6

5

4

3

2


1

10		9		8		7		6		5		4		3		2		1		
F	PLATING:	124 - BRIGHT TIN		124 - BRIGHT TIN		197 - REFLOW TIN		197 - REFLOW TIN		207 - 0.38 SGOLD		207 - 0.38 SGOLD		206 - 0.76 SGOLD		118 - BRIGHT TIN		118 - BRIGHT TIN		
	PACKAGING:	TUBE 713080003-PK		T&R 713080000-PK STYLE B		TUBE 713080003-PK		T&R 713080000-PK STYLE B		TUBE 713080003-PK		T&R 713080000-PK STYLE B		TUBE 713080003-PK		T&R 713080000-PK STYLE B		TUBE 713080003-PK		
	PICK AND PLACE CAPS	NO		YES		NO		YES		NO		YES		NO		YES		NO		
	CKTS:	MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO
	4	71308-8004								015-91-0048				015-91-5049						
	6	71308-8006								015-91-0068				015-91-5069						
	8	71308-8008								015-91-0088		71308-6908		015-91-5089						
	10	71308-8010								015-91-0108				015-91-5109				71308-5810		
	12	71308-8012								015-91-0128				015-91-5129						
	14	71308-8014								015-91-0148				015-91-5149						
	16	71308-8016				71308-8017		71308-0015		015-91-0168				015-91-5169				71308-5816		
	18	71308-8018								015-91-0188				015-91-5189						
	20	71308-8020								015-91-0208				015-91-5209						
	22	71308-8022								015-91-0228				015-91-5229						
	24	71308-8024		71308-8124						015-91-0248				015-91-5249		71308-5724		71308-5824		
	26	71308-8026								015-91-0268				015-91-5269						
	28	71308-8028								015-91-0288				015-91-5289						
	30	71308-8030								015-91-0308				015-91-5309						
	32	71308-8032																		
	34	71308-8034								015-91-0348				015-91-5349						
	36	71308-8036								015-91-0368				015-91-5369						
	38	71308-8038								015-91-0388				015-91-5389						
	40	71308-8040								015-91-0408				015-91-5409						
	42	71308-8042								015-91-0428				015-91-5429						
	44	71308-8044								015-91-0448				015-91-5449						
	46	71308-8046								015-91-0468				015-91-5469						
	48	71308-8048								015-91-0488				015-91-5489						
	50	71308-8050								015-91-0508				015-91-5509						
	52	71308-8052								015-91-0528				015-91-5529						
	54	71308-8054								015-91-0548				015-91-5549						
	56	71308-8056								015-91-0568				015-91-5569						
	58	71308-8058								015-91-0588				015-91-5589						
	60	71308-8060								015-91-0608				015-91-5609						
	62	71308-8062								015-91-0628				015-91-5629						
	64	71308-8064								015-91-0648				015-91-5649						
	66	71308-8066								015-91-0668				015-91-5669						
	68	71308-8068								015-91-0688				015-91-5689						
	70	71308-8070								015-91-0708				015-91-5709						
	72	71308-8072								015-91-0728				015-91-5729						
	74	71308-8074								015-91-0748				015-91-5749						
	76	71308-8076								015-91-0768				015-91-5769						
	78	71308-8078								015-91-0788				015-91-5789						
	80	71308-8080								015-91-0808				015-91-5809						
	100									71308-1200				71308-1300						


10		9		8		7		6		5		4		3		2		1	
PLATING:		124 - BRIGHT TIN		207 - 0.38 SGOLD		206 - 0.76 SGOLD		124 - BRIGHT TIN		207 - 0.38 GOLD		206 - 0.76 GOLD		118 - BRIGHT TIN		118 - BRIGHT TIN			
PACKAGING:		TUBE 713080001-PK		TUBE 713080001-PK		TUBE 713080001-PK		T&R 713080000-PK STYLE C		T&R 713080000-PK STYLE C		T&R 713080000-PK STYLE C		TUBE 713080001-PK		T&R 713080000-PK STYLE C			
PICK AND PLACE CAPS		NO		NO		NO		YES		YES		YES		NO		YES			
CKTS:		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO			
4		015-91-1041		015-91-1042		015-91-1043		015-91-6044		015-91-6045		015-91-6046		71308-6404		71308-6504			
6		015-91-1061		015-91-1062		015-91-1063		015-91-6064		015-91-6065		015-91-6066		71308-6406		71308-6506			
8		015-91-1081		015-91-1082		015-91-1083		015-91-6084		015-91-6085		015-91-6086		71308-6408		71308-6508			
10		015-91-1101		015-91-1102 / 71308-1102		015-91-1103		015-91-6104		015-91-6105		015-91-6106		71308-6410		71308-6510			
12		015-91-1121		015-91-1122		015-91-1123								71308-6412					
14		015-91-1141		015-91-1142		015-91-1143		015-91-6144		015-91-6145		015-91-6146		71308-6414		71308-6514			
16		015-91-1161		015-91-1162		015-91-1163		015-91-6164		015-91-6165		015-91-6166		71308-6416		71308-6516			
18		015-91-1181		015-91-1182		015-91-1183								71308-6418					
20		015-91-1201		015-91-1202		015-91-1203								71308-6420					
22		015-91-1221		015-91-1222		015-91-1223								71308-6422					
24		015-91-1241		015-91-1242		015-91-1243		71308-6901						71308-6424					
26		015-91-1261		015-91-1262		015-91-1263								71308-6426					
28		015-91-1281		015-91-1282		015-91-1283								71308-6428					
30		015-91-1301		015-91-1302		015-91-1303								71308-6430					
32		015-91-1321		015-91-1322		015-91-1323								71308-6432					
34		015-91-1341		015-91-1342		015-91-1343								71308-6434					
36		015-91-1361		015-91-1362		015-91-1363								71308-6436					
38		015-91-1381		015-91-1382		015-91-1383								71308-6438					
40		015-91-1401		015-91-1402		015-91-1403								71308-6440					
42		015-91-1421		015-91-1422		015-91-1423								71308-6442					
44		015-91-1441		015-91-1442		015-91-1443								71308-6444					
46		015-91-1461		015-91-1462		015-91-1463								71308-6446					
48		015-91-1481		015-91-1482		015-91-1483								71308-6448					
50		015-91-1501		015-91-1502		015-91-1503						015-91-6506		71308-6450					
52		015-91-1521		015-91-1522		015-91-1523						71308-5203		71308-6452					
54		015-91-1541		015-91-1542		015-91-1543								71308-6454					
56		015-91-1561		015-91-1562		015-91-1563								71308-6456					
58		015-91-1581		015-91-1582		015-91-1583								71308-6458					
60		015-91-1601		015-91-1602		015-91-1603								71308-6460					
62		015-91-1621		015-91-1622		015-91-1623								71308-6462					
64		015-91-1641		015-91-1642		015-91-1643								71308-6464					
66		015-91-1661		015-91-1662		015-91-1663								71308-6466					
68		015-91-1681		015-91-1682		015-91-1683								71308-6468					
70		015-91-1701		015-91-1702		015-91-1703								71308-6470					
72		015-91-1721		015-91-1722		015-91-1723								71308-6472					
74		015-91-1741		015-91-1742		015-91-1743								71308-6474					
76		015-91-1761		015-91-1762		015-91-1763								71308-6476					
78		015-91-1781		015-91-1782		015-91-1783								71308-6478					
80		015-91-1801		015-91-1802		015-91-1803								71308-6480					
100		71308-4100		71308-4200		71308-4300													

[illegible]

10	9	8	7	6	5	4	3	2	1
PLATING:	124 - BRIGHT TIN	124 - BRIGHT TIN	206 - 0.76 SGOLD	206 - 0.76 SGOLD	118 - BRIGHT TIN	118 - BRIGHT TIN			
PACKAGING:	TUBE 713080001-PK	T&R 713080000-PK STYLE C	TUBE 713080001-PK	T&R 713080000-PK STYLE C	TUBE 713080001-PK	T&R 713080000-PK STYLE C			
PICK AND PLACE CAPS	NO	YES	NO	YES	NO	YES			
CKTS:	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	
4			015-91-1048	015-91-6047					
6	71308-6106	71308-6206	015-91-1068	015-91-6067	71308-6706	71308-6806			
8	71308-6108	71308-6208	015-91-1088	015-91-6087	71308-6708	71308-6808			
10	71308-6110	71308-6210	015-91-1108	015-91-6107	71308-6710	71308-6810			
12			015-91-1128						
14			015-91-1148	015-91-6147					
16			015-91-1168	015-91-6167					
18			015-91-1188						
20			015-91-1208	015-91-6207					
22			015-91-1228						
24			015-91-1248						
26	71308-6126		015-91-1268		71308-6726				
28			015-91-1288						
30			015-91-1308						
32			015-91-1328						
34			015-91-1348						
36			015-91-1368						
38			015-91-1388						
40			015-91-1408						
42			015-91-1428						
44			015-91-1448						
46			015-91-1468						
48			015-91-1488						
50			015-91-1508	015-91-6507					
52			015-91-1528						
54			015-91-1548						
56			015-91-1568						
58			015-91-1588						
60			015-91-1608						
62			015-91-1628						
64			015-91-1648						
66			015-91-1668						
68			015-91-1688						
70			015-91-1708						
72			015-91-1728						
74			015-91-1748						
76			015-91-1768						
78			015-91-1788						
80			015-91-1808						
100			71308-6100						



PARTS ON THIS SHEET HAVE
SHORT PEGS WITH
A MATING HEIGHT OF 6.10


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex							
mm		1:1													
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 743966 DRWN: DANUSA 2022/10/27 CHK'D: SUAIFR 2023/03/31 APPR: MRAMAKRISHNA 2023/03/31				CGRID HEADER ASSY VERTICAL DUAL ROW SMT							
ANGULAR TOL ± °															
4 PLACES		±													
3 PLACES		±		INITIAL REVISION: DRWN: KSAMIEC 2017/09/07 APPR: FSMITH 2018/07/03				DOCUMENT NUMBER 713080000-SD		DOC TYPE PSD	DOC PART 000	REVISION A9			
2 PLACES		± 0.13													
1 PLACE		± 0.25													
0 PLACES		± 0.0													
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION 		DRAWING B-SIZE		SERIES 71308		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER 8 OF 10	


10	9	8	7	6	5	4	3	2	1
PLATING:	197 - REFLOW TIN	197 - REFLOW TIN	197 - REFLOW TIN						
PACKAGING:	T&R 713080000-PK STYLE D	TUBE 713080004-PK	TUBE 713080003-PK						
PICK AND PLACE CAPS	YES	YES	NO						
CKTS:	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO		
4									
6									
8	71308-8409	71308-8408	71308-8508						
10									
12									
14									
16									
18									
20	71308-8421	71308-8420	71308-8520						
22									
24									
26	71308-8426								
28									
30									
32									
34									
36									
38									
40									
42									
44									
46									
48									
50									
52									
54									
56									
58									
60									
62									
64									
66									
68									
70									
72									
74									
76									
78									
80									

PARTS ON THIS SHEET HAVE
SHORT PEGS WITH
A MATING HEIGHT OF 8.13

8.13


1.40



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex							
mm		1:1													
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 743966 DRWN: DANUSA 2022/10/27 CHK'D: SUAIFR 2023/03/31 APPR: MRAMAKRISHNA 2023/03/31 INITIAL REVISION: DRWN: KSAMIEC 2017/09/07 APPR: FSMITH 2018/07/03				CGRID HEADER ASSY VERTICAL DUAL ROW SMT							
ANGULAR TOL		± °													
4 PLACES		±													
3 PLACES		±													
2 PLACES		± 0.13													
1 PLACE		± 0.25		DOCUMENT NUMBER				713080000-SD		DOC TYPE		DOC PART		REVISION	
0 PLACES		± 0.0													
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						B-SIZE		71308						9 OF 10	

DOCUMENT STATUS	P1	RELEASE DATE	2023/03/31	07:34:54				
9	8	7	6	5	4	3	2	1

MATERIAL NO	MADE FROM	NO OF CKTS	VOID LOCATION	PICK AND PLACE CAP	PACKAGING
71308-9210	71308-0010	10	A5	711331000	713080002-PK
71308-9010	71308-0110	10	A2	711331000	713080002-PK
71308-9032	71308-0132	32	A9	711331000	713080002-PK
71308-9110	71308-0110	10	A5	711331000	713080002-PK
71308-9014	71308-0140	14	B5	711331000	713080002-PK
71308-9310	71308-0110	10	B5	711331000	713080002-PK
71308-9311	71308-0110	10	B5	711331000	713080000-PK STYLE A
71308-9312	71308-1504	04	A1	711331000	713080000-PK STYLE A



CIRCUIT IDENTIFICATION FOR VOIDED CKT ONLY

DOCUMENT STATUS	P1	RELEASE DATE	2023/03/31	07:34:54
-----------------	----	--------------	------------	----------

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex			
mm		5:1									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
ANGULAR TOL ± °								EC NO: 743966 DRWN: DANUSA			