



Assembly instruction see N 22 091 0023

Number of contacts	Standard	3	4	5	5	6	7	7	8	12	14	14	19	
Contact arrangement	IEC 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a	14-b	19-a	
Rated voltage	IEC 60664-1	150 V	100 V	32 V	100 V	32 V								
Rated impulse withstand voltage	IEC 60664-1	1500 V	800 V	1500 V	800 V									
Pollution degree	IEC 60664-1	3 ¹⁾												
Installation category	IEC 60664-1	I												
Insulation group	IEC 60664-1	II, 400 ≤ CTI < 600												
Current rating	IEC 60512-5-2 UL 1977	10A/+40°C	7A/+40°C						3A/+40°C					
Insulation resistance	IEC 60512-3-1	>10 ¹⁰ Ohm ²⁾												
Contact resistance	IEC 60512-2-1	<5mOhm												
Climatic category	IEC 60668-1	40 / 100 / 21												
Temperatur range	IEC 60668-1	-40°C...+100°C / -40°F...+212°F												
Salt spray resistance	DIN IEC 60068-2-11, test Ka	720h												
IP degree	IEC 60529	IP69K / IP 68 (in mated condition)												
Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N	35N	50N	55N	55N	60N	50N	50N	50N	60N	
mechanical operation	IEC 60512-9-1	Silver ≥500 mating cycles / Gold ≥1000 mating cycles												
housing material		brass and / or zinc die cast, nickel plated												
dielectric material		thermoplastic												
sealing material		Chloroprene												
contacts		silver or gold plated												
termination technique		solder												
wire gauge		≤0,5mm ² / 20 AWG						≤0,35mm ² / 22 AWG						
flamability		UL 94 V0												
locking system	DIN EN 61076-2-106	metal screw coupling, tightening torque 0,7 - 1,5 Nm												

¹⁾ designed according pollution degree 2, can be used under pollution degree 3 if the rules according IEC 60664-1 are fulfilled
²⁾ under operating conditions >10⁸ Ohm
 Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground.
 Remark for gold plated contacts:
 In order to avoid brittle inter-metallic connections, gold plated terminals have to be tin-plated in the solder area.
 All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guaranties ("Beschaffungsgarantie" or "Haltbarkeitsgarantie").

	149 (19-a)	C091 31H019 102 4 U	C091 31H019 202 4 U
	14 (14-b)	C091 31H114 102 4 U	C091 31H114 202 4 U
	14 (14-a)	C091 31H014 102 4 U	C091 31H014 202 4 U
	12 (12-a)	C091 31H012 102 4 U	C091 31H012 202 4 U
	8 (08-a)	C091 31H008 102 4 U	C091 31H008 202 4 U
	7 (07-b)	C091 31H107 102 4 U	C091 31H107 202 4 U
	7 (07-a)	C091 31H007 102 4 U	C091 31H007 202 4 U
	6 (06-a)	C091 31H006 102 4 U	C091 31H006 202 4 U
	5 (05-b)	C091 31H105 102 4 U	C091 31H105 202 4 U
	5 (05-a)	C091 31H005 102 4 U	C091 31H005 202 4 U
	4 (04-a)	C091 31H004 102 4 U	C091 31H004 202 4 U
	3 (03-a)	C091 31H003 102 4 U	C091 31H003 202 4 U
Contact arrangement View on mating side	Number of contacts (Contact arrangement acc. IEC 61076-2-106)	Part number with silver plated contacts	Part number with gold plated contacts

Gewicht (errechnet) / Calc WT: 0,05 kg		Zul. Abw./Tolerances:		Maßstab / Scale: 2:1		A3			
Prüfmaß / Testdimension		ISO 2768-c		CUSTOMER DRAWING					
Teileindex / Partindexnumber:		DIN / ISO 13715							
Bagatelle change:		Gez. 26.05.2020		Male cable connector for cable diameter 8-10,5 mm					
		Drawn MCARLE							
		Status Released							
		Gepr. 11.01.2021		M C091 31HXXX X02 4 U					
		Checked MBERTSCH							
		Amphenol Tuchel Industrial GmbH		Blatt / Sheet 1		Ers. f. / Replacement for: M-C0901 31HXXX X02 4 U Rev02			
03 202000083		26.10.2020 MCARLE		1 Bl.					
Index	Änderung / Description	Datum / Date	Name						

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadensersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.

FAI2020-001734
NXM-V02