




# PT07 (MS3114) SP07 jam nut receptacle




"A" General Duty/  
"C" Pressurized Receptacle  
PT07A-XX-XXX  
PT07C-XX-XXX

"E" Open Wire Seal




PT07E-XX-XXX  
SP07E-XX-XXX  
MS3114E-XX-XXX

TERMINATION ASSEMBLIES  
"A" (SR), "E" (SR), "P" (SR), MS / "F" Strain Relief



PT07A-XX-XXX (SR)  
SP07A-XX-XXX (SR)  
PT07E-XX-XXX (SR)  
MS3114F-XX-XXX

"P" Potting Boot



PT07P-XX-XXX  
MS3114P-XX-XXX

To complete part number see how to order on page 25.

| Shell<br>Size | Recept. Front View |       | Receptacle Side View     |                          |                     |      |                   |      |                              |      | Class "E", MS / "E" |      |           |            |
|---------------|--------------------|-------|--------------------------|--------------------------|---------------------|------|-------------------|------|------------------------------|------|---------------------|------|-----------|------------|
|               | H<br>±.016         | S     | A Dia.<br>+.001<br>−.005 | J Flat<br>+.000<br>−.010 | K<br>+.011<br>−.010 | M    | P Panel Thickness |      | R<br>Thread<br>Class 2A UNEF | Z    | L<br>Max.           | M    | N<br>Max. | Z<br>±.040 |
|               |                    |       |                          |                          |                     |      | Min.              | Max. |                              |      |                     |      |           |            |
| 6             | .625               | .812  | .348                     | .405                     | .125                | .696 | .062              | .125 | .4375-28                     | .231 | .568                | .696 | .604      | .191       |
| 8             | .750               | .938  | .473                     | .530                     | .125                | .696 | .062              | .125 | .5625-24                     | .231 | .568                | .696 | .729      | .191       |
| 10            | .875               | 1.062 | .590                     | .655                     | .125                | .696 | .062              | .125 | .6875-24                     | .231 | .568                | .696 | .854      | .191       |
| 12            | 1.062              | 1.250 | .750                     | .818                     | .125                | .696 | .062              | .125 | .8750-20                     | .231 | .568                | .696 | .979      | .191       |
| 14            | 1.188              | 1.375 | .875                     | .942                     | .125                | .696 | .062              | .125 | 1.0000-20                    | .231 | .568                | .696 | 1.104     | .191       |
| 16            | 1.312              | 1.500 | 1.000                    | 1.066                    | .125                | .696 | .062              | .125 | 1.1250-18                    | .231 | .568                | .696 | 1.229     | .191       |
| 18            | 1.438              | 1.625 | 1.125                    | 1.191                    | .125                | .696 | .062              | .125 | 1.2500-18                    | .231 | .568                | .696 | 1.354     | .191       |
| 20            | 1.562              | 1.812 | 1.250                    | 1.316                    | .156                | .884 | .062              | .250 | 1.3750-18                    | .261 | .630                | .884 | 1.510     | .221       |
| 22            | 1.688              | 1.938 | 1.375                    | 1.441                    | .156                | .884 | .062              | .250 | 1.5000-18                    | .261 | .630                | .884 | 1.635     | .221       |
| 24            | 1.816              | 2.062 | 1.500                    | 1.566                    | .156                | .917 | .062              | .250 | 1.6250-18                    | .228 | .660                | .917 | 1.760     | .188       |

| Shell Size | Class "A" (SR), "P" (SR), MS / "F" |        |      |       |       |      | Class "E" (SR) |        |      |       |       |      | Class "P", MS / "P" |                  |      |       |      |
|------------|------------------------------------|--------|------|-------|-------|------|----------------|--------|------|-------|-------|------|---------------------|------------------|------|-------|------|
|            | C Thread                           | D Max. | G    | H     | L     | M    | C Thread       | D Max. | G    | H     | L     | M    | D Max.              | L +.010<br>−.026 | M    | N     | Z    |
| 6          | —                                  | —      | —    | —     | —     | —    | —              | —      | —    | —     | —     | —    | .202                | .593             | .696 | .484  | .191 |
| 8          | 6-32                               | .250   | .125 | .781  | 1.062 | .696 | 6-32           | .250   | .125 | .775  | 1.029 | .696 | .327                | .593             | .696 | .608  | .191 |
| 10         | 6-32                               | .312   | .188 | .844  | 1.062 | .696 | 6-32           | .312   | .188 | .837  | 1.029 | .696 | .444                | .593             | .696 | .734  | .191 |
| 12         | 6-32                               | .438   | .312 | .969  | 1.062 | .696 | 6-32           | .438   | .312 | .963  | 1.029 | .696 | .558                | .593             | .696 | .858  | .191 |
| 14         | 6-32                               | .562   | .375 | 1.094 | 1.062 | .696 | 6-32           | .562   | .375 | 1.087 | 1.029 | .696 | .683                | .593             | .696 | .984  | .191 |
| 16         | 6-32                               | .625   | .500 | 1.156 | 1.188 | .696 | 6-32           | .625   | .500 | 1.150 | 1.161 | .696 | .808                | .593             | .696 | 1.110 | .191 |
| 18         | 8-32                               | .750   | .625 | 1.406 | 1.188 | .696 | 8-32           | .750   | .625 | 1.400 | 1.161 | .696 | .909                | .593             | .696 | 1.234 | .191 |
| 20         | 8-32                               | .750   | .625 | 1.406 | 1.250 | .884 | 8-32           | .750   | .625 | 1.400 | 1.224 | .884 | 1.034               | .718             | .884 | 1.360 | .221 |
| 22         | 8-32                               | .938   | .750 | 1.594 | 1.250 | .884 | 8-32           | .938   | .750 | 1.587 | 1.224 | .884 | 1.159               | .718             | .884 | 1.484 | .221 |
| 24*        | 8-32                               | 1.000  | .800 | 1.594 | 1.250 | .917 | 8-32           | 1.000  | .800 | 1.681 | 1.320 | .917 | 1.284               | .718             | .917 | 1.610 | .188 |

\* Size 24 strain relief available in PT only.

All dimensions for reference only.