




D38999/45



Solder Mount Hermetic Receptacle

MIL-DTL-38999 Series IV

How To Order: *MS*



**Non-Environmental
Rear Accessory Thread Adapter
Available for this Receptacle
See P/N 980-002 on Page B-90**



Dimensions in Inches (millimeters) are subject to change without notice.

234-100-H5
Solder Mount Hermetic Receptacle
MIL-DTL-38999 Series IV Type




How To Order: Commercial

Connector Series 234-100 - Series IV Type	Shell Style H5 - Hermetic Solder Mount	Shell Size 11, 13, 15, 17, 19, 21, 23, 25	Contact Termination P - Pin, Solder Cup S - Socket, Solder Cup X - Pin, Eyelet Z - Socket, Eyelet C - Pin, PCB D - Socket, PCB
---	--	---	---

234 - 100 - H5 Z1 11 - 35 P N

Connector Material / Finish ZL - CRES, Nickel Z1 - CRES, Passivated	Insert Arrangement Per MIL-STD-1560; See Pages B-2 - B-4	Alternate Key Position A, B, C, D, K, L, M, R, U (N = Normal)
--	---	--

B



WIRE ACCOMODATION	
Contact Size	Wire Gauge
22D	#22 - #28
20	#20 - #24
16	#16 - #20
12	#12 - #14

HERMETIC LEAK RATE MOD CODES	
Designator	Required Leak Rate
-585A	1 x 10 ⁻¹⁰ cc Helium per second
-585B	1 x 10 ⁻⁹ cc Helium per second
-585C	1 x 10 ⁻⁸ cc Helium per second

TABLE I: CONNECTOR DIMENSIONS					
SHELL SIZE CODE	SHELL SIZE	ø A MAX	ø B MAX	ø C ±.005(0.1)	D
B	11	.783(19.9)	.862(21.9)	.789(20.0)	.793(20.1) .778(19.8)
C	13	.909(23.1)	.988(25.1)	.914(23.2)	.919(23.3) .904(23.0)
D	15	1.035(26.3)	1.110(28.2)	1.038(26.4)	1.044(26.5) 1.028(26.1)
E	17	1.157(29.4)	1.236(31.4)	1.164(29.6)	1.170(29.7) 1.155(29.3)
F	19	1.252(31.8)	1.331(33.8)	1.258(32.0)	1.294(32.9) 1.279(32.5)
G	21	1.378(35.0)	1.457(37.0)	1.383(35.1)	1.419(36.0) 1.404(35.7)
H	23	1.504(38.2)	1.583(40.2)	1.508(38.3)	1.544(39.2) 1.528(38.8)
J	25	1.630(41.4)	1.705(43.3)	1.643(41.7)	1.670(42.4) 1.654(42.0)

TABLE II: CONTACT SIZE	
PRINTED CIRCUIT TAIL CONFIGURATIONS CONTACT STYLE C AND D SIZE 12 AND SIZE 16 SIZE 22D AND SIZE 20	
Contact Size	ø P
22D	.011 (0.28) .015 (0.38)
20	.024 (0.61) .028 (0.71)
16	.0635 (1.61) .0615 (1.56)
12	.095 (2.41) .093 (2.36)

Dimensions in Inches (millimeters) are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[230-012Z111-05PN](#) [230-012Z111-99XN](#) [230-012Z111-99PN](#) [230-012P15-97PN](#) [230-012P11-05PC](#) [230-012P11-05PA](#) [230-012P13-98PN](#) [230-012P17-08PN](#) [230-012P17-26PN](#) [230-012P19-35PN](#) [230-012P21-35PN](#) [230-012P21-41PN](#) [230-012P25-35PN](#) [230-012P25-61PN](#) [230-012P11-05PB](#) [230-012P11-05PN](#) [230-012P13-35PN](#)