




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	27JUL2015	NP	XX
	A1	ECR-15-018715 ADD 114 SPEC.	29DEC2015	NP	XX

D



C

TECHNICAL DATA	T411350X02X-000	T411350X03X-000	T411350X04X-000	T411350X05X-000
RATED VOLTAGE	250V	250V	250V	60V
RATED CURRENT	4A	4A	4A	4A
POLLUTION DEGREE	3	3	3	3
OVERVOLTAGE CATEGORY	II	II	II	II
MATERIAL GROUP	II	II	II	II
CONTACT RESISTANCE	≤8mΩ	≤8mΩ	≤8mΩ	≤8mΩ
INSULATION RESISTANCE	>100MΩ	>100MΩ	>100MΩ	>100MΩ
DEGREE OF PROTECTION	IP67	IP67	IP67	IP67
OPERATION TEMPERATURE	-40~85°C	-40~85°C	-40~85°C	-40~85°C

B

PIN ARRANGEMENT D-CODE		
T411350X02X-000	T411350X03X-000	T411350X04X-000
T411350X05X-000		

T4113502051-000	RPC-M12D-MR-5CON-PG9-MU
T4113501051-000	RPC-M12D-MR-5CON-PG7-MU
T4113502052-000	RPC-M12D-MR-5CON-PG9-M
T4113501052-000	RPC-M12D-MR-5CON-PG7-M
T4113502041-000	RPC-M12D-MR-4CON-PG9-MU
T4113501041-000	RPC-M12D-MR-4CON-PG7-MU
T4113502042-000	RPC-M12D-MR-4CON-PG9-M
T4113501042-000	RPC-M12D-MR-4CON-PG7-M
T4113502031-000	RPC-M12D-MR-3CON-PG9-MU
T4113501031-000	RPC-M12D-MR-3CON-PG7-MU
T4113502032-000	RPC-M12D-MR-3CON-PG9-M
T4113501032-000	RPC-M12D-MR-3CON-PG7-M
T4113502021-000	RPC-M12D-MR-2CON-PG9-MU
T4113501021-000	RPC-M12D-MR-2CON-PG7-MU
T4113502022-000	RPC-M12D-MR-2CON-PG9-M
T4113501022-000	RPC-M12D-MR-2CON-PG7-M
TE PN	TYPE

- NOTE:
- MATERIAL:
 - ITEM NO.1:NUT -BRASS
 - ITEM NO.2:HOUSING -PA
 - ITEM NO.3:CONTACT -BRASS
 - ITEM NO.4: HOUSING BODY: -PBT+GF
 - CONTACT FINISH:
 - GOLD OVER NICKEL OR SILVER OVER NICKEL
 - CABLE WIRES:
 - 18AWG/0.75mm² Max. FOR 2-5 PINS
 - ALLDIMENSIONS ARE FOR NOMINAL REFERENCE ONLY UNLESS OTHERWISE STATED
 - PACKAGEING: 1PIECE IN A BAG
 - PN INFORMATION

T411350XXX-000

CONTACT FINISH:
1: GOLD OVER NICKEL
2: SILVER OVER NICKEL

NUMBERS OF PINS:
02: 2 PINS
03: 3 PINS
04: 4 PINS
05: 5 PINS
08: 8 PINS

CABLE OUTLET:
1: PG7(CABLE FEED: 4-6mm)
2: PG9(CABLE FEED: 6-8mm)

BRAND:
T: W/ TE LOGO
N: W/O LOGO

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN HAO WANG 08DEC2014	TE Connectivity		
		CHK KOBBY ZHAO 08DEC2014			
DIMENSIONS: mm		APVD XIANG XU 08DEC2014	NAME M12 MALE, RIGHT ANGLE UNSHIELDED CONNECTOR D CODE, SCREW TERMINAL		
		PRODUCT SPEC 108-106140			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ± FINISH		APPLICATION SPEC 114-137144	SIZE A2	CAGE CODE -	DRAWING NO T411350XXXX000
MATERIAL - -		WEIGHT -	RESTRICTED TO -		
		Customer Drawing	SCALE 2:1	SHEET 1 OF 1	REV A2