

# SACC-DSI-M12FSL-4FE-M16XL-L180 - Device connector rear mounting



1415338  
<https://www.phoenixcontact.com/us/products/1415338>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, Power, 5-position, Socket, straight, M12, coding: L, Rear mounting, M16 x 1.5, Wave soldering, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239091

## Your advantages

- Easy PCB assembly: one-piece connectors for wave soldering
- For compact devices: transmit high power in a confined space
- Easy-to-install, optimized XL housing contour with wrench size 19
- Mechanical tightening limitation for long-term-stable gasket

## Commercial data

Item number	1415338
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB26
Product key	ABQEHN
GTIN	4055626055794
Weight per piece (including packing)	18.135 g
Weight per piece (excluding packing)	18 g
Customs tariff number	85366990
Country of origin	DE

# SACC-DSI-M12FSL-4FE-M16XL-L180 - Device connector rear mounting



1415338

<https://www.phoenixcontact.com/us/products/1415338>

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Notes on operation	FE not connected to metal parts that can be touched, no protective function
Order information:	Lock nut is included in the scope of delivery

### Mounting

Mounting type	Rear mounting M16 x 1.5 With flat nut
Assembly note	With flat nut

### Product properties

Product type	Circular connectors (device side)
Sensor type	Power
Number of positions	5
Shielded	no
Coding	L
Thread type	M12

### Data management status

Article revision	05
------------------	----

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA
Material for screw connection	Zinc die-cast, nickel-plated

### Electrical properties

Rated voltage in acc. with IEC 61076-2-101	630 V
Rated surge voltage	1.5 kV
Nominal voltage $U_N$	63 V DC
Nominal current $I_N$	16 A

# SACC-DSI-M12FSL-4FE-M16XL-L180 - Device connector rear mounting



1415338

<https://www.phoenixcontact.com/us/products/1415338>

## Connection data

### Conductor connection

Connection method	Wave soldering
Contact connection type	Socket

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

## Connector

### Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	L

## Cable/line

Signal type/category	Power
----------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
	IP65/IP67
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-40 °C ... 85 °C (without mechanical actuation)

## Standards and regulations

### M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-111
Note	In line with


# SACC-DSI-M12FSL-4FE-M16XL-L180 - Device connector rear mounting

1415338

<https://www.phoenixcontact.com/us/products/1415338>

## Drawings

Schematic diagram



Pin assignment of M12 socket, 5-pos., L-coded, socket side view


# SACC-DSI-M12FSL-4FE-M16XL-L180 - Device connector rear mounting



1415338  
<https://www.phoenixcontact.com/us/products/1415338>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1415338>

	<b>cULus Recognized</b>			
	Approval ID: E468743-20180113			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	63 V	16 A	-	-

# SACC-DSI-M12FSL-4FE-M16XL-L180 - Device connector rear mounting



1415338

<https://www.phoenixcontact.com/us/products/1415338>

## Classifications

### ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-DSI-M12FSL-4FE-M16XL-L180 - Device connector rear mounting



1415338  
<https://www.phoenixcontact.com/us/products/1415338>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	0cd0c1a3-3429-4356-88cc-fdc633ec431c

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)