

HC-26P1N122300 - Device connector front mounting



1590276

<https://www.phoenixcontact.com/us/products/1590276>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, straight, Screw locking mechanism, M27, number of positions: 26, contact connection type: Pin, Flat gasket, 4x Ø 3.2, shielded: yes, degree of protection: IP67, number of positions: 26, connection method: Solder connection, series: HC, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1240134

Commercial data

Item number	1590276
Packing unit	24 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAJL
GTIN	4046356186520
Weight per piece (including packing)	45.45 g
Weight per piece (excluding packing)	45.45 g
Customs tariff number	85366990
Country of origin	DE

HC-26P1N122300 - Device connector front mounting

1590276

<https://www.phoenixcontact.com/us/products/1590276>



Technical data

Mounting

Mounting type	Front mounting
Mounting	4x Ø 3.2

Product properties

Product type	Circular connectors (device side)
Series	HC
Application	Signal
Number of positions	26
Connection profile	26
Shielded	yes
Coding	N
Thread type	M27

Data management status

Article revision	05
------------------	----

Material specifications

Flammability rating according to UL 94	V0
Seal material	FPM or NBR or EPDM
Housing material	Metal
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA66
Contact material	CuZn
Contact surface	Nickel-plated, gold coating
Gasket and O-ring material	NBR

Electrical properties

Contact

Contact diameter	1 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²
Max. current	8 A
Nominal voltage U _N	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Conductor connection

HC-26P1N122300 - Device connector front mounting

1590276

<https://www.phoenixcontact.com/us/products/1590276>



Connection method	Solder connection
Contact connection type	Pin

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	50

Connector

Type	straight
Direction of rotation	Standard

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

HC-26P1N122300 - Device connector front mounting




1590276

<https://www.phoenixcontact.com/us/products/1590276>

Drawings


Dimensional drawing



Dimensional drawing

Dimensional drawing

4xØ3,2/M3/□23±0,1



Installation dimensions


HC-26P1N122300 - Device connector front mounting

1590276

<https://www.phoenixcontact.com/us/products/1590276>



Schematic diagram



Connector pin assignment

HC-26P1N122300 - Device connector front mounting

1590276

<https://www.phoenixcontact.com/us/products/1590276>



Classifications

ECLASS

ECLASS-11.0	27440109
ECLASS-12.0	27440109
ECLASS-13.0	27440109

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-26P1N122300 - Device connector front mounting

1590276

<https://www.phoenixcontact.com/us/products/1590276>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ffa12381-6aad-4067-a8d5-ab0a0b528863

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com