

HDC enclosures
HDC 10A TSLU 1M20G**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 10A TSLU 1M20G
Order No.	1967660000
Version	HDC enclosures, Size: 2, Protection degree: IP65, Cable entry from side, Plug housing, End-locking clamp, lower side, Standard, Size of cable entries: M 20
GTIN (EAN)	4032248665761
Qty.	1 pc(s).

HDC enclosures

HDC 10A TSLU 1M20G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	72.5 mm	Length (inches)	2.854 inch
Width	32.5 mm	Width (inches)	1.28 inch
Height	54 mm	Height (inches)	2.126 inch
Net weight	103 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Dimensions

Cable entry	w. threading	Height of housing B	54 mm
Total length housing	63 mm	Width housing C	29.5 mm

General data

EMC housings	No	Housing main material	diecast aluminium
Material of locking element	Stainless steel, rust-proof	Protection degree	IP65
Surface finish	Powder coating		

Version

Cable entry	w. threading	Clamp version	End-locking clamp
Design	Standard	Design of housing	Cable entry from side, Plug housing
Design of locking system	End-locking clamp, lower side	Internal thread	M 20
Number of cable entry on top	0	Number of cable entry sideways	1
Sealing	NBR	Size	2
Size of cable entries	M 20	Suitable for ModuPlug®	No
Top part/bottom part/lid	upper part	Type	Plug

Classifications

ETIM 3.0	EC000437	ETIM 4.0	EC000437
ETIM 5.0	EC000437	ETIM 6.0	EC000437
UNSPSC	30-21-18-01	eClass 5.1	27-14-34-19
eClass 6.2	27-26-12-03	eClass 7.1	27-44-02-02
eClass 8.1	27-44-02-02	eClass 9.0	27-44-02-02
eClass 9.1	27-44-02-02		

Approvals

Approvals



ROHS	Conform
------	---------

HDC enclosures HDC 10A TSLU 1M20G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN FL FIELDWIRING EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

HDC enclosures HDC 10A TSLU 1M20G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

