




CORE DIMENSIONS 33T0155-00P

UNCOATED CORE					
	MM	INCHES		MM	INCHES
OD	3.94	(.155)	±	.13	(.005)
ID	2.24	(.088)	±	.13	(.005)
TH	2.54	(.100)	±	.13	(.005)
SINGLE PARAYLENE					
OD	3.96	(.156)	±	.13	(.005)
ID	2.21	(.087)	±	.13	(.005)
TH	2.57	(.101)	±	.13	(.005)

WEIGHT / K 0.1022 KGS .2253 LBS
INITIAL PERMEABILITY 2700

ROOM TEMPERATURE ELECTRICAL SPECIFICATION								
	MIN. TOL.	MIN. (μH)	NOM. (μH)	MAX. (μH)	MAX. TOL.	FREQ. (kHz)	VOLT. (mV)	TURNS
L1-1T	-20.0%	0.621	0.776	0.931	+20.0%	100	≤0.94	1
Q		62					≤0.94	1

COATING SPECIFICATIONS			
TYPE	Max. Coating (mm / mils.)	Min. DLB VAC	TEST FORCE (LB)
Paraylene	0.5	1000	.13

NOTES:

1. Cosmetic Specification refer to WI-QA-015.



Rev	Description	Date	INT
A	Original Draft	06/02/2002	TPM
B	Reactivate print Changed P/N to-00P Removed Q coating per ERP List 9-23-05	09/29/2005	TMB
C	Remove Min Tolerance Max Value & Freq Value From Q Ref Line	11/14/2005	TMB
-	Add KGS Weight Corrected Uncoated Tolerance Per Engr	-	-
D	Revised Template	6/1/2006	WMM
E	Correct voltage setting from 0.94V to 0.94mV	01/15/2007	Dxu
F	Revised Template	2019/3/10	Jcai

Date:2019/3/10	DWG # 33T0155-00P-F	Rev: F
Drawn By: Jcai	Title # 33T0155-00P	

Laird This document contains information which is proprietary to laird. No production or publication of this document in whole or in part shall be made without written authorization from Laird.