

HC-STA-B16-HHWD-1TTP21-EL-AL - Housing



1412715

<https://www.phoenixcontact.com/us/products/1412715>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing B16, with double locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, straight, 1x Pg21, height: 76 mm, cable gland: none, Standard

Your advantages

- Good shielding in the event of electromagnetic interference

Commercial data

Item number	1412715
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	BF7APB
Catalog page	Page 628 (C-2-2019)
GTIN	4055626059891
Weight per piece (including packing)	249.8 g
Weight per piece (excluding packing)	257.6 g
Customs tariff number	85389099
Country of origin	PL

HC-STA-B16-HHWD-1TTP21-EL-AL - Housing



1412715

<https://www.phoenixcontact.com/us/products/1412715>

Technical data

Notes

General	For contact inserts HC-B16, BB32, D40, DD72, HS6, HV6, M, K
General	also available as a powder-coated or color version: 1373023 HC-STA-B16-HHWD-1TTP21-EL/...


Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B16
No. of cable outlets	1
Type of the screw connection	1x Pg21
Type	Tall design
Cable outlet	straight
Pg screw connection	none

Data management status

Article revision	03
------------------	----

Dimensions

Dimensional drawing	
Width	44 mm
Height	76 mm
Length	93.5 mm

Material specifications

Flammability rating according to UL 94	V0 (Interlock)
Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated
Locking latch material	PA

Mechanical properties

Mechanical data

Type of the screw connection	1x Pg21
Locking type	Latch

Environmental and real-life conditions

HC-STA-B16-HHWD-1TTP21-EL-AL - Housing



1412715

<https://www.phoenixcontact.com/us/products/1412715>

Ambient conditions

Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Impact strength	IK09
Ambient temperature (operation)	-40 °C ... 125 °C

HC-STA-B16-HHWD-1TTP21-EL-AL - Housing


1412715

<https://www.phoenixcontact.com/us/products/1412715>



Drawings

Dimensional drawing



Dimensional drawing

HC-STA-B16-HHWD-1TTP21-EL-AL - Housing



1412715

<https://www.phoenixcontact.com/us/products/1412715>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1412715>

DNV

Approval ID: TAE000037S



cUL Recognized

Approval ID: E255026



UL Recognized

Approval ID: E255026



EAC

Approval ID: RU C-DE.AI30.B.01102



EAC

Approval ID: RU C-DE.BL08.B.00511

cULus Recognized

HC-STA-B16-HHWD-1TTP21-EL-AL - Housing



1412715

<https://www.phoenixcontact.com/us/products/1412715>

Classifications

ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

ETIM

ETIM 9.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-STA-B16-HHWD-1TTP21-EL-AL - Housing



1412715

<https://www.phoenixcontact.com/us/products/1412715>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com