

SACC-CI-M12FS-5CON-L180 - Contact carrier



1551464

<https://www.phoenixcontact.com/us/products/1551464>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 5-position, Socket, straight, M12, coding: A, PCB mounting, Wave soldering, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239983

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Additional gasket for the device when not plugged in

Commercial data

Item number	1551464
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB23
Product key	ABQAGS
Catalog page	Page 254 (C-2-2013)
GTIN	4046356153669
Weight per piece (including packing)	4.815 g
Weight per piece (excluding packing)	4.4 g
Customs tariff number	85366990
Country of origin	DE

SACC-CI-M12FS-5CON-L180 - Contact carrier



1551464

<https://www.phoenixcontact.com/us/products/1551464>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Number of positions	5
Seal present	yes
Coding	A
Thread type	M12

Data management status

Article revision	05
------------------	----

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	60 V
Nominal current I_N	4 A

Connection data

Connection method	Wave soldering
-------------------	----------------

Signaling

Status display	no
Status display present	No

Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM / EPDM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 6.6

Connector

SACC-CI-M12FS-5CON-L180 - Contact carrier



1551464

<https://www.phoenixcontact.com/us/products/1551464>

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
	IP67
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-40 °C ... 85 °C (without mechanical actuation)

Standards and regulations

M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

Mounting


Mounting type	PCB mounting
---------------	--------------

1551464

<https://www.phoenixcontact.com/us/products/1551464>

Drawings

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

SACC-CI-M12FS-5CON-L180 - Contact carrier





1551464


<https://www.phoenixcontact.com/us/products/1551464>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1551464>

 cUL Recognized Approval ID: E118976-20100522				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	60 V	4 A	22 - 22	-

 UL Recognized Approval ID: E118976-20100522				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	60 V	4 A	22 - 22	-

 cULus Recognized Approval ID: E221474-20140616				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	60 V	4 A	-	-

cULus Recognized				
-------------------------	--	--	--	--

SACC-CI-M12FS-5CON-L180 - Contact carrier



1551464

<https://www.phoenixcontact.com/us/products/1551464>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27460201

ETIM

ETIM 9.0	EC002637
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CI-M12FS-5CON-L180 - Contact carrier



1551464
<https://www.phoenixcontact.com/us/products/1551464>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	798bdf1d-39ed-4f6f-99ae-b9bc184b115a

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com