




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **.51 – 1.65 mm²**

Mating Tab Width: **2.8 mm [.11 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Connection Capacity	Single
Compatible With Wire & Cable Type	Discrete Wire

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	2.8 mm[.11 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Phosphor Bronze
Terminal Plating Material	Pre-Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

	.055 in
Wire Insulation Support	With
Mating Retention Type	Locking Lance

Dimensions

Terminal Material Thickness	.41 mm[.016 in]
Product Length	22 mm[.866 in]
Compatible Insulation Diameter Range	2.31 – 3 mm[.091 – .118 in]
Wire Size	.51 – 1.65 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Packaging Features

Packaging Quantity	6000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these




limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2150603-2

[OCEAN_2.0_Applicator-E-090F130F-REA](#)



KIT

TE Part # 7-2150603-7

[OCEAN_2.0_SPARE_PART_KIT-090F130F](#)

Also in the Series | FASTIN-FASTON 110



[Automotive Housings\(6\)](#)




[Automotive Terminals\(5\)](#)



[Crimp Terminal Housings\(34\)](#)



[Insertion & Extraction Tools\(3\)](#)



[Quick Disconnects\(83\)](#)

Customers Also Bought





TE Part #WHDS-24-2
STRAIN RELIEF, HD30, 24SZ, RA




TE Part #165015
PLASTI-GRIP, SPADE 12-10 4.5MM




TE Part #160655-4
FF 110 REC TERMINAL 20-15 AWG PTPPB



TE Part #160864-2
FF 110 REC TERMINAL 20-17 AWG PTPB




TE Part #626064
2 WAY FASTIN-ON 110 HOUSING REC PA66 NAT



TE Part #626065
2 P FASTIN-ON 110 HOUSING TAB PA66 NAT



TE Part #31812
TERMINAL,SOLIS R 4 3/8



TE Part #2029150-5
5P R/A HDR VAL-U-LOK V2 W/P

Documents

Product Drawings

FF 110 TAB 0.5-1.5MM2 PTPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_160762-2_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_160762-2_L.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_160762-2_L.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

FASTIN-FASTON CONN. .110 INCH, .187 INCH, .250 INCH, .375 INCH SRS.

English

Product Specification

English