

REVISION E

DIMENSIONS ARE IN INCHES

UNLESS OTHERWISE NOTED


TOLERANCES ARE:

ONE PLACE DECIMALS $\pm .1$
TWO PLACE DECIMALS $\pm .01$ THREE PLACE DECIMALS $\pm .005$
FOUR PLACE DECIMALS $\pm .0020$ ANGLES
 $\pm 2^\circ$ TITLE:
.100 ϕ IDC MOLD
TO POSITION MALE
SUB-ASSEMBLY

DWG NO:

HCMD-XX-XX-X

SHEET 1 OF 1



HCMD-XX-XX-X

NO. OF POS. PER ROW
-02, -03, -04, -05,
-07, -08, -09, -10,
-13, -14, -15, -17,
-20, -25, -30, -32,
-36

OPTIONS

-S: SELECTIVE PLATING
USE T-1S12-XX-S)
(LEAVE BLANK FOR
STANDARD TIN PLATING AND
USE T-1S12-XX-T)

LEAD STYLE



-01: USE T-1S12-01-X
(SEE TABLE 1)
-02: USE T-1S12-02-X
(SEE TABLE 1)END VIEW SHOWN WITH
MFC-XX-D REMOVED

TABLE 1

LEAD STYLE	"A"
-01	.120
-02	.230

POSITION PARTS IN TUBE AS SHOWN



ARROW TO POINT AWAY FROM FIRST POS. INDICATOR

DO NOT SCALE
FROM THIS PRINT

NOTES:

- RETENTION FORCE OF TERMINAL IN BODY TO BE 2 lbs. MIN
- $\triangle$ REPRESENTS CRITICAL DIMENSION FOR STATISTICAL PROCESS CONTROL.

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322MADE BY: KOLB 9-27-91
CHECKED BY: McCARTINENG.
APPROVAL
D.E.MHCMD-XX-XX-X
SHEET 1 OF 1