

Han HPR HPTC 850 CS UNSH IP65/67 240



Image is for illustration purposes only. Please refer to product description.

Part number	10 40 281 2129
Specification	Han HPR HPTC 850 CS UNSH IP65/67 240
HARTING eCatalogue	https://b2b.harting.com/10402812129

Identification

Category	Connector sets
Series of hoods/housings	Han® HPR HPTC
Type of hood/housing	Complete set
Description of hood/housing	Cable side
Type of cable	Copper cable (round)
Features	for stranded wires according to IEC 60228 Class 5

Version

Shielding	360° shielding
Coding	16 coding options
Cable entry	1x M40
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Conductor cross-section	240 mm ²
Rated current	850 A
Rated voltage	3,600 V
Rated impulse voltage	20 kV
Pollution degree	4
Overvoltage category	III (protection by low voltage)
Limiting temperature	-40 ... +125 °C
Mating cycles	≥25

Technical characteristics

Degree of protection acc. to IEC 60529	IP65 IP67
--	--------------

Material properties

Material (insert)	Polyamide (PA)
Material (hood/housing)	Aluminium die-cast
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 50467 EN 50124-1 IEC 61373 Category 1 Class B EN 45545 EN 60137
----------------	--

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440101 Rectangular connectors (set)