



AMP CT

TE Internal #: 6-173977-4

Connector Assembly, Receptacle, Wire-to-Board, 4 Position, 2 mm [.079 in] Centerline, Insulation Displacement (IDC), 1 Row, Black, AMP CT

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings > AMP COMMON TERMINATION HOUSINGS



Connector Product Type: **Connector Assembly**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Board**
Number of Positions: **4**
Centerline (Pitch): **2 mm [.079 in]**

[All AMP COMMON TERMINATION HOUSINGS \(176\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	1

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

--	--



Contact Current Rating (Max)	2 A
------------------------------	-----

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT GF
Centerline (Pitch)	2 mm[.079 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-3983178-PHBXVD CT 2mm Post Header Asmbly: Box V DIP	 TE Part # CAT-3984552-BHTHVS CT Box Header SMT: Vert, Shrouded	 TE Part # CAT-AM7017-H342 AMP COMMON TERMINATION HEADERS	 TE Part # CAT-3980408-PHDWKV CT 2mm Post Header Assembly with Kink - Vertical
 TE Part # CAT-3984552-PHITPS CT Post Header Assembly: Part. Shrouded	 TE Part # CAT-3980407-RHDRRA CT 2mm Header Assembly: Right Angle	 TE Part # 58074-1 MTA 50/100/156 MANUAL TOOL FRAME	 TE Part # 58372-1 HEAD (IDC) 2MM C.T. W/O TL
 TE Part # 292215-4 MINI CT SGL RELAY 4P NAT	 TE Part # CAT-3980655-RHAWP CT Relay Header Assembly: Wire-to-Panel	 TE Part # CAT-3983174-PHBXHK CT 2mm Post Header Assembly Box H Kink	 TE Part # 2-292254-4 CT RELAY HDR ASSY 4P BLUE
 TE Part # 2-292164-4 CT P/HDR BOX H ASSY 4P T/P BLU	 TE Part # 2-292165-4 CT P/HDR BOX V 4P T/P BLUE	 TE Part # 4-292165-4 CT P/HDR BOX V 4P T/P YELLOW	 TE Part # 5-292215-4 MINI CT SGL RELAY 4P BLUE



TE Part # 6-292165-4
CT P/HDR BOX V 4P T/P BLACK

TE Part # 6-292170-4
CT P/HDR ASSY 4P V W/O KINK T

TE Part # 6-292254-4
CT RELAY HDR ASSY 4P BLACK

TE Part # 292254-4
CT RELAY HDR ASSY 4P NAT

Also in the Series

AMP CT

Connector Contacts(8)

Connector Hardware(46)

PCB Headers & Receptacles(756)

Wire-to-Board Connector Assemblies & Housings(255)

Customers Also Bought

TE Part #1462038-4
IM01CGR=IM RELAY 140mW 3V HDV

TE Part #6-173977-2
CT CONN MT REC ASSY 2P BLACK

TE Part #2309414-1
DDR4 SODIMM 260P 9.2H RVS

TE Part #292180-1
CAP ASS'Y W/O COMMONING TAB FO

TE Part #292228-4
1.5 MINI CT SGL H SMT W/O BOSS

TE Part #1565089-1
GRACE INERTIA CONNECTOR 3.5 2P

TE Part #66102-4
III+ PIN,24-20,30AU/FL,STRIP

TE Part #3-2176091-1
RP 2A 0.25W 118R 0.1% 25PPM 1K RL

Documents

- CAD Files
- Customer View Model
- ENG_CVM_CVM_6-173977-4_M.2d_dxf.zip
- English
- 3D PDF
- 3D



Customer View Model

[ENG_CVM_CVM_6-173977-4_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-173977-4_M.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[MINI PRESS CT CONNECTOR \(WAS IS-553J\)](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese

Agency Approvals

[CSA Certificate](#)

English