







THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2015/09/07	Cary	Change Rev. 01 to Rev.A




MI2S-04PMMS-SH8CXX

XX: 150~1500mm
15: 150mm
30: 300mm
50: 500mm
A0: 1000mm
A5: 1500mm
Wire Length(L): 150~1500mm



Pin Assignment
Front View



Recommended
Panel Cut-Out

PE	Black	黑
3	Blue	藍
2	White	白
1	Brown	棕
Conn.	Wire Color Pin Out	

Note:
* $\varnothing$ Important Dimension.
* Waterproof Rate: IP68.
IP68: 1M Depth Of Water In 24hours.
* Housing: PA66, UL94V-0, Black.
* Male Pin: Copper Alloy, Gold Plated.
* Shield: Zinc Alloy, Nickel Plated.
* Panel Nut: Zinc Alloy, Nickel Plated.
* O-Ring: Viton, Black.
* Wire Harness: UL1015 16AWG(1.5mm²).
* Rated Voltage: 630V AC
* Rated Current at 40°C: 12A
* Operation Temperature: -40~85°C.
* For Panel Thickness Max 4.5mm.
* Nut Torque: 4-6 Kgf.cm(0.4~0.6N.m).
* Wire harness Tolerance: 150~300 ±15mm
301~1000 ±20mm
Over1000 ±40mm

UNIT:mm		TITLE		ITEM NO		DRAWN BY		DATE	
TOLERANCE		MI2 S-Code 4Pin Male Type		DWG NO		Cary		2015-09-07	
.X	±0.25	SCALE	1:1	SIZE	A4	CHECKED BY		DATE	
.XX	±0.1	REV.	A	WC-REV.	A.1	Yu Long		2015-09-07	
.XXX	±0.05	SHEET 1 OF 1		CUSTOMER		APPROVED BY		DATE	
ANGLES	±1°	QC: Inspection item		ALTW		Jerry		2015-09-07	

Amphenol LTW
安費諾亮泰企業股份有限公司