

SACC-CI-M12FS-8CON-L180-10G - Contact carrier



1402457

<https://www.phoenixcontact.com/us/products/1402457>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Ethernet CAT6_A, 8-position, Socket, straight, M12, coding: X, PCB mounting, THR solder connection, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1238675

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Compatible with connectors with screw or push-in connection

Commercial data

Item number	1402457
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB23
Product key	ABQAGS
Catalog page	Page 90 (C-2-2013)
GTIN	4046356615907
Weight per piece (including packing)	4.657 g
Weight per piece (excluding packing)	3.9 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Data
Sensor type	Ethernet
Number of positions	8
Seal present	no
Shielded	yes
Coding	X
Thread type	M12

Data management status

Article revision	03
------------------	----

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 5 \text{ m}\Omega$
Insulation resistance	$> 100 \text{ M}\Omega$
Nominal voltage U_N	50 V AC
	60 V DC
Nominal current I_N	0.5 A
Transmission characteristics (category)	CAT6 _A

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Interfaces

Signal type/category	Ethernet CAT6 _A
----------------------	----------------------------

Material specifications

Material	Zinc die-cast (nickel-plated)
Flammability rating according to UL 94	V0
Contact material	Copper alloy

SACC-CI-M12FS-8CON-L180-10G - Contact carrier



1402457

<https://www.phoenixcontact.com/us/products/1402457>

Contact surface material	Gold
Contact carrier material	PPA

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	X

Cable/line

Signal type/category	Ethernet CAT6 _A
----------------------	----------------------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
	IP67, when plugged in
Ambient temperature (operation)	-40 °C ... 90 °C

Standards and regulations

M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-109

Mounting


Mounting type	PCB mounting
---------------	--------------

Packaging specifications

Type of packaging	Blister
-------------------	---------

Drawings

Schematic diagram



Pin assignment M12 connector, 8-pos., view socket side

SACC-CI-M12FS-8CON-L180-10G - Contact carrier





1402457

<https://www.phoenixcontact.com/us/products/1402457>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1402457>

 cUL Recognized Approval ID: E335024-20120308				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	60 V	0.5 A	-	-

 UL Recognized Approval ID: E335024-20120308				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	60 V	0.5 A	-	-

cULus Recognized				
-------------------------	--	--	--	--

SACC-CI-M12FS-8CON-L180-10G - Contact carrier



1402457

<https://www.phoenixcontact.com/us/products/1402457>

Classifications

ECLASS

ECLASS-11.0	27440223
ECLASS-12.0	27440116
ECLASS-13.0	27440223

ETIM

ETIM 9.0	EC003557
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ebece220-b57c-4dcb-8b4a-6148d527e8ef