

Datasheet for part number CIR020R-22-7P-F80

Our Catalog Part Number: CIR020R-22-7P-F80
Our Global Manufacturing Part Number: 000445430
Brand: VEAM Product Category: Circular Product Line: Veam CIR, VBN, Other Series: CIR / FRCIR

Product Datasheet	
SERIES	Connector with Bayonet Coupling
Shell Style	Front Panel Mount Receptacle, with rear thread
Mounting	Flange with through mounting hole
Environmental Class	no endbell
Shell Size	22
Contact Arrangement	22-7
Total Number of contacts	1 contact
Number of Contacts Size 0	1 contact size 0
Gender	Pin
Contact Type	Crimp for AWG wire (used in F80 insert)
Contact Plating	Silver
Contact Material	Copper alloy
Shell Material	Aluminium alloy
Shell Plating	Chromate over Cadmium, olive drab, min. 500h salt spray resistance, conductive
Insulator Material	Chloroprene rubber
Wire Size Cross Section for Contacts Size 0	53 mm ² or AWG 0
Wire Size Cross Section for Contacts Size 12	3 mm ² or AWG 12
Contact Rating for Contacts Size 0	Maximum Current = 245 A Rated and Test Current = 150 A Potential Drop max. 53 mV
Contact Rating for Contacts Size 12	Maximum Current = 41 A Rated and Test Current = 23 A Potential Drop max. 63 mV
Shock Resistance	Waterproof to 10 metres (33 ft) 12 h (14.7 PSI)
Coupling	2000 couplings minimum
Service Rating Letter	E
Operating Voltage DC	1750 V
Operating Voltage AC	1250 V
Dielectric strength - Minimum Flashover AC RMS	4500 V
Dielectric strength - Test Voltage AC RMS (Hi Pot)	3500 V
Note	Voltages in excess of 30 V ac or 42.5 V dc are potentially hazardous and care should be taken to ensure that such voltages can't be transmitted in any way to exposed metal parts of the connector body.
General	Veam CIR series Connectors are produced in accordance with NATO Standard VG95234, which is based on MIL-C-5015 for physical size, layout and environment requirements.