

CA-17P1N12T006 - Cable connector



1620267
<https://www.phoenixcontact.com/us/products/1620267>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: CA, angled, shielded: yes, Screw locking mechanism, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Pin, Solder connection, cable diameter range: 4 mm ... 6 mm, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1244118

Your advantages

- Angled cable outlet for confined spaces
- Can be adapted to various applications, thanks to adjustable cable outlet direction
- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires

Commercial data

Item number	1620267
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAEC
Catalog page	Page 93 (C-2-2019)
GTIN	4046356818162
Weight per piece (including packing)	146.539 g
Weight per piece (excluding packing)	146.539 g
Customs tariff number	85366990
Country of origin	DE

CA-17P1N12T006 - Cable connector



1620267

<https://www.phoenixcontact.com/us/products/1620267>

Technical data

Product properties

Product type	Circular connector (cable-side)
Data management status	
Article revision	06

Connector

Insulating body	
Coding	N
Insulation body material	PBT
Contact material	CuZn
Contact surface material	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Pin
Application	Signal
Number of positions	17
Direction of rotation	Standard
Connection profile	17
Rated voltage	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Contact diameter	1 mm
Litz wire cross-section	1 mm²
Nominal current per signal contact	8 A

Housing	
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Type of locking	Screw locking mechanism
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

Seal	
External cable diameter	4 mm ... 6 mm
Seal material	NBR

Environmental and real-life conditions

CA-17P1N12T006 - Cable connector



1620267

<https://www.phoenixcontact.com/us/products/1620267>

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (storage/transport)	15 °C ... 25 °C
Permissible humidity (storage/transport)	50 % ... 65 %

CA-17P1N12T006 - Cable connector




1620267

<https://www.phoenixcontact.com/us/products/1620267>

Drawings

Schematic diagram



Connector pin assignment

CA-17P1N12T006 - Cable connector



1620267

<https://www.phoenixcontact.com/us/products/1620267>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1620267>

 cUL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	5 A	18 - 18	-

 UL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	8 A	18 - 18	-

cULus Recognized				
-------------------------	--	--	--	--

CA-17P1N12T006 - Cable connector



1620267

<https://www.phoenixcontact.com/us/products/1620267>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CA-17P1N12T006 - Cable connector



1620267
<https://www.phoenixcontact.com/us/products/1620267>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	efba72b6-669e-4240-8308-95b1fd08417c

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com