

S-PT-EX(I)-24DC-3/4" - Surge protection device



2882585

<https://www.phoenixcontact.com/us/products/2882585>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge protection in the IP67 screw-on module for measuring sensors in intrinsically safe circuits, direct mounting with 3/4" NPT external thread, cable gland for the signal line, two-stage protective circuit. HART-compatible. Can be used in safety-related circuits up to SIL 3.

Your advantages

- Easiest field mounting with standardized thread
- Versatile in use with universal protective circuit
- Use under extreme ambient conditions with robust design

Commercial data

Item number	2882585
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	CL02
Product key	CL2231
Catalog page	Page 154 (C-4-2019)
GTIN	4046356098076
Weight per piece (including packing)	440.6 g
Weight per piece (excluding packing)	391 g
Customs tariff number	85363010
Country of origin	DE

S-PT-EX(I)-24DC-3/4" - Surge protection device



2882585

<https://www.phoenixcontact.com/us/products/2882585>

Technical data

Notes

Notes on operation	When the bridge is disconnected, the shield connection is indirectly connected to the housing or reference potential.
--------------------	---

Product properties

Product type	Surge protection for MCR technology
Product family	SURGETRAB
IEC test classification	C1
	C2
	C3
	D1
Type	Screw-in module
Number of positions	3
Surge protection fault message	none
Wire pairs per module	1

Data management status

Article revision	17
------------------	----

Insulation characteristics

Overvoltage category	III
Pollution degree	2

Electrical properties

Nominal voltage U_N	24 V DC
-----------------------	---------

Connection data

Connection method	Screw connection
Screw thread	M3
Tightening torque	0.6 Nm
Conductor cross section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross section rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross section AWG	26 ... 16

Ex data

Maximum inner capacitance C_i	2 nF
Max. internal inductance L_i	1 µH
Max. input current I_i	350 mA ($T_4 / \leq 50^\circ\text{C}$)
	350 mA ($T_5 / \leq 50^\circ\text{C}$)
	350 mA ($T_6 / \leq 50^\circ\text{C}$)
Max. input voltage U_i	30 V
max. input power P_i	3.00 W
Insulation voltage to ground	500 V AC

S-PT-EX(I)-24DC-3/4" - Surge protection device



2882585

<https://www.phoenixcontact.com/us/products/2882585>

Ambient temperature (operation)	-40 °C ... 50 °C
Max. surface temperature	135 °C (T4)
	100 °C (T5)
	85 °C (T6)

Dimensions

Dimensional drawing	
Width	33.5 mm
Height	33.5 mm
Depth	148 mm

Material specifications

Color	Steel/stainless steel color
Housing material	Zinc die-cast, surface bronzed and nickel-plated
Housing surface material	nickel-plated

Mechanical properties

Mechanical data	
Open side panel	No

Protective circuit

Direction of action	Line-Line & Line-Earth Ground
Maximum continuous voltage U_C	30 V DC
	21 V AC
Rated current	350 mA (50 °C)
Operating effective current I_C at U_C	$\leq 10 \mu A$
Residual current I_{PE}	$\leq 2 \mu A$
Nominal discharge current I_n (8/20) μs (line-line)	10 kA
Nominal discharge current I_n (8/20) μs (line-ground)	10 kA (per path)
Nominal discharge current I_n (8/20) μs (shield-ground)	10 kA (optional)
Pulse discharge current I_{imp} (10/350) μs	1 kA
Max. discharge current I_{max} (8/20) μs maximum (line-line)	10 kA
Max. discharge current I_{max} (8/20) μs maximum (line-earth)	10 kA (per path)
Discharge surge current I_{max} (8/20) μs maximum (shield-ground)	10 kA
Nominal pulse current I_{an} (10/1000) μs (line-line)	30 A
Nominal pulse current I_{an} (10/1000) μs (line-earth)	100 A (per path)
Nominal pulse current I_{an} (10/1000) μs (shield-ground)	100 A
Output voltage limitation at 1 kV/ μs (line-line) spike	$\leq 50 V$
Output voltage limitation at 1 kV/ μs (line-earth) spike	$\leq 1.4 kV$ (Direct grounding)
Output voltage limitation at 1 kV/ μs (shield-ground) spike	$\leq 600 V$ (optional)

S-PT-EX(I)-24DC-3/4" - Surge protection device



2882585

<https://www.phoenixcontact.com/us/products/2882585>

Output voltage limitation at 1 kV/μs (line-line) static	≤ 50 V
Output voltage limitation at 1 kV/μs (line-earth) static	≤ 1.4 kV (Direct grounding)
Residual voltage at I _n (conductor-conductor)	≤ 50 V
Residual voltage with I _{an} (10/1000) μs (line-line)	≤ 50 V
Voltage protection level U _p (line-line)	≤ 50 V (C1 - 0.5 kV / 250 A)
	≤ 55 V (C1 - 1 kV / 500 A)
	≤ 55 V (C2 - 2 kV/1 kA)
	≤ 55 V (C2 - 10 kV / 5 kA)
	≤ 50 V (C3 - 10 A)
	≤ 50 V (C3 - 25 A)
	≤ 80 V (D1 - 1 kA)
Voltage protection level U _p (line-earth)	≤ 1.4 kV (C1 - 1 kV / 500 A)
	≤ 1.4 kV (C2 - 2 kV/1 kA)
	≤ 1.4 kV (C2 - 10 kV / 5 kA)
	≤ 1.4 kV (C3 - 25 A)
	≤ 1.4 kV (C3 - 100 A)
	≤ 1.4 kV (D1 - 1 kA)
Voltage protection level U _p (shield-ground)	≤ 600 V (C1 - 0.5 kV / 250 A)
	≤ 650 V (C1 - 1 kV / 500 A)
	≤ 650 V (C2 - 2 kV/1 kA)
	≤ 650 V (C2 - 10 kV / 5 kA)
	≤ 650 V (C3 - 10 A)
	≤ 750 V (C3 - 25 A)
	≤ 750 V (C3 - 100 A)
	≤ 650 V (D1 - 1 kA)
Response time t _A (line-line)	≤ 1 ns
Response time t _A (line-earth)	≤ 100 ns
Response time t _A (shield-ground)	≤ 100 ns
Input attenuation aE, sym.	typ. 0.5 dB (≤ 1 MHz / 50 Ω)
	typ. 0.2 dB (≤ 400 kHz / 150 Ω)
Cut-off frequency f _g (3 dB), sym. in 50 Ω system	typ. 6 MHz
Cut-off frequency f _g (3 dB), sym. in 150 Ω system	typ. 2.5 MHz
Resistance per path	2.2 Ω ±10 %
Surge protection fault message	none
Impulse durability (line-line)	C1 - 1 kV / 500 A
	C2 - 10 kV / 5 kA
	C3 - 25 A
	D1 - 1 kA
Impulse durability (line-earth)	C1 - 1 kV / 500 A
	C2 - 10 kV / 5 kA
	C3 - 100 A
	D1 - 1 kA
Impulse durability (shield-ground)	C1 - 1 kV/500 A
	C2 - 10 kV/5 kA

S-PT-EX(I)-24DC-3/4" - Surge protection device



2882585

<https://www.phoenixcontact.com/us/products/2882585>

	C3 - 100 A
	D1 - 1 kA
Alternating current carrying capacity (line-earth)	10 A - 1 s
Alternating current carrying capacity (shield-ground)	10 A - 1 s

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 2000 m (amsl)

Approvals

Conformity/Approvals

ATEX	⚡ II 1G Ex ia IIC T4...T6 Ga
IECEX	Ex ia IIC T4...T6 Ga

Standards and regulations

Air clearances and creepage distances

Standards/regulations	IEC 60664-1 / EN 60079-0 / EN 60079-11
Standards/specifications	EN 61643-21
Note	A2:2013
Standards/specifications	EN 60079-0
Note	2018
Standards/specifications	EN 60079-11
Note	2012
Standards/specifications	IEC 60079-0
Note	2017
Standards/specifications	IEC 60079-11
Note	2011

Mounting

Mounting type	direct screw connection
---------------	-------------------------

S-PT-EX(I)-24DC-3/4" - Surge protection device


2882585

https://www.phoenixcontact.com/us/products/2882585




Drawings

Dimensional drawing



Circuit diagram



Schematic diagram

S-PT-1X2-24DC*									
Category	1oo1 architecture, HFT=0				1oo2 architecture, HFT=1				
	PFD _{AVG}	PFH	Used budget of SIL 2 SIF		PFD _{AVG}	PFH	CCF	Used budget of SIL 3 SIF	
			PFD _{AVG}	PFH				PFD _{AVG}	PFH
	4.50 _{x10⁻⁶}	8.00 _{x10⁻¹⁰} 1/h	0.0 %	0.1 %	2.25 _{x10⁻⁷}	4.00 _{x10⁻¹¹} 1/h	5 %	0.0 %	0.0 %
					4.50 _{x10⁻⁷}	8.00 _{x10⁻¹¹} 1/h	10 %	0.0 %	0.1 %
Calculation based on exida report, Phoenix Contact 23/05-128 R029 V1R0 exida Profile 1, FMEDA Analysis 2, T _{proof} : 1 year, MT: 10 years, MTTR: 24 hours, PTC: 99%									
Used standards IEC/EN 61508, edition 2010 (device specific) IEC/EN 61511, edition 2016 + COR1:2016 + A1:2017 (system specific)									

Functional safety scenarios
Table also applies to the S-PT-EX(I)-24DC* item group

S-PT-EX(I)-24DC-3/4" - Surge protection device



2882585

<https://www.phoenixcontact.com/us/products/2882585>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2882585>



EAC

Approval ID: EAC-Zulassung



EAC

Approval ID: RU C-DE.*09.B.00169

Functional Safety

Approval ID: 23-05-128 R029 V1R0



ATEX

Approval ID: KEMA 06ATEX0002



IECEx

Approval ID: IECEx KEM 10.0064



CCC

Approval ID: 2020322316000817



NEPSI-EX

Approval ID: GYJ20.1178X



UKCA-EX

Approval ID: DEKRA 21UKEX0235

S-PT-EX(I)-24DC-3/4" - Surge protection device



2882585

<https://www.phoenixcontact.com/us/products/2882585>

Classifications

ECLASS

ECLASS-11.0	27130807
ECLASS-13.0	27171502

ETIM

ETIM 9.0	EC001625
----------	----------

UNSPSC

UNSPSC 21.0	39121620
-------------	----------

S-PT-EX(I)-24DC-3/4" - Surge protection device



2882585

<https://www.phoenixcontact.com/us/products/2882585>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	9fe9047c-a6e3-4d64-9c1f-a077e2ef3e21

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com