

1332646

https://www.phoenixcontact.com/us/products/1332646

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



USB PCB connectors, degree of protection: IP20, number of positions: 24, 10 Gbps, material: Metal, connection method: Solder connection

Your advantages

- · Optimized for SMD reflow soldering processes
- · Data transmission up to 10 Gbps
- · Can be processed automatically thanks to tape-on-reel packaging

Commercial data

Item number	1332646
Packing unit	500 pc
Minimum order quantity	500 pc
Sales key	AB14
Product key	ABNDAC
GTIN	4063151629953
Weight per piece (including packing)	1.19 g
Weight per piece (excluding packing)	1 g
Customs tariff number	85366930
Country of origin	CN



1332646

https://www.phoenixcontact.com/us/products/1332646

Technical data

Product properties

Product type	Data connector (device side)
Туре	USB-C
Number of positions	24
Connection profile	USB-C
Type of packaging	Tape and Reel
[W] tape width	24.00 mm
[A] coil diameter	330.00 mm
Number of slots	1
Туре	Socket
Shielded	yes
Data management status	
Article revision	00
Insulation characteristics	
Overvoltage category	
Degree of pollution	2

Electrical properties

Rated voltage (III/2)	20 V
Rated surge voltage (III/2)	1500 V
Rated current	5 A
Contact resistance	40 mΩ
Frequency range	10 Hz 55 Hz
Insulation resistance	100 ΜΩ
Transmission medium	Copper
Transmission characteristics (category)	USB 3.2 Gen 2
Transmission speed	10 Gbps
Power transmission	100 W

Connection data

Connection technology

Connection method Solder connection	Connection method	Solder connection
-------------------------------------	-------------------	-------------------

Dimensions

Width	11 mm
Height	3.16 mm
Length	6.6 mm
Orientation to	180.00 °

Material specifications



1332646

https://www.phoenixcontact.com/us/products/1332646

Color of the housing part	black
Material	Gold-plated
	Nickel coating 50 μ min
	Tin coating 100 μ min
	Nickel coating 50 μ min
	LCP
Flammability rating according to UL 94	V0
Housing material	Metal
Contact material	Copper alloy
Contact surface material	Gold over nickel
Contact carrier material	LCP

Cable/line

Test voltage Core/Core	100 V
Test voltage Core/Shield	100.00 V
Acceleration	3.1 m/s²
Halogen-free	yes

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 10000
Insertion force per signal contact	20.00 N
Extraction force per signal contact	< 8 N

Environmental and real-life conditions

Test specification

Specification	EIA 364-1000
Frequency	10-55 Hz
Sweep speed	1 octave/min
Amplitude	1.52 mm
Test duration	2.00 h
Contact resistance R ₁	40.00 mΩ

Test specification

Specification	60068-2-27
Acceleration	50.00 g
Number of shocks per direction	18.00

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-55 °C 85 °C

Mounting

Mounting type	SMD soldering



1332646

https://www.phoenixcontact.com/us/products/1332646

Processing notes

Process	SMD
Moisture Sensitive Level	MSL 1
Classification temperature T _c	260 °C
Solder cycles in the reflow	3



1332646

https://www.phoenixcontact.com/us/products/1332646

Classifications

ECLASS

UNSPSC 21.0

	ECLASS-11.0	27440390	
	ECLASS-12.0	27440390	
	ECLASS-13.0	27460201	
ETIM			
	ETIM 9.0	EC002637	
UN	SPSC		

39121400



1332646

https://www.phoenixcontact.com/us/products/1332646

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions		
China RoHS			
nvironment friendly use period (EFUP)	EFUP-E		
	No hazardous substances above the limits		
EU REACH SVHC			
REACH candidate substance (CAS No.)	No substance above 0.1 wt%		

Phoenix Contact 2024 @ - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com