

SF-7EE1N8AS000 - Panel feed-through

1605567

<https://www.phoenixcontact.com/us/products/1605567>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Panel feed-through, straight, M23, M23, number of positions: 4+3+PE, contact connection type: Socket/pin, Axial O-ring, 4xM3, shielded: yes, degree of protection: IP67, cable diameter range: 0 mm ... 0 mm, number of positions: 8, connection method: Crimp connection, series: SF, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1241924

Commercial data

Item number	1605567
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB32
Product key	ABRBFJ
Catalog page	Page 159 (C-2-2019)
GTIN	4046356253635
Weight per piece (including packing)	192.53 g
Weight per piece (excluding packing)	192.53 g
Customs tariff number	85444290
Country of origin	DE

SF-7EE1N8AS000 - Panel feed-through

1605567

<https://www.phoenixcontact.com/us/products/1605567>



Technical data

Notes

Safety note

Safety note	<p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p> <ul style="list-style-type: none">• WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.• WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.• The products are suitable for applications in plant, controller, and electrical device engineering.• When operating the connectors in outdoor applications, they must be separately protected against environmental influences.• Assembled products may not be manipulated or improperly opened.• Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).• When using the product in direct connection with third-party manufacturers, the user is responsible.• For operating voltages > 50 V AC, conductive connector housings must be grounded• Ensure that the protective or functional ground has been properly connected.• VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector• Only use tools recommended by Phoenix Contact• The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product.• Operate the connector only when it is fully plugged in and interlocked.• Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.• Observe the minimum bending radius of the cable. Lay the cable without twisting it.• The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).
-------------	---

SF-7EE1N8AS000 - Panel feed-through

1605567

<https://www.phoenixcontact.com/us/products/1605567>



Mounting

Mounting	4x M3
----------	-------

Product properties

Product type	Circular connectors (device side)
Series	SF
Application	Power
Number of positions	8
Connection profile	4+3+PE
Shielded	yes
Coding	N
Thread type	M23

Data management status

Article revision	08
------------------	----

Material specifications

Seal material	FPM
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA 6.6
Gasket and O-ring material	FPM

Electrical properties

Contact

Max. current	30 A
Nominal voltage U_N	630 V
Oversupply category	III
Degree of pollution	3
Rated surge voltage	4 kV

Contact

Max. current	9 A
Nominal voltage U_N	250 V
Oversupply category	III
Degree of pollution	3
Rated surge voltage	6 kV

Connection data

Conductor connection

Connection method	Crimp connection
Contact connection type	Socket/pin

Connector

SF-7EE1N8AS000 - Panel feed-through

1605567

<https://www.phoenixcontact.com/us/products/1605567>



Type	straight
------	----------

Connection 1

Head design	Socket
-------------	--------

Connection 2

Head design	Plug
-------------	------

Cable/line

External cable diameter	0 mm ... 0 mm
-------------------------	---------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (storage/transport)	15 °C ... 25 °C
Altitude	3000 m
Permissible humidity (storage/transport)	50 % ... 65 %

SF-7EE1N8AS000 - Panel feed-through


1605567

<https://www.phoenixcontact.com/us/products/1605567>




Drawings

Schematic diagram



Pin assignment of pin

Schematic diagram



Socket pin assignment


SF-7EE1N8AS000 - Panel feed-through



1605567


<https://www.phoenixcontact.com/us/products/1605567>

Dimensional drawing



Installation dimensions

Diagram



I = current strength, T = ambient temperature

SF-7EE1N8AS000 - Panel feed-through

1605567

<https://www.phoenixcontact.com/us/products/1605567>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1605567>

cUL Recognized	Approval ID: E153698-20041116	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
		600 V	18 A	12 - 12	-

UL Recognized	Approval ID: E153698-20041116	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
		600 V	27 A	12 - 12	-

cULus Recognized

SF-7EE1N8AS000 - Panel feed-through

1605567

<https://www.phoenixcontact.com/us/products/1605567>



Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SF-7EE1N8AS000 - Panel feed-through

1605567

<https://www.phoenixcontact.com/us/products/1605567>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	629760da-ca22-43ab-bf0d-a2d38025d6a5

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com