

# PLD M 260 W-75/95 510/D70 - LED machine light



2702485

<https://www.phoenixcontact.com/us/products/2702485>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



LED machine light, 24 V DC, emission angle (vertical/Horizontal): 75 °/95 °, length: 510 mm, diameter: 70 mm, degree of protection: IP67, can be swiveled, resistant to coolants and lubricants

## Product description

This LED machine light is designed to provide illumination inside or on machinery. You can use the light in harsh environments. This is possible thanks to the following properties: - High type of protection - Resistance to common cooling agents and lubricants - Resistance to vibrations and shock - 4 mm-thick safety glass The 70 mm diameter enables easy replacement of conventional tube lights. Mounting is by means of holders or brackets (neither of which are supplied as standard) in which the light can swivel and the lighting can therefore be optimally aligned.

## Your advantages

- Easy mechanical replacement of traditional tube lights (retrofit), thanks to 70 mm diameter
- Plug-in supply line enables free choice of the cable length as well as quick and easy installation
- Focused illumination, thanks to swivel action
- IP67 protection and resistance to cooling agents and lubricants enables use in machine tools
- Can be used at high temperatures and can be subjected to strong vibrations and shocks
- Safety glass enables use even in environments with potential mechanical strain
- ETL approval permits use on the North American market
- Particularly economical thanks to energy-efficient LED technology and an LED service life of at least 60000 h

## Commercial data

Item number	2702485
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR08
Product key	DRL222
Catalog page	Page 506 (C-6-2019)
GTIN	4055626213910
Weight per piece (including packing)	2,030 g
Weight per piece (excluding packing)	1,760 g
Customs tariff number	94054239
Country of origin	DE

# PLD M 260 W-75/95 510/D70 - LED machine light



2702485

<https://www.phoenixcontact.com/us/products/2702485>

## Technical data

### Notes

Order information:	The PLD M-ME MC/D70 mounting holder (Item No. 2702493) or the PLD M-ME MB/D70 mounting bracket (Item No. 2702494) is required in order to mount the light.
--------------------	--

### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Machine light
Application	Machine tool
Mounting position	any
Special properties	can be swiveled with mounting accessories resistant to coolants and lubricants

### Data management status

Article revision	02
------------------	----

### Electrical properties

#### Supply: Module electronics

Connection method	M12 connector (A-coded)
Number of positions	4
Permissible conductor cross section	min. 0.34 mm <sup>2</sup>
Supply voltage	24 V DC
Supply voltage range	18 V DC ... 30 V DC
Current consumption	typ. 0.75 A (at 24 V DC)
Power consumption	approx. 18 W (at 24 V DC)
Protective circuit	Surge protection; Varistor and suppressor diode, 36 V DC Reverse polarity protection; Polarity protection diode

### Connection data

Connection method	M12 connector (A-coded)
-------------------	-------------------------

### Signaling

#### Light properties

Source of light type	LED
Number of LEDs	36
Color temperature	5000 K $\pm$ 8 %
Color rendering index	85
Luminous flux	approx. 1350 lm (Net luminous flux)
Luminous efficacy	approx. 75 lm/W
Illumination	max. 662 lx (Distance of 1 m)

# PLD M 260 W-75/95 510/D70 - LED machine light



2702485

<https://www.phoenixcontact.com/us/products/2702485>

	min. 311 lx (Distance of 1 m over 1 m² area)
Average illumination	506 lx (Distance of 1 m over 1 m² area)
Emission angle	75 ° (C0-C180) 95 ° (C90-C270)
Ordinance	Delegated Regulation (EU) 2019/2015
Energy efficiency class	D (1 light source)
Note	This product contains an energy efficiency class D light source.

## Dimensions

Dimensional drawing	
Width	70 mm
Height	58 mm
Length	510 mm
Diameter	70 mm
Note on dimensions	Length without M12 flush-type connector

## Material specifications

Color	aluminum color
Material ( )	Anodized aluminum (Light housing) Single-pane safety glass (ESG, thermally toughened float glass) (Pane)

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	0 °C ... 45 °C
Degree of protection	IP67
Air pressure (operation)	69 kPa ... 102 kPa
Air pressure (storage/transport)	69 kPa ... 102 kPa
Ambient temperature (storage/transport)	-20 °C ... 75 °C
Permissible humidity (operation)	95 % (non-condensing)
Permissible humidity (storage/transport)	95 % (non-condensing)

## Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

## Mounting

Mounting type	Screw mounting
Assembly note	Mounting with mounting holders or mounting brackets, please observe the notes in the package slip.
Mounting position	any

# PLD M 260 W-75/95 510/D70 - LED machine light


2702485

<https://www.phoenixcontact.com/us/products/2702485>



## Drawings

Dimensional drawing



# PLD M 260 W-75/95 510/D70 - LED machine light



2702485

<https://www.phoenixcontact.com/us/products/2702485>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2702485>



**ETLus**

Approval ID: LV-Lighting-Systems



**cETL**

Approval ID: Luminaires



**EAC**

Approval ID: TR\_TS\_D\_12879-22

**cETLus**

# PLD M 260 W-75/95 510/D70 - LED machine light



2702485

<https://www.phoenixcontact.com/us/products/2702485>

## Classifications

### ECLASS

ECLASS-11.0	27110345
ECLASS-12.0	27110345
ECLASS-13.0	27110345

### ETIM

ETIM 9.0	EC000348
----------	----------

### UNSPSC

UNSPSC 21.0	32151500
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(a)-I, 6(c), 7(a)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	caad0e90-9ceb-4fd7-bc51-b3e49957ffca