



PPCEGG3K22CLL Datasheet

Product Name // 22 Contacts Fixed Socket 3Y Series Push Pull Connector

 [View Product Page](#)

* Representative product image only





// Product Description:	
 22 Contacts Fixed Socket 3Y Series Push Pull Connector	 Temp:-50 C to +200 C
 M24x1.0mm Thread	 Solder Terminals
 Nut Installation torque 12Nm	 Durability >4500 cycles
 Available in Straight Plug version	 Operating humidity up to 95%
 ROHS compliance	 Salt Spray Corrosion Test >144h
 IP66 rated	 High packing density for space savings on panel mounts

// General Information:	
Product Display Title:	3Y Series Fixed Socket Push Pull Connector
Product Family:	Circular Automation Connectors
Product Series:	Push Pull Connectors Y Series
Contact Pin Material:	Phosphor bronze gold plated 3u"
Coupling Nut Retention Force:	12Nm
Current Max:	5.5A
Diameter Over Coupling Ring Mm:	31mm
Durability:	>4500 cycles
Fixing Nut Material:	Nickel Plated brass
Function:	Fixed Socket Push Pull Connector
Insulator:	PPS
Ip Rating:	IP66
Max Contact Accomodation Awg:	22AWG
Max Contact Accomodation Mm2:	0.34mm2
Max Operating Temperature:	+200°C
Min Operating Temperature:	-50°C
Max Panel Thickness:	10mm
Number Of Contacts:	22 Contacts
Operating Humidity:	0.95
Panel Cut Out:	24.20mmx22.60mm
Pin Pin Terminal Voltage:	1000V
Pin Shell Terminal Voltage:	900V
Push Pull Connector Series:	3Y Series
Rohs Compliant:	Yes
Salt Spray Corrosion Test:	48h
Shielding Efficiency Min:	95dB
Shielding Efficiency Max:	80dB
Shock Resistance:	100g
Terminal Diameter:	0.7mm
Thread Size:	M24x1.0mm
Vibration Resistance Min:	10Hz
Vibration Resistance Max:	2000Hz

// Product PDF Links

 Push-Pull Connector Y Series...

// Product 3D CAD Model Links

 PPCEGG3K22CLL3D CAD Model