


PAGE 1/1	ISSUE 03-06-13	SERIES LC	PART NUMBER F727452700
----------	-----------------------	------------------	-------------------------------



Dimensions: mm [inches]

GENERAL

Type: IEC 61754-20 (LC)
Singlemode Zirconia ferrule
RJ-45 latching connector system

Ferrule inner diameter: Ø126µm

Fiber size: 9/125µm Singlemode

Cable size & type: Ø3mm Duplex

Termination: Refer to 503.08.500 assembly instruction manual

Color: GREEN

CHARACTERISTICS (Dependent on cable or fiber construction)

Optical:

- Attenuation at 1300 nm and 1550 nm
- Insertion loss (IEC 61300-3-4 method B): ≤0.15dB mean
≤0.10dB Stand.dev
- Attenuation of random mated connectors (IEC 61300-3-34): ≤0.15dB mean
≤0.12dB Stand.dev

Return-Loss: (IEC 61300-3-6): >60dB APC

Mechanical:

Vibration tests: 10 to 55 Hz , 1,5 mm (peak to peak), 2 Hr/axis
Impact test: 1,5 m drop, 8 cycles
Endurance: 200 matings
Cable retention: 68N

Environmental:

Storage temperature range: -40°C / +85°C
Operating temperature range: -40°C / +85°C
Thermal cycle test: -40°C / +75°C , 21 Cycles , 168
Humidity / Condensation cycling test: 95% RH, -10°C / +65°C, 14 cycles, 168 Hr

(Performance and specification: see document **GEN_F727 001**)