


Series
EPXB

2 cavity plug connector
Disconnect application - Rear panel mounting
With ground block

Issue:
May 13, 2013

Page
1/1



MATERIALS & FINISHES:


- SHELL: Aluminium alloy 6061 T651; Nickel plated,
- INSERTION RETENTION CLIP: beryllium copper,
- INTERMEDIATE PLATE: Brass alloy, Nickel plated,
- GROUNDING CLIP: Beryllium copper, Gold over nickel plated,
- GROUND BLOCK: High grade thermoplastic with beryllium copper retention clip,
- GROUND BLOCK RETENTION SCREW: Stainless steel,
- POLARIZATION GUIDE: Stainless steel,
- DUST CAP: Thermoplastic.

CONNECTOR SUPPLIED WITH :


- Polarization guide for A, B, C, D, E & F polarization; P/N: 617 980 037, uninstalled,
- Dust caps on each cavities,

NOTES:

- If polarization device is delivered unassembled, it must be installed with resin (Loctite 272) and torqued at 1.2 Nm on the shell.



DIMENSIONS : mm (inch are given for information only)



Estimated weight : 85 g

CREATION				
PEN:				
NOM: LEGAVE F.				
DATE: Dec 04, 03	May 13, 13	TDS Updated	Ceberio	LeGloahec
APPR.: GARCIA L.	Sept 27, 11	Guide pin was 617980020 & TDS updated	Pailot N.	LeGloahec
	Issue	Revisions	Name	Approved

EPXB2WA42NEN

RADIAL PROPRIETARY INFORMATION