

# SACC-CI-M12FSX-8CON-L90 - Contact carrier



1424180

<https://www.phoenixcontact.com/us/products/1424180>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Ethernet CAT6<sub>A</sub> (10 Gbps), 8-position, Socket, angled, M12, coding: X, PCB mounting, Wave soldering, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1237389

## Your advantages

- Reduced mounting costs thanks to two-piece device connector
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate

## Commercial data

Item number	1424180
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB23
Product key	ABQAHS
Catalog page	Page 91 (C-2-2013)
GTIN	4046356692663
Weight per piece (including packing)	6.9 g
Weight per piece (excluding packing)	6.205 g
Customs tariff number	85366990
Country of origin	DE

# SACC-CI-M12FSX-8CON-L90 - Contact carrier



1424180

<https://www.phoenixcontact.com/us/products/1424180>

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

### Product properties

Product type	Contact insert
Application	Data
Sensor type	Ethernet
Number of positions	8
Seal present	no
Shielded	yes
Coding	X
Thread type	M12

### Data management status

Article revision	03
------------------	----

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	< 3 mΩ
Insulation resistance	> 100 MΩ
Nominal voltage $U_N$	50 V AC (Data) 60 V DC
Nominal current $I_N$	0.5 A (Data)
Transmission characteristics (category)	CAT6 <sub>A</sub>

### Connection data

Connection method	Wave soldering
-------------------	----------------

### Interfaces

Signal type/category	Ethernet CAT6 <sub>A</sub> , 10 Gbps
----------------------	--------------------------------------

### Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Gold

# SACC-CI-M12FSX-8CON-L90 - Contact carrier



1424180

<https://www.phoenixcontact.com/us/products/1424180>

Contact carrier material	PA 6T/66
--------------------------	----------

## Connector

### Connection 1

Head design	Socket
Head cable outlet	angled
Head thread type	M12
Coding	X

## Cable/line

Signal type/category	Ethernet CAT6 <sub>A</sub> , 10 Gbps
----------------------	--------------------------------------

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (when plugged in)	IP67 (When plugged in)
Degree of protection	IP67 (When plugged in)
	IP67, when plugged in
Ambient temperature (operation)	-40 °C ... 105 °C (Plug / socket)
	-40 °C ... 105 °C (without mechanical actuation)
	-25 °C ... 105 °C (Cable, flexible installation)
	-40 °C ... 105 °C (cable, fixed installation)

## Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-109
Standard designation	Shock, vibration
Standards/specifications	EN 50155

## Mounting

Mounting type	PCB mounting
---------------	--------------

### Processing notes

Process	Wave soldering
---------	----------------

# SACC-CI-M12FSX-8CON-L90 - Contact carrier




1424180

<https://www.phoenixcontact.com/us/products/1424180>

## Drawings

Schematic diagram



Pin assignment M12 connector, 8-pos., view socket side

# SACC-CI-M12FSX-8CON-L90 - Contact carrier





1424180

<https://www.phoenixcontact.com/us/products/1424180>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424180>

 <b>cUL Recognized</b> Approval ID: E335024-20120308				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	60 V	0.5 A	-	-

 <b>UL Recognized</b> Approval ID: E335024-20120308				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	60 V	0.5 A	-	-

<b>cULus Recognized</b>				
-------------------------	--	--	--	--

# SACC-CI-M12FSX-8CON-L90 - Contact carrier



1424180

<https://www.phoenixcontact.com/us/products/1424180>

## Classifications

### ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27460201

### ETIM

ETIM 9.0	EC002637
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	fa4a0fc9-4b6e-4255-89bb-4c0db9e5f819