

SERIES 802 2400M / 3500 PSI Ultraminiature Subsea Connectors



802-012 or 802-030 Submersible solder cup or PC tail receptacle



Printed Circuit Board/ Solder Cup Receptacles feature low profile shells for minimum protrusion inside enclosures and integral standoffs for board washout. Contacts are non-removable.

Water Immersion, Unmated


Specify **802-012** connectors for applications where open face water immersion is not a requirement. For MIL-STD-810 Method 512G immersion requirements, specify **802-030** watertight connectors. These 802-030 connectors are specially sealed ("MOD-518") and are 100% tested to maintain a helium leak rate of 1×10^{-4} cc/second at one atmosphere pressure differential from -40C to +70C.


SUBSEA/SHALLOW WATER: AQUAMOUSE™

How To Order						
Sample Part Number	802-012	-00	Z1	9-200	P	A
Series	802-012 = Receptacle for Solder Cup or PCB Termination, with Standard Epoxy Potting 802-030 = Receptacle for Solder Cup or PCB Termination, with Special "MOD-518" Sealing for Open Face (Unmated) Water Immersion Requirements. 100% Leak Tested.					
Shell Style (See Table I)	-00 = Jam Nut for Front Panel Mounting -02 = Square Flange for Front Panel Mounting -07 = Jam Nut for Rear Panel Mounting					
Shell Material and Finish	Z1 = Stainless Steel / Passivated RoHS Compliant ZM = Stainless Steel/Electroless Nickel Plated AB = Marine Bronze/Unplated					
Shell Size - Contact Arrangement	See Contact Arrangements page 4-6 See beginning of this section for PCB footprints					
Contact Type	P = Pin, PC Tail E = Pin, Solder Cup S = Socket, PC Tail F = Socket, Solder Cup					
Shell Key Position (See Table II)	A = Normal B = Pos. B C = Pos. C D = Pos. D E = Pos. E F = Pos. F					

Table I: Shell Style		
-00 Jam Nut for Front Panel Mounting	-02 Square Flange	-07 Jam Nut for Rear Panel Mounting

Table II: Keyway Positions		
Key Position	Key Rotation	
	A°	B°
A Normal	150°	210°
B	75°	210°
C	95°	230°
D	140°	275°
E	75°	275°
F	9°	210°






SERIES 802 2400M / 3500 PSI Ultraminiature Subsea Connectors




802-012 or 802-030 (FCR)


Flange connector receptacle, front panel mount

FLANGE CONNECTOR RECEPTACLE (FCR), SOLDER CUP OR PC TAIL RECEPTACLE - SHELL STYLE 02



Dimensions					
Shell Size	A Square	B Bsc.	C Mating Threads	Ø D Tail Dia.	Ø E
5	.885 (22.48)	.500 (12.70)	.4375-28 UNEF	#23 .018/.022 (0.46/0.56)	.327 (8.31)
6	1.010 (25.65)	.625 (15.88)	.5625-20 UN		.390 (9.91)
7	1.072 (27.23)	.688 (17.48)	.6250-20 UN		.515 (13.08)
8	1.135 (28.83)	.750 (19.05)	.6875-20 UN	#20 .024/.028 (0.61/0.71)	.577 (14.66)
9	1.195 (30.35)	.812 (20.62)	.7500-20 UNEF		.640 (16.26)
10	1.260 (32.00)	.875 (22.23)	.8125-20 UNEF	#16 .060/.064 (1.52/1.63)	.702 (17.83)
12	1.323 (33.60)	.938 (23.83)	.8750-20 UNEF		.765 (19.43)
14	1.510 (38.25)	1.125 (28.58)	1.0625-20 UN	#12 .092/.096 (2.34/2.44)	.953 (24.21)
15	1.573 (39.95)	1.188 (30.18)	1.1250-20 UN		1.015 (25.78)
21	1.750 (44.45)	1.375 (34.92)	1.4375-20 UN		1.312 (33.32)






SERIES 802 2400M / 3500 PSI Ultraminiature Subsea Connectors

802-012 or 802-030

Rear panel mount, jam nut receptacle




REAR PANEL MOUNT, SOLDER CUP OR PC TAIL RECEPTACLE - SHELL STYLE 07



Dimensions					Panel Cutout	
Shell Size	Ø A Max.	B Flat ± .003	C Mating Threads	D Threads	Ø E Tail Dia.	Ø G
5	.885 (22.48)	.466 (11.84)	.4375-28 UNEF	.5000-32 UN-2A	#23 .018/.022 (0.46/0.56) #20 .024/.028 (0.61/0.71) #16 .060/.064 (1.52/1.63) #12 .092/.096 (2.34/2.44)	.477 (12.12)
6	1.010 (25.65)	.591 (15.01)	.5625-20 UN	.6250-28 UN-2A		.510 (12.95)
7	1.072 (27.23)	.653 (16.59)	.6250-20 UN	.6875-28 UN-2A		.602 (15.29)
8	1.135 (28.83)	.716 (18.19)	.6875-20 UN	.7500-28 UN-2A		.635 (16.13)
9	1.195 (30.35)	.778 (19.76)	.7500-20 UNEF	.8125-28 UN-2A		.664 (16.87)
10	1.260 (32.00)	.827 (21.01)	.8125-20 UNEF	.8750-28 UN-2A		.697 (17.70)
12	1.322 (33.58)	.890 (22.61)	.8750-20 UNEF	.9375-28 UN-2A		.727 (18.47)
14	1.510 (38.35)	1.077 (27.36)	1.0625-20 UN	1.1250-28 UN-2A		.760 (19.30)
15	1.572 (39.93)	1.140 (28.96)	1.1250-20 UN	1.1875-28 UN-2A		.789 (20.04)
21	1.940 (49.28)	1.463/1.467	1.4375-20 UN	1.500-28 UN-2A		.822 (20.88)
						.838 (21.29)
						.885 (22.48)
						.901 (22.89)
						.948 (24.08)
						1.088 (27.64)
						1.135 (28.83)
						1.151 (29.24)
						1.198 (30.43)
						1.473 (37.41)
						1.510 (38.35)

SUBSEA/SHALLOW WATER: AQUAMOUSE™






SERIES 802 2400M / 3500 PSI Ultraminiature Subsea Connectors

802-012 or 802-030

Front panel mount, jam nut receptacle



FRONT PANEL MOUNT, SOLDER CUP OR PC TAIL RECEPTACLE - SHELL STYLE 00



Dimensions							
Shell Size	$\varnothing A$ Max.	B Flat	C Mating Threads	D Threads	$\varnothing E$ Tail Dia.	F Flat	G Hex
5	.72 (18.29)	.625 (15.88)	.4375-28 UNEF-2A	.312-28 UN-2A	#23 .018/.022 (0.46/0.56) #20 .024/.028 (0.61/0.71) #16 .060/.064 (1.52/1.63) #12 .092/.096 (2.34/2.44)	.281 (7.14)	.500 (12.70)
6	.78 (19.81)	.750 (19.05)	.5625-20 UN-2A	.438-28 UN-2A		.344 (8.74)	.625 (15.88)
7	.91 (23.11)	.812 (20.62)	.6250-20 UN-2A	.500-32 UN-2A		.469 (11.91)	.688 (17.48)
8	.96 (24.38)	.875 (22.23)	.6875-20 UN-2A	.562-28 UN-2A		.531 (13.49)	.750 (19.05)
9	1.03 (26.16)	.937 (23.80)	.7500-20 UNEF-2A	.625-28 UN-2A		.594 (15.09)	.812 (20.62)
10	1.09 (27.69)	1.000 (25.40)	.8125-20 UNEF-2A	.687-28 UN-2A		.656 (16.66)	.875 (22.23)
12	1.16 (29.46)	1.062 (26.97)	.8750-20 UNEF-2A	.750-28 UN-2A		.719 (18.26)	.938 (23.83)
14	1.34 (34.04)	1.250 (31.75)	1.0625-20 UN-2A	.938-28 UN-2A		.893 (22.68)	1.125 (28.58)
15	1.41 (35.81)	1.312 (33.32)	1.1250-20 UN-2A	1.000-28 UN-2A		.955 (24.26)	1.188 (30.18)
21	1.70 (43.18)	1.562 (39.67)	1.4375-20 UN-2A	1.312-28 UN		1.257 (31.93)	1.500 (38.10)

Cutout Dimensions						
RECOMMENDED PANEL CUTOUT FOR STYLE 00 FRONT MOUNT JAM NUT	Shell Size	H Flat	$\varnothing J$	Shell Size	H Flat	$\varnothing J$
	5	.291 (7.39)	.322	10	.666 (16.92)	.697
	6	.417 (10.59)	.448	12	.729 (18.52)	.760
	7	.479 (12.17)	.510	14	.903 (22.94)	.948
	8	.541 (13.74)	.572	15	.965 (24.51)	1.010
	9	.604 (15.34)	.635	21	1.267 (32.18)	1.322
		.599 (15.21)			1.263 (32.08)	

SUBSEA SHALLOW WATER: AQUAMOUSE™



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[802-012-00Z16-7EB](#) [802-012-00Z16-7FA](#) [802-012-00Z17-10EC](#) [802-012-00Z17-10PB](#) [802-012-02Z16-7FA](#) [802-030-02Z114-12EA](#) [802-030-02Z114-12FA](#) [802-030-02Z16-6EA](#) [802-030-07ZM9-19PA](#) [802-012-07Z19-4FA](#) [802-030-02Z16-6EC](#) [802-030-07AB7-10EA](#)