

8

7

6





5

4

3

2

1

推奨モールドパネル加工寸法
PANEL CUT DIMENSIONS注)
NOTES:

1. 材質

MATERIAL

ハウジング : ポリカーボネート, UL94V-0 黒

HOUSING : POLYCARBONATE, UL94V-0, BLACK

ターミナル : リン青銅

TERMINAL : PHOSPHOR BRONZE

2. ターミナルメッキ仕様

TERMINAL PLATING

金メッキ : 0.25µm MIN. (接点部)

GOLD : 0.25µm MIN. (CONTACT AREA)

錫メッキ : 1µm MIN. (リセプタクル嵌合部)

TIN-LEAD : 1µm MIN. (RECEPTACLE CONNECTED AREA)

ニッケルメッキ : 1µm MIN. (下地メッキ)

NICKEL : 1µm MIN. (UNDER PLATING)

3. 適合リセプタクル : 52484-**10, 51090-**00

APPLICABLE RECEPTACLE : 52484-**10, 51090-**00

4. 嵌合相手 : 53717-**19

MATES WITH: 53717-**19

5. 本製品は 52968-**11 の鉛フリー品である。

THIS PRODUCT IS LEAD FREE OF 52968-**11.

12.3	21.4	10	12	24.9	9.5	33	17.5	4	52968-0619	52968-**19	6
J	H	G	F	E	D	C	B	(A)	MATERIAL NO.	MODEL NO.	CKT.

124NO. DRWN: CH'K: APPR:	123NO. DRWN: CH'K: APPR:	122NO. DRWN: CH'K: APPR:	121NO. DRWN: CH'K: APPR:	RELEASED '04/02/13 DRWN: M.NINOMIYA CH'K: K.TOJO APPR: M.SASAO	DESCRIPTION	MATERIAL 材料	GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差		SCALE 2-1	DESIGN UNITS ☒ mm ☐ INCH	 THIRD ANGLE PROJECTION	☐ mm INCH ☐ mm INCH ☒ mm ONLY	22215E ON CAD ONLY	
						SEE NOTE		10 UNDER 未満	±0.2	DRAWN BY & DATE M.NINOMIYA '04/02/13		TITLE: 2mm PITCH FLOATING CONN. REC.HS'G ASS'Y -LEAD FREE-		
						SEE NOTE		10 OVER 10 UNDER 以上 未満	±0.25	CHECKED BY & DATE K.TOJO '04/02/13				
						SEE NOTE		30 OVER 以上	±0.3	APPROVED BY & DATE M.SASAO '04/02/13		MOLEX INCORPORATED		
WIRE RANGE 適用電線範囲							ANGLE 角度		±3°	CAD FILENAME SD-52968-008.S01	MATERIAL NO. SEE CHART	DRAWING NO. SD-52968-008	SHEET NO. 1 OF 1	
INS. RANGE 被覆外径							22215E DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.							SIZE B

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.

SIZE
B