

Sealed Sensor Connector SSC System

TE Internal #: 936106-1
Yellow, PBT, -40 – 120 °C [-40 – 248 °F], Sealed Sensor Connector
SSC System, Automotive Connector Locks & Position Assurance
[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Locks & Position Assurance



Primary Product Color: **Yellow**
Primary Product Material: **PBT**
Operating Temperature Range: **-40 – 120 °C [-40 – 248 °F]**

Features

Body Features

Primary Product Color	Yellow
Primary Product Material	PBT

Usage Conditions

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	8000
Packaging Method	Bag

Other

Serviceable	Yes
-------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241)




	Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # CAT-T4827-CH8172
Timer Connector Housing




TE Part # CAT-AM705-CH8172
AMP MCP, SEALED CONNECTOR HOUSING



TE Part # 936060-1
2.8MM SLD 3P PLUG ASSY-TDC



TE Part # 2-936060-1
2.8MM SLD 3P PLUG ASSY



TE Part # 936060-2
2.8MM SLD 3P PLUG ASSY-TDC

Also in the Series | Sealed Sensor Connector SSC System



Automotive Connector Caps & Covers (2)	Automotive Connector Locks & Position Assurance(2)	Automotive Housings(126)	Automotive Terminals(3)
Connector Seals & Cavity Plugs(4)	Insertion & Extraction Tools(1)		

Customers Also Bought

TE Part #170456-2 PL 250 AM REC 12-10 0.40 X 21 PRE-TPBR	TE Part #173633-1 TAB CONT. (SIGNAL) AWG#22-24	TE Part #1897702-2 Timer Connector Housing	TE Part #368261-2 E-S MK-2(+) PLUG 2P ASSY
TE Part #2-2005344-3 MCON 13MM REC ASSY	TE Part #2371783-1 050 MCON SLD 2P PLUG ASSY CODE A	TE Part #936059-2 2.8MM SLD 2P PLUG ASSY	TE Part #2321369-6 TPA REC HSG,119POS,MCON 1.2
TE Part #2373977-2 025 14P JOINT PLUG ASSY TYPE B			

Documents



Product Drawings

2.8MM SLD 3P PLUG RETAINER YEL

English

CAD Files

Customer View Model

ENG_CVM_CVM_936106-1_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_936106-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_936106-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

2.8MM series

English