

# HC-STA-B16-HHFS-1TTP29-EL-AL - Housing

1412702

<https://www.phoenixcontact.com/us/products/1412702>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing B16, for single locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, straight, 1x Pg29, height: 76 mm, cable gland: none, Standard

## Your advantages

- Good shielding in the event of electromagnetic interference

## Commercial data

Item number	1412702
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	BF7APB
Catalog page	Page 620 (C-2-2019)
GTIN	4055626059822
Weight per piece (including packing)	234.7 g
Weight per piece (excluding packing)	226.09 g
Customs tariff number	85389099
Country of origin	PL

# HC-STA-B16-HHFS-1TTP29-EL-AL - Housing

1412702

<https://www.phoenixcontact.com/us/products/1412702>



## Technical data

### Notes

General	For contact inserts HC-B16, BB32, D40, DD72, HS6, HV6, M, K
General	also available as a powder-coated or color version: 1373013 HC-STA-B16-HHFS-1TTP29-EL/...

### Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B16
No. of cable outlets	1
Type of the screw connection	1x Pg29
Type	Tall design
Cable outlet	straight
Pg screw connection	none

### Data management status

Article revision	03
------------------	----

## Dimensions

Dimensional drawing	
Width	44 mm
Height	76 mm
Length	93.5 mm

### Internal dimensions

Length of internal thread	14 mm
---------------------------	-------

## Material specifications

Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated

## Mechanical properties

Mechanical data	
Type of the screw connection	1x Pg29
Locking type	Pin

## Environmental and real-life conditions

# HC-STA-B16-HHFS-1TTP29-EL-AL - Housing

1412702

<https://www.phoenixcontact.com/us/products/1412702>



## Ambient conditions

Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C

# HC-STA-B16-HHFS-1TTP29-EL-AL - Housing




1412702

<https://www.phoenixcontact.com/us/products/1412702>

## Drawings

Dimensional drawing



Dimensional drawing

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1412702>

**DNV**

Approval ID: TAE000037S



**cUL Recognized**

Approval ID: E255026



**UL Recognized**

Approval ID: E255026



**EAC**

Approval ID: RU C-DE.AI30.B.01102



**EAC**

Approval ID: RU C-DE.BL08.B.00511

**cULus Recognized**

## Classifications

### ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

### ETIM

ETIM 9.0	EC000437
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

1412702

<https://www.phoenixcontact.com/us/products/1412702>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)