

IPT1-1XX-XX-XX-D-DH-A-XXX

No OF POS PER ROW
-04 THRU -25

LEAD STYLE
-01

PLATING SPECIFICATION

-T: TIN (USE T-1S6-08-T-2 & T-1S6-09-T-2)
-S: SELECTIVE GOLD (USE T-1S6-08-S-2 & T-1S6-09-S-2)
-TM: MATTE TIN TAIL (USE T-1S6-08-T-2 & T-1S6-09-T-2)
-SM: SELECTIVE GOLD, MATTE TIN TAIL (USE T-1S6-08-S-2 & T-1S6-09-S-2)
-L: LIGHT SELECTIVE GOLD, MATTE TIN TAIL (USE T-1S6-08-L-2 & T-1S6-09-L-2)

OPTIONS

-POL: POSITION #1 REMOVED (USE IPT1-XX-DH-P)
-TR: TAPE AND REEL PACKAGING

ALIGNMENT PINS





TAIL OPTION

-DH: DOUBLE HORIZONTAL

ROW SPECIFICATION

-D: DOUBLE (USE IPT1-XX-DH-A)

DO NOT
SCALE FROM
THIS PRINT



NOTES:


1. C1 REPRESENTS A CRITICAL DIMENSION.
2. NOTE DELETED
3. MINIMUM TERMINAL PUSH OUT FORCE: 2 lbs.
4. MAXIMUM VARIATION BETWEEN PIN ROWS: .005[.13].
5. NOTE DELETED
6. ALL DIMENSIONS TO BE ABOUT CENTERLINE WITHIN +/- .005[.13].
7. NOTE DELETED.
8. PINS TO BE FLUSH TO .010[0.25] BELOW TOP OF SHROUD.
9. SHEAR TAILS TO DIMENSION SHOWN.

FIG. 1

IPT1-110-01-XX-D-DH-A SHOWN

SECTION "A"- "A"

-POL: POLARIZED OPTION
IPT1-110-01-X-D-DH-A-POL SHOWN



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES.
TOLERANCES ARE:
DECIMALS .XX: ± .01[.3]
.XXX: ± .005[.13]
.XXXX: ± .0020[.051]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING
INSULATOR: VECTRA E130i, COLOR: BLACK
TERMINAL: PHOS BRONZE, 510, 3/4 HARD

SHEET SCALE: 2.25:1

SAMTEC


520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812.944.6733 FAX: 812.948.5047
e-Mail: INFO@SAMTEC.COM CODE: 55322

DESCRIPTION:
.100 DOUBLE ROW, HORIZONTAL SHROUDED TERMINAL ASSM


DWG. NO.
IPT1-1XX-XX-XX-D-DH-A-XXX

BY: BRATCHER 11/15/02 SHEET 1 OF 2


IN-PROCESS 1



IN-PROCESS 2



IN-PROCESS 3



IN-PROCESS 4







FIG. 2

-DH: SURFACE MOUNT DIAGRAM

PACKAGING VIEW

(PARTS TO HAVE POSITION #1 LOADED IN
SAME DIRECTION AS ARROW ON TUBE)



TUBE: PT-1-24-15-29
PLUG: TP-07

F:\ DWG\ MISC\ Mktg\ IPT1-1XX-XX-XX-D-DH-A-XXX-MKT.SLDDRW

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2.5:1

SAMTEC

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812.944.6733 FAX: 812.948.5047
e-Mail: INFO@SAMTEC.COM CODE: 55322

DESCRIPTION:
.100 DOUBLE ROW, HORIZONTAL SHROUDED TERMINAL ASSM

DWG. NO.
IPT1-1XX-XX-XX-D-DH-A-XXX

BY: BRATCHER 11/15/02 SHEET 2 OF 2