




Terminals & Splices > Automotive Terminals > TIMER, RECEPTACLE AND TAB



Terminal Type: **Tab**
Mating Tab Width: **2.8 mm [.11 in]**
Mating Tab Thickness: **.8 mm [.031 in]**
Terminal Transmits: **25 – 40 A (Power)**
Wire Size: **22 AWG**

[All TIMER, RECEPTACLE AND TAB \(323\)](#)

Features

Product Type Features

Sealable	Yes
Primary Locking Feature	Locking Lance

Body Features

Terminal Seal Type	Single Wire Seal (SWS)
--------------------	------------------------

Contact Features

Contact Size	2.8mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Typical Current Rating	30 A
Crimp Type	F-Crimp
Terminal Type	Tab
Mating Tab Width	2.8 mm[.11 in]



Mating Tab Thickness	.8 mm[.031 in]
Interface Plating	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Compatible Insulation Diameter Range	3.4 mm[.134 in]
Wire Size	.35 mm²
Wire Size Search	22 AWG
Tab Length	25 mm[.984 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	130 °C[266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Operation/Application

Conforms to KOMAX Automatic Component Insertion Guideline	Yes, per Version 5.0 (March 2018)
Compatible With Wire Base Material	Copper

Packaging Features

Packaging Quantity	3500
Packaging Method	Reel

Other

Terminal Transmits	25 – 40 A (Power)
--------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC




Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-T4827-CH8172 Timer Connector Housing	 TE Part # 963292-1 WIRE SEALING 2,2	 TE Part # 2151193-1 OCEAN_2.0_APPLICATOR-S-062F155O-RSM	 TE Part # 2151193-2 OCEAN_2.0_APPLICATOR-S-062F155O-RSA
 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 5-2151193-1 OCEAN_2.0_APPLICATOR-S-062F155O-RSM	 TE Part # 5-2151193-2 OCEAN_2.0_APPLICATOR-S-062F155O-RSA	 TE Part # 7-2151193-7 OCEAN_2.0_SPARE_PART_KIT-062F155O

Also in the Series | Junior Power Timer

 Automotive Connector Caps & Covers (9)	 Automotive Connector Locks & Position Assurance (8)	 Automotive Housings (319)	 Automotive Terminals (189)
---	---	--	---



Busbars & Terminals(1)



Connector Seals & Cavity Plugs(9)



Insertion & Extraction Tools(8)



Module Components(1)



Other Automotive Connector Accessories(2)




Special Purpose Terminals(2)

Also in the Series | Timer Connector System



Automotive Connector Caps & Covers (14)



Automotive Connector Locks & Position Assurance(15)



Automotive Housings(215)



Automotive Terminals(135)



Connector Seals & Cavity Plugs(36)



Crimp Terminal Housings(13)




Insertion & Extraction Tools(18)



Other Automotive Connector Accessories(1)




PCB Headers & Receptacles(40)



Quick Disconnects(4)



Customers Also Bought



TE Part #160916-3
250 FASTON,REC.,17-14 AWG,PB



TE Part #962942-2
TIMER, RECEPTACLE AND TAB



TE Part #1394139-1
8POS MQS REC



TE Part #1564984-3
AMP MCP 2.8K, CONTACT, SWS



TE Part #5-1241608-1
MQS1,5 Sn rec CB unseal. 0,75-1,5



TE Part #1-1801155-5
COVER FOR 2W HP CONNECTOR



TE Part #1-969489-2
6POS MQS REC COD A



TE Part #1801176-5
2W RECEPTACLE HP SL CONNECTOR GREEN



TE Part #708412-2
XCT 25-8 EQ

Documents

Product Drawings

TAB A 2.8x0.8 CONTACT CF SWS Sn

English

TAB A 2.8x0.8 CONTACT CF SWS Sn

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-2141876-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-2141876-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-2141876-1_A.3d_stp.zip



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

German

Application Specification

English

Application Specification

English