

RC-17P1N8D0000 - Contact insert



1601634

<https://www.phoenixcontact.com/us/products/1601634>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M23, number of positions: 17, contact connection type: Pin, Crimp connection, series: NC, RC, RM, TU, UC, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1241379

Commercial data

Item number	1601634
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAFU
GTIN	4046356235808
Weight per piece (including packing)	10.6 g
Weight per piece (excluding packing)	5.45 g
Customs tariff number	85389099
Country of origin	DE

RC-17P1N8D0000 - Contact insert



1601634

<https://www.phoenixcontact.com/us/products/1601634>

Technical data

Notes

Assembly note	Integrated contacts: 12 x 1597862 and 5 x 1602996
---------------	---

Product properties

Product type	Contact insert
Series	NC
	RC
	RM
	TU
	UC
Application	Signal
Number of positions	17
Connection profile	17
Coding	N
Thread type	M23

Data management status

Article revision	04
------------------	----

Electrical properties

Contact

Contact diameter	1 mm
Min. cross section	0.14 mm ²
Max. cross section	0.56 mm ²
Max. current	8 A
Nominal voltage U _N	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Connection method	Crimp connection
-------------------	------------------

Material specifications

Insulator material	PA66
Contact material	CuZn
Contact surface	Nickel-plated, gold coating

Connector

Direction of rotation	Standard
-----------------------	----------

Mechanical properties

RC-17P1N8D0000 - Contact insert



1601634

<https://www.phoenixcontact.com/us/products/1601634>

Mechanical data

Insertion/withdrawal cycles	50
-----------------------------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (storage/transport)	15 °C ... 25 °C
Permissible humidity (storage/transport)	50 % ... 65 %

RC-17P1N8D0000 - Contact insert




1601634

<https://www.phoenixcontact.com/us/products/1601634>

Drawings

Schematic diagram



Connector pin assignment


RC-17P1N8D0000 - Contact insert



1601634

<https://www.phoenixcontact.com/us/products/1601634>

Schematic diagram



Dimensional drawing

RC-17P1N8D0000 - Contact insert



1601634

<https://www.phoenixcontact.com/us/products/1601634>

Classifications

ECLASS

ECLASS-11.0	27440223
ECLASS-12.0	27440223
ECLASS-13.0	27440223

ETIM

ETIM 9.0	EC003557
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-17P1N8D0000 - Contact insert



1601634
<https://www.phoenixcontact.com/us/products/1601634>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b4124d8a-7120-41cf-a038-6e5a49c7c229

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com