



Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Cover**

Cable Exit Angle: **180°**

Strain Relief: **With**

Primary Product Color: **Brown**

Primary Product Material: **PBT GF**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover
---	-------

Configuration Features

Number of Positions	16
---------------------	----

Body Features

Cable Exit Angle	180°
Primary Product Color	Brown
Primary Product Material	PBT GF

Mechanical Attachment

Strain Relief	With
---------------	------

Dimensions

Compatible Cable Bundle Diameter Range	8 mm[.314 in]
--	---------------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features



Packaging Method	Package
Other	
Serviceable	Yes

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts













TE Part # 1534101-1
16POS MQS REC



TE Part # 966870-1
MOD2 ST-WANNE 2X 8P

Customers Also Bought



 <p>TE Part #175268-1 070 REC (S) FOR NSCC</p>	 <p>TE Part #1-1534093-1 MQS COVER 2X6 POS</p>	 <p>TE Part #2294463-1 MCON 1.2 CB TAB MONO</p>	 <p>TE Part #2298002-1 SECONDARY LOCK, MQS/MCON1.2, DTB 50P</p>
 <p>TE Part #2298567-1 22POSN.,REC ASSY, MCON1.2, MQS, MCP2.8</p>	 <p>TE Part #2411042-1 TAB0.64X0.64,TERMINAL,025 TAB CONTACT</p>	 <p>TE Part #1-1534121-1 MQS ABDECKKAP6P,SW</p>	 <p>TE Part #2050986-1 REM0.64 Terminal</p>
 <p>TE Part #1813018-6 MINI FUSE RECEPTACLE</p>	 <p>TE Part #2219008-3 025HYB 56P COVER ASSY GRY</p>		

Documents

Product Drawings

MQS COVER 2X8P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1534097-1_A_c-1-1534097-1-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1534097-1_A_c-1-1534097-1-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1534097-1_A_c-1-1534097-1-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English