



KISSLING PUSH BUTTON SWITCH

Series TS - from TE Connectivity (TE)

Quality Switch

Our push button switches are designed and manufactured to the highest quality standards. The switches are available as 1-pole and 2-pole versions with change-over function. These switch types are suited for various mounting conditions and meet your individual requirements. The push button itself is available in various colors, with different symbols on the actuator and also as an illuminated version.

The push button switch is characterized by its IP6K9K sealing rating and its high shock and vibration resistance. It is highly suitable for performance under demanding environmental conditions.

Features


- Central thread & flange mounting options
- DIN Connector, solder pins, or flying lead electrical connection options
- Various actuator colors available both with or without function symbols
- Indicator light option (integrated LED)

Applications


- Commercial vehicles
- Plant and industrial engineering
- System start/stop applications
- Remote control panels

Actuator Symbol

Without print



Battery



Start



Stop



Lamp



Motor



other types and special types upon request

KISSLING PUSH BUTTON SWITCH


Series TS

Specification

Technical Data


Temperature range	-40°C to +90°C
Thread sizes / Torque	M30 = max. 5Nm M6 = max 7Nm
Pre-travel	1.5 ± 0.5mm
Contact travel	2.5 ± 0.5mm
Operating force	max. 40N
Mechanical life	100.000 cycles
Frequency	max. 100/min
Voltage range	9VDC - 32VDC
Resistive load	10mA - 5A

Ordering Information




Circuits


Indicator Light



Change-over 1-pole




Change-over 2-pole



Series TS

Housing Socket



Solder connection

Cable connection



Page 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

[TS-111-GN32](#) [TS-211-GN11](#) [TS-211-GN12](#) [TS-211-GN31](#) [TS-211-RT11](#) [TS-211-SW11](#) [TS-221-GE11](#) [TS-221-RT41](#) [TS-221-SW11](#)