




NOTES.

- 1

材料及び仕上げ(めっき仕様) : TABLE 1 参照
MATERIAL AND FINISHES : SEE TABLE 1
- 2

製品仕様書 : PS-501646-001
PRODUCT SPECIFICATION:PS-501646-001
- 3

嵌合相手:
MATES WITH:
- | | | |
|-----------------------------------|---|---------------|
| リセプタクルハウジング
RECEPTACLE HOUSING | 501646 SERIES | |
| 圧着端子
RECEPTACLE CRIMP TERMINAL | AWG #22-26 錫めっき
AWG #22-26 TIN PLATING | 501647 SERIES |
| | AWG #26-28 錫めっき
AWG #26-28 TIN PLATING | 501648 SERIES |
- 4

アプリケーション仕様書(コネクタ取扱い説明書) : 5016460000 PS A01
APPLICATION SPECIFICATION(CONNECTOR MANNUAL): 5016460000 PS A01
- 5

本製品は錫めっき品です。
THIS PRODUCT IS A TIN PLATING.
- 6

極数/2 = 偶数に適応
APPLY FOR CIRCUIT SIZE / 2 =EVEN
- 7

ターミナルに錫めっきを使用している為、外観に摺動痕が付く場合があります。
THE WOUND OF FRICTION MIGHT ADHERE TO EXTERNALS
BECAUSE THE TIN PLATING IS USED FOR TERMINAL.
- 8



梱包仕様書: SPK-501645-001
PACKING INFORMATION : SPK-501645-001
- 9

発注番号 : SHEET 3 参照
ORDER No. : PLEASE REFER TO SHEET 3 FOR PRODUCT LIST


501645 **2*

極数
CIRCUIT SIZE

ハウジングカラー HOUSING COLOR
0:ナチュラル NATURAL (白 WHITE)
1:黒 BLACK
2:赤 RED
4:青 BLUE
6:緑 GREEN



基板取付穴推奨寸法(マウント面)
POLARIZED RECOMMENDED PCB LAYOUT HOLE DIMENSION (MOUNTING SIDE)
参考基板厚 t=1.2~1.6
REFERENCE PCB THICKNESS t=1.2~1.6

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex						
mm		NTS											
GENERAL TOLERANCES (UNLESS SPECIFIED)				IGRID 2.0 PLUG ASSEMBLY VERTICAL TIN PLATING									
ANGULAR TOL ± 3.0 °													
4 PLACES		± 0.2		EC NO: 755147			PRODUCT CUSTOMER DRAWING						
3 PLACES		± 0.2		DRWN: SNAKAMURA08 2023/06/27									
2 PLACES		± 0.2		CHK'D: MARAI 2023/07/07									
1 PLACE		± 0.2		APPR: AIDA 2023/07/07			DOCUMENT NUMBER						
0 PLACES		± 0.2		INITIAL REVISION:						5016450000-SD			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				DRWN: SNAKAMURA08 2019/05/09			DOC TYPE		DOC PART				REVISION
				APPR: KOMURAKAMI 2019/05/24			PSD		000		F		
THIRD ANGLE PROJECTION				DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				A3-SIZE		501645		SEE SHEET 3		GENERAL		2 OF 3	

10

9

8

7

6

5

4

3

2

1

F

E

D


C

B


A

製品形状
PRODUCT SHAPE

10, 12極
10, 12CIRCUIT



14 - 40 極
14 - 40 CIRCUIT



△₉ 製品一覧 PRODUCT LIST

緑: GREEN	青: BULE	赤: RED	黒 : BLACK	ナチュラル : NATURAL (白 : WHITE)	HOUSING COLOR
501645 4026	501645 4024	501645 4022	501645 4021	501645 4020	40
↑3826	↑3824	↑3822	↑3821	↑3820	38
3626	3624	3622	3621	3620	36
3426	3424	3422	3421	3420	34
3226	3224	3222	3221	3220	32
3026	3024	3022	3021	3020	30
2826	2824	2822	2821	2820	28
2626	2624	2622	2621	2620	26
2426	2424	2422	2421	2420	24
2226	2224	2222	2221	2220	22
2026	2024	2022	2021	2020	20
1826	1824	1822	1821	1820	18
1626	1624	1622	1621	1620	16
↓1426	↓1424	↓1422	↓1421	↓1420	14
1226	1224	1222	1221	1220	12
501645 1026	501645 1024	501645 1022	501645 1021	501645 1020	10

発注番号 ORDER No.
PACKAGING STYLE : TRAY

極数
CIRCUIT SIZE

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
DIMENSION UNITS mm	SCALE NTS
GENERAL TOLERANCES (UNLESS SPECIFIED)	
ANGULAR TOL	± 3.0 °
4 PLACES	± 0.2
3 PLACES	± 0.2
2 PLACES	± 0.2
1 PLACE	± 0.2
0 PLACES	± 0.2
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
		A3-SIZE	501645	SEE CHART	GENERAL	3 OF 3

CURRENT REV DESC:		molex	
IGRID 2.0 PLUG ASSEMBLY VERTICAL TIN PLATING		PRODUCT CUSTOMER DRAWING	
EC NO: 755147 DRWN: SNAKAMURA08 CHK'D: MARAI APPR: AIDA		DOCUMENT NUMBER 5016450000-SD	
INITIAL REVISION: DRWN: SNAKAMURA08 APPR: KOMURAKAMI		DOC TYPE PSD	
2023/06/27 2023/07/07 2023/07/07		DOC PART 000	
2019/05/09 2019/05/24		REVISION F	

DOCUMENT STATUS

P1

RELEASE DATE

2023/07/07

04:35:51

9

8

7

6

5

4

3

2

1