

DESCRIPTION: 2MM RECEPTACLES - DUAL ROW - SMT






UNITS = INCHES [MM]

MATERIAL:

HOUSING: NYLON 6T, UL 94V-0, BLACK
CONTACT: PHOSPHOR BRONZE
PLATING: GOLD FLASH ENTIRE CONTACT

ELECTRICAL:

CURRENT RATING: 2 AMPS
CONTACT RESISTANCE: 20mOHMS Max.
INSULATOR RESISTANCE: 5,000MOHMS Min.
DIELECTRIC WITHSTANDING: 500VAC
OPERATING TEMPERATURE: -40° TO +105° C
PROCESS TEMPERATURE: 260° C FOR 10 SECONDS



PCB LAYOUT

RoHS COMPLIANT

2864 YY 06 R P2

SERIES _____
2864 = DUAL ROW
POSITIONS _____
DUAL - INCREMENTS OF 2
(6 TO 80)
TYPE _____
06 = SURFACE MOUNT
RoHS COMPLIANT _____
HIGH TEMP.
PLATING _____
P2 = GOLD FLASH

GENERAL TOLERANCE = ± 0.008 [± 0.20]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

NorComp

DRAWN: J. KADEL		DATE: 03/05/2019	
SCALE: NTS	SHEET 1	OF 1	REV 0
DWG NO. 2864YY06RP2			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[28640806RP2](#) [28641206RP2](#) [28641606RP2](#) [28642006RP2](#) [28642406RP2](#) [28642606RP2](#) [28643006RP2](#)