

Standard Recovery Diodes, 400 A



TO-244

FEATURES

- Standard rectifier
- Popular series for rough service
- Cathode and anode to base available
- UL approved file E222165
- Designed and qualified for industrial level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

TYPICAL APPLICATIONS

- Welders
- Power supplies
- Motor controls
- Battery chargers
- General industrial current rectification

PRIMARY CHARACTERISTICS

$I_{F(AV)}$ per module	400 A
Type	Modules - diode, high voltage
Package	TO-244
Circuit configuration	Two diodes common anode, two diodes common cathode

MAJOR RATINGS AND CHARACTERISTICS

SYMBOL	CHARACTERISTICS	VALUES	UNITS
$I_{F(AV)}$		400	A
	T_C	133	°C
$I_{F(RMS)}$		628	A
I_{FSM}	50 Hz	2500	
	60 Hz	2620	
I^2t	50 Hz	31	kA ² s
	60 Hz	28	
$I^2\sqrt{t}$		312	kA ² √s
V_{RRM}		600	V
T_{Stg}, T_J		-40 to +175	°C

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS

TYPE NUMBER	VOLTAGE CODE	V_{RRM} : MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V_{RSM} : MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I_{RRM} MAXIMUM AT $T_J = 175$ °C mA
VS-VSMD400.W60	60	600	700	12



FORWARD CONDUCTION					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum average forward current at case temperature per leg	$I_{F(AV)}$	180° conduction, half sine wave, 133 °C		200	A
Maximum RMS forward current per leg	$I_{F(RMS)}$	DC at 137 °C case temperature		314	A
Maximum peak, one-cycle forward, non-repetitive surge current per leg	I_{FSM}	t = 10 ms	No voltage reapplied	2500	
		t = 8.3 ms	No voltage reapplied	2620	
		t = 10 ms	100 % V_{RRM} reapplied	2100	
		t = 8.3 ms	100 % V_{RRM} reapplied	2200	
Maximum I^2t for fusing per leg	I^2t	t = 10 ms	No voltage reapplied	32	kA ² s
		t = 8.3 ms	No voltage reapplied	29	
		t = 10 ms	100 % V_{RRM} reapplied	22	
		t = 8.3 ms	100 % V_{RRM} reapplied	20	
Maximum $I^2\sqrt{t}$ for fusing per leg	$I^2\sqrt{t}$	t = 0.1 ms to 10 ms, no voltage reapplied		311	kA ² √s
Low level value of threshold voltage per leg	$V_{F(TO)1}$	$(16.7 \% \times \pi \times I_{F(AV)} < I < \pi \times I_{F(AV)})$, $T_J = T_J$ maximum		0.73	V
High level value of threshold voltage per leg	$V_{F(TO)2}$	$(I > \pi \times I_{F(AV)})$, $T_J = T_J$ maximum		0.85	
Low level value of forward slope resistance per leg	r_{f1}	$(16.7 \% \times \pi \times I_{F(AV)} < I < \pi \times I_{F(AV)})$, $T_J = T_J$ maximum		1.52	mΩ
High level value of forward slope resistance per leg	r_{f2}	$(I > \pi \times I_{F(AV)})$, $T_J = T_J$ maximum		1.36	
Maximum forward voltage drop per leg	V_{FM}	$I_{FM} = 200$ A, $T_J = 25$ °C, $t_p = 400$ μs square wave		1.31	V

BLOCKING					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum peak reverse leakage current per leg	I_{RRM}	$T_J = 175$ °C		12	mA
		$T_J = 25$ °C		200	μA

THERMAL AND MECHANICAL SPECIFICATIONS					
PARAMETER	SYMBOL	VALUES			UNITS
		MIN.	TYP.	MAX.	
Thermal resistance, junction to case per leg per module	R_{thJC}	-	-	0.10	°C/W
		-	-	0.05	
Thermal resistance, case to heatsink per module	R_{thCS}	-	0.10	-	
Weight		-	68	-	g
		-	2.4	-	oz.
Mounting torque		30 (3.4)	-	40 (4.6)	lbf · in (N · m)
Mounting torque center hole		12 (1.4)	-	18 (2.1)	
Terminal torque		30 (3.4)	-	40 (4.6)	
Vertical pull		-	-	80	lbf · in
2" lever pull		-	-	35	
Case style		TO-244			

ΔR CONDUCTION PER JUNCTION											
DEVICES	SINE HALF WAVE CONDUCTION					RECTANGULAR WAVE CONDUCTION					UNITS
	180°	120°	90°	60°	30°	180°	120°	90°	60°	30°	
VSMD400.W60	0.041	0.047	0.060	0.084	0.131	0.029	0.049	0.064	0.087	0.132	°C/W

Note

- Table shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics Per Leg




Fig. 3 - Maximum Non-Repetitive Surge Current Per Leg




Fig. 2 - Current Ratings Characteristics Per Leg




Fig. 4 - Maximum Non-Repetitive Surge Current Per Leg





Fig. 5 - Forward Power Loss Characteristics






Fig. 6 - Forward Power Loss Characteristics




Fig. 7 - Forward Voltage Drop Characteristics Per Leg




Fig. 8 - Thermal Impedance Z_{thJC} Characteristics Per Leg



ORDERING INFORMATION TABLE

Device code	VS-VS	MD	400	C	W	60
	①	②	③	④	⑤	⑥

- 1** - Vishay Semiconductors product
- 2** - MD = standard recovery diode
- 3** - Current rating (400 = 400 A)
- 4** - Circuit configuration:
 - C = two diodes common cathode
 - A = two diodes common anode
- 5** - Type of device:
 - W = TO-244 not isolated
- 6** - Voltage rating (60 = 600 V)

CIRCUIT CONFIGURATION		
CIRCUIT DESCRIPTION	CIRCUIT CONFIGURATION CODE	CIRCUIT DRAWING
Two diodes common anode	A	
Two diodes common cathode	C	

LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95021



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.