

SACC-M12MS-5CON-PG11-DUO VA - Connector



1403371

<https://www.phoenixcontact.com/us/products/1403371>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, 5-position, Plug straight M12, coding: A, Screw connection, knurl material: Stainless steel 1.4404, cable gland Pg11-DUO, external cable diameter 2.1 mm ... 3 mm / 4 mm ... 5.2 mm

Your advantages

- Safe use in the field, thanks to a high degree of protection
- Screw connection: proven connection technology for a large selection of different conductors
- Save space: connect two sensors to one connector with a multiple grommet

Commercial data

| | |
|--------------------------------------|--------------------|
| Item number | 1403371 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF30 |
| Product key | BF2CAA |
| Catalog page | Page 25 (C-2-2019) |
| GTIN | 4046356649384 |
| Weight per piece (including packing) | 30.58 g |
| Weight per piece (excluding packing) | 28.5 g |
| Customs tariff number | 85366990 |
| Country of origin | HU |

Technical data

Notes

| | |
|---------------|---|
| Assembly note | NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties. |
|---------------|---|

Mounting

| | |
|---------------|--|
| Assembly note | This connector includes one seal for small and one seal for large outer cable diameters. |
|---------------|--|


Product properties

| | |
|----------------------|---------------------------------|
| Product type | Circular connector (cable-side) |
| Number of positions | 5 |
| No. of cable outlets | 2 |
| Shielded | no |
| Coding | A |
| Cable outlet | straight |
| Pg screw connection | Pg11 |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Length | 63 mm |

External dimensions

| | |
|------------------|--|
| Outside diameter | 2x 2.1 mm ... 3 mm (when using the seal for small outer cable diameters) |
| | 2x 4 mm ... 5.2 mm (when using the seal for large outer cable diameters) |

Housing

| | |
|------------------|-------|
| Diameter housing | 20 mm |
|------------------|-------|

Material specifications

| | |
|-----------------------|-----|
| Seal material | NBR |
| Material of grip body | PA |

SACC-M12MS-5CON-PG11-DUO VA - Connector

1403371

<https://www.phoenixcontact.com/us/products/1403371>



| | |
|-------------------------------|------------------------|
| Contact material | CuZn |
| Contact surface material | Au |
| Contact carrier material | PA |
| Material for screw connection | Stainless steel 1.4404 |

Connection data

Conductor connection

| | |
|---|---|
| Connection method | Screw connection |
| Connection cross section | 0.25 mm ² ... 0.75 mm ² (without ferrule) |
| | 0.14 mm ² ... 0.75 mm ² (with ferrule) |
| | 0.25 mm ² ... 0.75 mm ² (solid) |
| Connection cross section AWG | 24 ... 18 (without ferrule) 26 ... 20 (with ferrule) |
| Stripping length of the individual wire | 5 mm |
| Tightening torque | 0.4 Nm (M12 knurl) |
| | 0.8 Nm ... 1 Nm |
| | 0.2 Nm (Screw terminal blocks) |

Electrical properties

| | |
|--------------------------------|--------------------|
| Rated surge voltage | 1.5 kV |
| Contact resistance | ≤ 8 mΩ |
| Insulation resistance | ≥ 100 MΩ |
| Nominal voltage U _N | 48 V AC 60 V DC |
| Nominal current I _N | 4 A |

Connector

Connection 1

| | |
|-------------------|----------|
| Head design | Plug |
| Head cable outlet | straight |
| Head thread type | M12 |
| Coding | A |

Cable/line

| | |
|---|------|
| Stripping length of the individual wire | 5 mm |
|---|------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|----------------------------------|
| Degree of protection | IP67 |
| Ambient temperature (operation) | -40 °C ... 85 °C (Plug / socket) |

Standards and regulations

M12

SACC-M12MS-5CON-PG11-DUO VA - Connector

1403371

<https://www.phoenixcontact.com/us/products/1403371>



| | |
|--------------------------|-----------------|
| Standard designation | M12 connector |
| Standards/specifications | IEC 61076-2-101 |

SACC-M12MS-5CON-PG11-DUO VA - Connector


1403371

<https://www.phoenixcontact.com/us/products/1403371>



Drawings

Dimensional drawing



Plug, M12 x 1, straight


SACC-M12MS-5CON-PG11-DUO VA - Connector

1403371

<https://www.phoenixcontact.com/us/products/1403371>




Schematic diagram



Cable connection side M12 (screw connection)

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27440102 |
| ECLASS-12.0 | 27440116 |
| ECLASS-13.0 | 27440116 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|---|---------|
| Environment friendly use period (EFUP) | EFUP-50 |
| An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. | |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 1e79aff6-513b-4f7d-a227-65f91f8dfd1a |

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com