

SUBCON-PLUS-PROFIB/90/M12 - D-SUB bus connector



2902318

<https://www.phoenixcontact.com/us/products/2902318>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB plug, 9-pos., pin, assignment: 3, 5, 6, 8; two 90° M12 cable glands (B-coded). Bus system: PROFIBUS DP up to 12 Mbps. Termination resistor via separate M12 terminator.



Product description

The SUBCON-PLUS fast connectors with M12 connection ensure error-free installation of bus systems, thanks to the use of fully-tested components such as cables and connectors. The innovative housing concept is lightweight yet offers optimum mechanical protection against environmental influences. This means that the fast connection plugs are ideal, even in applications subject to vibration. The unique SPEEDCON fast locking system on the M12 connections offers reliable connection with just half a turn.

Your advantages

- Easy startup, plug and play
- Error-free installation, particularly in standard machine production
- Quick connection thanks to M12-SPEEDCON fast locking system
- Low weight
- PROFIBUS
- Termination using M12 termination resistor
- Adapter between IP20 and IP67 environments
- Through-contacted shielding from M12 to D-SUB

Commercial data

Item number	2902318
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN10
Product key	DNC531
Catalog page	Page 445 (C-6-2019)
GTIN	4046356654975
Weight per piece (including packing)	66.4 g
Weight per piece (excluding packing)	41 g
Customs tariff number	85366990
Country of origin	CN

SUBCON-PLUS-PROFIB/90/M12 - D-SUB bus connector



2902318

<https://www.phoenixcontact.com/us/products/2902318>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Data plug
MTTF	6706 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	1817 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)
	155 Years (SN 29500 standard, temperature 40°C, operating cycle 100%)
Pin assignment	3, 5, 6, 8

Data management status

Article revision	03
------------------	----

Electrical properties

Nominal voltage U_N	5 V
Nominal current I_N	100 mA

Connection data

Tightening torque	... 0.4 Nm
-------------------	------------

D-SUB connection

Connection method	D-SUB connector
-------------------	-----------------

M12 connector

Connection method	M12 male, B-coded
-------------------	-------------------

M12 connector


Connection method	M12 female, B-coded
-------------------	---------------------

Interfaces

Bus system	PROFIBUS DP
Signal	PROFIBUS

Dimensions

Dimensional drawing



Technical drawing of a mechanical part, showing dimensions in millimeters. The part is a T-shaped component with a central vertical section and two horizontal sections extending from the top and bottom. The dimensions are as follows:

- Overall width: 71 mm
- Overall height: 45 mm
- Top horizontal section width: 38 mm
- Bottom horizontal section width: 38 mm
- Central vertical section height: 35 mm
- Central vertical section width: 30 mm

SUBCON-PLUS-PROFIB/90/M12 - D-SUB bus connector



2902318

<https://www.phoenixcontact.com/us/products/2902318>

Width	16 mm
Height	40 mm
Length	71 mm

Material specifications

Material (Housing)	Polyamide
--------------------	-----------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP40
Ambient temperature (operation)	-30 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-20 °C ... 80 °C
Altitude	≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

Standards and regulations

Free from substances that could impair the application of coating	VDMA 24364:2018-05
---	--------------------

SUBCON-PLUS-PROFIB/90/M12 - D-SUB bus connector




2902318

<https://www.phoenixcontact.com/us/products/2902318>


Drawings

Block diagram



SUBCON-PLUS-PROFIB/...M12 function block diagram

Dimensional drawing



SUBCON-PLUS...90...M12 dimensional drawing, short 90° version


SUBCON-PLUS-PROFIB/90/M12 - D-SUB bus connector



2902318

<https://www.phoenixcontact.com/us/products/2902318>

Schematic diagram



Function elements

1 = D-SUB 9

2 = Outgoing M12 connection

3 = Incoming M12 connection

4 = D-SUB PG connection (depending on the version)

SUBCON-PLUS-PROFIB/90/M12 - D-SUB bus connector




2902318
<https://www.phoenixcontact.com/us/products/2902318>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2902318>



cUL Recognized
Approval ID: E238705



UL Recognized
Approval ID: E238705

cULus Recognized

SUBCON-PLUS-PROFIB/90/M12 - D-SUB bus connector



2902318
<https://www.phoenixcontact.com/us/products/2902318>

Classifications

ECLASS

ECLASS-11.0	27440302
ECLASS-12.0	27440302
ECLASS-13.0	27440302

ETIM

ETIM 9.0	EC001132
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SUBCON-PLUS-PROFIB/90/M12 - D-SUB bus connector



2902318

<https://www.phoenixcontact.com/us/products/2902318>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	370f4418-6d95-437a-b721-75275f0a9b3c

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com